


RoHS

REV	ECN NO.	DESCRIPTION	DESIGN	APPROVAL	DATE
A1	NEW	更换图框			2023.11.25



技术要求:

1. 端子铆接牢固，无松动，脱落现象；
1. 2. 线材印字清晰，无破损划伤；
2. 外观要求按品质管理部检验标准执行
3. 包装要求按包装作业指引或者客户制定包装要求

序号	名称	规格描述	数量(PCS)
①	胶壳	M0800HI-7-GN XFCN 兴飞	1
②	电线	10064 32# ODO. 38mm 7*0.08mm 黑	1
③	电线	10064 32# ODO. 38mm 7*0.08mm 棕	1
④	电线	10064 32# ODO. 38mm 7*0.08mm 红	1
⑤	电线	10064 32# ODO. 38mm 7*0.08mm 橙	1
⑥	电线	10064 32# ODO. 38mm 7*0.08mm 黄	1
⑦	电线	10064 32# ODO. 38mm 7*0.08mm 绿	1
⑧	电线	10064 32# ODO. 38mm 7*0.08mm 蓝	1

X. ±0.50	x. ° ±	PART NO: XF7006	XFCN兴飞连接器						
. X ±0.25	. x ° ±					TITLE: 连接线/0.8刺破-7P单头线长100mm 尾部剥皮镀锡1.5mm			
. XX ±0.15	. xx ° ±					0769-82001899			
. XXX ±0.10	. xxx ° ±					www.xfconn.com			
UNITS:	mm	DWG NO: /							
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF XFCN AND SHALL NOT BE REPRODUCED, COPIED OR CUED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF XFCN		APPD	VIEW						
		CHKD				SCALE	SHEET	REV	
		DRAW				Wang	NONE	1:1	A1
		DATE				2023.11.25			