


RoHS

REV	ECN NO.	DESCRIPTION	DESIGN	APPROVAL	DATE
A1	NEW	更换图框			2023.11.25



技术要求:

1. 端子铆接牢固，无松动，脱落现象；
1. 2. 线材印字清晰，无破损划伤；
2. 外观要求按品质管理部检验标准执行
3. 包装要求按包装作业指引或者客户制定包装要求

序号	名称	规格描述	数量(PCS)
①	胶壳	M0800HI-8-GN XFCN 兴飞	2
②	电线	UL0064 32# ODO. 38mm 7*0.08mm 黑	1
③	电线	UL0064 32# ODO. 38mm 7*0.08mm 黑	1
④	电线	UL0064 32# ODO. 38mm 7*0.08mm 黑	1
⑤	电线	UL0064 32# ODO. 38mm 7*0.08mm 黑	1
⑥	电线	UL0064 32# ODO. 38mm 7*0.08mm 黑	1
⑦	电线	UL0064 32# ODO. 38mm 7*0.08mm 黑	1
⑧	电线	UL0064 32# ODO. 38mm 7*0.08mm 黑	1

X. ±0.50	x. ° ±	PART NO: XF7017	XFCN兴飞连接器			
. XX ±0.25	. xx ° ±					
. XX ±0.15	. xx ° ±					
. XXX ±0.10	. xxx ° ±					
UNITS:	mm	TITLE: 连接线/0.8刺破-7P双同面线长100mm 不含头	0769-82001899			
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF XFCN AND SHALL NOT BE REPRODUCED, COPIED OR CUED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF XFCN		APPD	www.xfconn.com			
		CHKD	DWG NO: /			
		DRAW	Wang	VIEW		
		DATE	2023.11.25	SCALE	SHEET	REV
				NONE	1:1	A1