SIEMENS

Data sheet for SINAMICS G120X

Article No. :

6SL3230-1YH24-0AP0



Figure similar

Client order no. :
Order no. :
Offer no. :
Remarks :

Rated data		
Input		
Number of phases	3 AC	
Line voltage	500 690 V +10 % -20 %	
Line frequency	47 63 Hz	
Rated voltage	690V IEC	600V NEC
Rated current (LO)	11.00 A	11.00 A
Rated current (HO)	9.90 A	9.90 A
Output		
Number of phases	3 AC	
Rated voltage	690V IEC	600V NEC ¹⁾
Rated power (LO)	7.50 kW	10.00 hp
Rated power (HO)	5.50 kW	7.50 hp
Rated current (LO)	11.00 A	11.00 A
Rated current (HO)	9.00 A	9.00 A
Rated current (IN)	12.00 A	
Max. output current	15.00 A	
Pulse frequency	2 kHz	
Output frequency for vector control	0 200 Hz	
Output frequency for V/f control	0 550 Hz	
Over the end over a billion		

Overload capability

Low Overload (LO)

110% base load current IL for 60 s in a 300 s cycle time

High Overload (HO)

150% x base load current IH for 60 s within a 600 s cycle time

General tech. specifications			
Power factor λ	0.90 0.95		
Offset factor $\cos \phi$	0.99		
Efficiency η	0.97		
Sound pressure level (1m)	70 dB		
Power loss ³⁾	0.306 kW		
Filter class (integrated)	RFI suppression filter for Category C2		
EMC category (with accessories)	Category C2		
Safety function "Safe Torque Off"	without SIRIUS device (e.g. via S7- 1500F)		
Communication			
Communication	PROFIBUS DP		

ltem no. : Consignment no. : Project :

Inputs / outputs			
Standard digital inputs			
Number	6		
Switching level: $0 \rightarrow 1$	11 V		
Switching level: $1 \rightarrow 0$	5 V		
Max. inrush current	15 mA		
Fail-safe digital inputs			
Number	1		
Digital outputs			
Number as relay changeover contact	2		
Output (resistive load)	DC 30 V, 5.0 A		
Number as transistor	0		
Analog / digital inputs			
Number	2 (Differential input)		
Resolution	10 bit		
Switching threshold as digital input			
0 → 1	4 V		
$1 \rightarrow 0$	1.6 V		
Analog outputs			
Number	1 (Non-isolated output)		
PTC/ KTY interface			
1 motor temperature sensor input, ser Thermo-Click, accuracy $\pm 5~^\circ\text{C}$	nsors that can be connected PTC, KTY and		
Closed-loop co	ntrol techniques		

Closed-loop control techniques			
V/f linear / square-law / parameterizable	Yes		
V/f with flux current control (FCC)	Yes		
V/f ECO linear / square-law	Yes		
Sensorless vector control	Yes		
Vector control, with sensor	No		
Encoderless torque control	No		
Torque control, with encoder	No		

SIEMENS

Data sheet for SINAMICS G120X

Article No. :

6SL3230-1YH24-0AP0

Ambier	at conditions			
Ambient conditions				
Standard board coating type	Class 3C3, according to IEC 60721-3-3: 2002			
Cooling	Air cooling using an integrated fan			
Cooling air requirement	0.055 m³/s (1.942 ft³/s)			
Installation altitude	1,000 m (3,280.84 ft)			
Ambient temperature				
Operation	-20 45 °C (-4 113 °F)			
Transport	-40 70 °C (-40 158 °F)			
Storage	-25 55 °C (-13 131 °F)			
Relative humidity				
Max. operation	95 % At 40 °C (104 °F), condensation and icing not permissible			
Connections				
Signal cable				
Conductor cross-section	0.15 1.50 mm² (AWG 24 AWG 16)			
Line side				
Version	screw-type terminal			
Conductor cross-section	10.00 35.00 mm² (AWG 8 AWG 2)			
Motor end				
Version	Screw-type terminals			
Conductor cross-section	10.00 35.00 mm² (AWG 8 AWG 2)			
DC link (for braking resistor)				
PE connection	Screw-type terminals			
Max. motor cable length				
Shielded	100 m (328.08 ft)			

Me	chanical data		
Degree of protection	IP20 / UL open	IP20 / UL open type	
Frame size	FSD		
Net weight	18.3 kg (40.34	lb)	
Dimensions			
Width	200 mm (7.87	200 mm (7.87 in)	
Height	472 mm (18.58 in)		
Depth	248 mm (9.76	in)	
	Standards		
Compliance with standards	UL, cUL, CE, C-Tick (RCM), EAC, KCC, SEMI F47, REACH		
CE marking	EMC Directive 2004/108/EC, Low- Voltage Directive 2006/95/EC		
Converter lo	osses to IEC61800-	9-2*	
Efficiency class	IE2		
Comparison with the reference converter (90% / 100%)	42.9 %		
I ▲ 274.0 W (2.1 %)	287.0 W (2.2 %)	306.0 W (2.3 %)	
100% •	•	•	
	220.0W(4.7%)		
215.0 W (1.6 %) 50% •	220.0 W (1.7 %)	227.0 W (1.7 %)	
193.0 W (1.5 %)	195.0 W (1.5 %)		
25% •	•		

The percentage values show the losses in relation to the rated apparent power of the converter.

90% **f**

50%

The diagram shows the losses for the points (as per standard IEC61800-9-2) of the relative torque generating current (I) over the relative motor stator frequency (f). The values are valid for the basic version of the converter without options/components.

*converted values

¹⁾The output current and HP ratings are valid for the voltage range 550V-600V

³⁾ Typical value. More information can be found in the element group "Converter losses to IEC 61800-9-2" in this datasheet.