


# RoHS

REV	ECN NO.	DESCRIPTION	DESIGN	APPROVAL	DATE
A1	NEW	更换图框			2023.11.25



- 技术要求:
1. 端子铆接牢固, 无松动, 脱落现象;
  1. 2. 线材印字清晰, 无破损划伤;
  2. 外观要求按品质管理部检验标准执行
  3. 包装要求按包装作业指引或者客户制定包装要求

序号	名称	规格描述	数量(PCS)
①	胶壳	M0800HI-10-GN XFCN 兴飞	2
②	电线	10064 32# OD0.38mm 7*0.08mm 黑	1
③	电线	10064 32# OD0.38mm 7*0.08mm 黑	1
④	电线	10064 32# OD0.38mm 7*0.08mm 黑	1
⑤	电线	10064 32# OD0.38mm 7*0.08mm 黑	1
⑥	电线	10064 32# OD0.38mm 7*0.08mm 黑	1
⑦	电线	10064 32# OD0.38mm 7*0.08mm 黑	1
⑧	电线	10064 32# OD0.38mm 7*0.08mm 黑	1
⑨	电线	10064 32# OD0.38mm 7*0.08mm 黑	1
⑩	电线	10064 32# OD0.38mm 7*0.08mm 黑	1
⑪	电线	10064 32# OD0.38mm 7*0.08mm 黑	1

X. ±0.50	x. ° ±	PART NO: XF7020	<b>XFCN兴飞连接器</b>				
. X ±0.25	. x ° ±					0769-82001899	
. XX ±0.15	. xx ° ±					www.xfconn.com	
. XXX ±0.10	. xxx ° ±					DWG NO: /	
UNITS:	mm	TITLE: 连接线/0.8刺破-10P双同面线长 100mm不含头	APPD				
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF XFCN AND SHALL NOT BE REPRODUCED, COPIED OR CUED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF XFCN			CHKD		VIEW		
			DRAW	Wang	SCALE	SHEET	
			DATE	2023.11.25	NONE	1:1	REV
							A1