

т	D I	н <b>т</b>	m	0







LAYOUT SHOWN AS

Keying Shown as example

## CHARACTERISTICS

ယ

 $\sim$ 

-Mass

BASIC SERIES:

SHELL SIZE : 11

Н

SHELL TYPE : Square Flange Receptacle

CONTACT TYPE : Standard Crimp Contact

PLATING : W = Olive drab Cadmium

-Standard : Based on MIL-DTL-38999 Series III

ł	-Shell Material	: Aluminium
	-Shell Plating	: Olive drab Cadmium
	-Insulator	: Thermoplastic
	-Contacts	: Copper Alloy
	-Seals & Grommet	: Silicon Elastomer
	-Contact Plating	: Gold over copper Alloy $0.8 \mu m$ minimum
	-Durability	: 500 Mating cycles
-Delivered without Souriau contacts		
	-Temperature Range	: -65°C to +175°C
	-Salt Spray	: 500 hours

: 12.92 g ± 10%

8D 0

G

11

W

22

S

F


В ΙL

Connector dimension			
Dim	Nominal		
Р	3.25±0.2		
PP	4.93±0.2		
R1	20.62		
R2	18.26		
S	26.2±0.3		
V	20.83+0/-1.25		
W	2.1/2.5		
Z	31.5 Max		
VV THREAD	M15x1-6g		

CONTACT TYPE : SOCKET(500 Matings)

Е

SOURIAU shall not be liable for due to a use of the Products the Specifications issued by either (professional recomment



	σ		А			
		I				
-						
					4	
1	6 500					
	V DAVES	7				
	-					
	1					
	1 10	1				
	1					
S EXA	MPLE				3	
	non-conformit h does not co					
	of the Parties or by a third party dation, technical notice.)					
Intry R	Jurisd	liction & Cont Not Listed	rol List		2	
<u>\۷</u> /	W22SBL					
		CUSTONAL		MOD N°		
		CUSIONE	R DRAWING			
um	m Receptacle 8D series					
ar	NPRDS / PROJECT					
			59		1	
	.COM This document is the property of SOURIAU it must not be reproduced or					
		it must not be reproduced or communicated without permission				
	U DRG N° SHEET					
N2	2SBL-C			1/2		
	В		А			

4	(	Contact Layout 22*				SI T	QUARE FLANGE RECEPTACLE ( REAR MOUNTING R1	Panel Cu TYPE 0)
	Ctc A B	4#22D 11-22 X Y 1.905 1.905 1.905 -1.905				V		ØT_
ယ	C D	-1.905 -1.905 -1.905 1.905						Dim ØA ØAA R1 ØT
							the Specifications	of the Products
2							PI	Cou F N: 8D011
					A ISS Design	DATE	6 First Release Latest modificatio Date:	n - by
-					SCA N.			Aluminiu General linea Tolerances: ±
					FOR		WWW	SOURIAU
		I	I		A	3		8D011V
	Н	G	F	E	D		С	

Т

ш

т

G

0

