


■ PRODUCT CHARACTERISTICS

VDSS	500
R _{DS(on)typ} (@V _{GS} = 10 V)	0.48Ω
Q _G @type	43nC
ID	13A



■ APPLICATIONS

- High efficiency switch mode power supplies
- Electronic ballasts
- LED power supply

■ FEATURES

- * High Switching Speed
- * 100% Avalanche Tested



■ ORDER INFORMATION

Order codes		Package	Packing
Halogen-Free	Halogen		
N/A	MOT13N50SF	TO-220F	50 pieces/Tube
N/A	MOT13N50SA	TO-220	50 pieces/Tube

■ ABSOLUTE MAXIMUM RATINGS (T_C = 25°C, unless otherwise specified)

PARAMETER	SYMBOL	RATINGS	UNIT
Drain-Source Voltage	V _{DSS}	500	V
Gate-Source Voltage	V _{GSS}	±30	V
Continuous Drain Current	I _D	13	A
Pulsed Drain Current (Note 2)	I _{DM}	52	A
Avalanche Current (Note 2)	I _{AR}	13	A
Single Pulsed Avalanche Energy (Note 3)	E _{AS}	860	mJ
Repetitive Avalanche Energy (Note 2)	E _{AR}	19.5	mJ
Peak Diode Recovery dv/dt (Note 4)	dv/dt	4.5	V/ns
Power Dissipation (T _C =25°C)	TO-220	P _D	195
	TO-220F		48
Junction Temperature	T _J	+150	°C
Storage Temperature	T _{STG}	-55~+150	°C

Notes: 1. Absolute maximum ratings are those values beyond which the device could be permanently damaged.

Absolute maximum ratings are stress ratings only and functional device operation is not implied.

2. Repetitive Rating : Pulse width limited by maximum junction temperature

3. L = 6.0, I_{AS} = 13A, V_{DD} = 50V, R_G = 25Ω, Starting T_J = 25°C

4. I_{SD} ≤ 13A, di/dt ≤ 200A/μs, V_{DD} ≤ BV_{DSS}, Starting T_J = 25°C



■ ELECTRICAL CHARACTERISTICS ($T_C=25^\circ\text{C}$, unless otherwise noted)







PARAMETER	SYMBOL	TEST CONDITIONS	MIN	TYP	MAX	UNIT
Off characteristics						
Drain-Source Breakdown Voltage	BV_{DSS}	$V_{\text{GS}} = 0\text{V}, I_{\text{D}} = 250\mu\text{A}$	500	-	-	V
Drain-Source Leakage Current	I_{DSS}	$V_{\text{DS}} = 500\text{V}, V_{\text{GS}} = 0\text{V}$	-	-	1	μA
Gate-Source Leakage Current	I_{GSS}	$V_{\text{GS}} = 30\text{V}, V_{\text{DS}} = 0\text{V}$	-	-	100	nA
		$V_{\text{GS}} = -30\text{V}, V_{\text{DS}} = 0\text{V}$	-	-	-100	nA
Breakdown Voltage Temperature Coefficient	$\Delta \text{BV}_{\text{DSS}}/\Delta T_J$	$I_{\text{D}} = 250\mu\text{A}$ Referenced to 25°C	-	0.5	-	$\text{V}/^\circ\text{C}$
On characteristics						
Gate Threshold Voltage	$V_{\text{GS(TH)}}$	$V_{\text{DS}} = V_{\text{GS}}, I_{\text{D}} = 250\mu\text{A}$	2.0	-	4.0	V
Static Drain-Source On-State Resistance	$R_{\text{DS(ON)}}$	$V_{\text{GS}} = 10\text{V}, I_{\text{D}} = 6.5\text{A}$	-	0.48	0.52	Ω
Dynamic characteristics						
Input Capacitance	C_{ISS}	$V_{\text{DS}}=25\text{V}, V_{\text{GS}}=0\text{V}, f=1.0\text{MHz}$	-	1580	-	pF
Output Capacitance	C_{OSS}		-	180	-	pF
Reverse Transfer Capacitance	C_{RSS}		-	20	-	pF
Switching characteristics						
Turn-On Delay Time	$t_{\text{D(ON)}}$	$V_{\text{DD}} = 250\text{V}, I_{\text{D}} = 13\text{A}$ $R_{\text{G}} = 25\Omega$ (Note 1,2)	-	25	-	nS
Turn-On Rise Time	t_{R}		-	100	-	nS
Turn-Off Delay Time	$t_{\text{D(OFF)}}$		-	130	-	nS
Turn-Off Fall Time	t_{F}		-	100	-	nS
Total Gate Charge	Q_{G}	$V_{\text{DS}}=400\text{V}, I_{\text{D}}=13\text{A}, V_{\text{GS}}=10\text{V}$ (Note 1, 2)	-	43	-	nC
Gate-Source Charge	Q_{GS}		-	7.5	-	nC
Gate-Drain Charge	Q_{GD}		-	18.5	-	nC
Drain-source diode characteristics						
Drain-Source Diode Forward Voltage	V_{SD}	$V_{\text{GS}} = 0\text{V}, I_{\text{S}} = 13\text{ A}$	-	-	1.4	V
Maximum Continuous Drain-Source Diode Forward Current	I_{S}		-	-	13	A
Maximum Pulsed Drain-Source Diode Forward Current	I_{SM}		-	-	52	A
Reverse Recovery Time	t_{RR}	$V_{\text{GS}} = 0\text{V}, I_{\text{S}} = 13\text{A},$ $dI_{\text{F}}/dt = 100\text{A}/\mu\text{s}$ (Note 1)	-	410	-	nS
Reverse Recovery Charge	Q_{RR}		-	4.5	-	μC

Notes: 1. Pulse Test : Pulse width $\leq 300\mu\text{s}$, Duty cycle $\leq 2\%$


2. Essentially independent of operating ambient temperature

■ TEST CIRCUITS AND WAVEFORMS


Fig. 1A Peak Diode Recovery dv/dt Test Circuit

Fig. 1B Peak Diode Recovery dv/dt Waveforms

■ TEST CIRCUITS AND WAVEFORMS(Cont.)

Fig. 2A Switching Test Circuit

Fig. 2B Switching Waveforms

Fig. 3A Gate Charge Test Circuit

Fig. 3B Gate Charge Waveform

Fig. 4A Unclamped Inductive Switching Test Circuit

Fig. 4B Unclamped Inductive Switching Waveforms

■ TO-220F-3L PACKAGE OUTLINE DIMENSIONS



■ TO-220-3L PACKAGE OUTLINE DIMENSIONS

