

Ŧ	۵	г	m	0







LAYOUT SHOWN AS

Keying Shown as example

F

## CHARACTERISTICS

ω

-Standard : Based on MIL-DTL-38999 Series III

CONTACT TYPE : Standard Crimp Contact

SHELL SIZE : 21

PLATING : M = Nickel

Н

$\frown$		: Composite	Р
			PP
	-Shell Plating	: Nickel	R1
	-Insulator	: Thermoplastic	R2
	-Contacts	: Copper Alloy	S V'
	-Seals & Grommet	: Silicon Elastomer	W'
$\sim$	-Contact Plating	: Gold over copper Alloy 0.8µm minimum	Ζ'
	-Durability	: 500 Mating cycles	VV THREAD
	-	u contacts and Accessories	
	-Temperature Range	65°C to +200°C	
	-Salt Spray	: 2000 hours	
_	-Mass	: 42.6 g ± 10%	
	BASIC SERIES:	8D 0 - 21 M 75 A A	
-	SHELL TYPE : Square	Flange Receptacle	
I			k

G

P PP	3.25±0.2 4.93±0.2
	4.93±0.2
R1	31.75
R2	29.36
S	39.7±0.3
V'	18.7+1.4/-0
W'	2.1/4.35
Z'	32 Max
VV THREAD	M31x1-6g

**ORIENTATION : A** 


D

CONTACT TYPE : PIN(500 Matings)

Е

CONTACT LAYOUT : 21-75

SOURIAU shall not be liable for due to a use of the Products the Specifications issued by either (professional recomment



	Φ		А			
	Re				4	
					3	
AS EXA	EXAMPLE					
any non-conformity or damage which does not comply with or of the Parties or by a third party adation, technical notice.)						
untry FR	y Jurisdiction & Control List Not Listed					
1M	M75AA					
		CUSTOME	R DRAWING	MOD N°		
site	e Receptacle 8D series					
ar	NPRDS / PROJECT 859					
J.CC	.COM This document is the property of SOURIAU it must not be reproduced or communicated without permission					
	DRG N°			SHEET		
M7	'5AA-C		A	1/2	J	
	В		A			

