

■ PRODUCT CHARACTERISTICS

VDSS	650V
$R_{DS(on)}$ Typ(@ $V_{GS}=10V$ )	0.33Ω
Qg@type	4.8nC
ID	11A




■ APPLICATIONS

- \* Power factor correction
- \* Switched mode power supplies
- \* Uninterruptible power supply

■ FEATURES

- \* low  $R_{DS(on)}$
- \* low gate charge
- \* 100% UIS tested
- \* RoHS compliant

Symbol



■ ORDER INFORMATION

Order codes		Package	Packing
Halogen-Free	Halogen		
N/A	MOT65R380C	TO-251	70 pieces/Tube
N/A	MOT65R380D	TO-252	2500 pieces/Reel

■ ABSOLUTE MAXIMUM RATINGS ( $T_C=25^{\circ}C$  unless otherwise specified)

Parameter	Symbol	Value	Unit	
Drain-Source Voltage	$V_{DSS}$	650	V	
Continuous drain current	$I_D$	( $T_C = 25^{\circ}C$ )	11	
		( $T_C = 100^{\circ}C$ )	8.2	
Pulsed drain current <sup>1)</sup>	$I_{DM}$	30	A	
Gate-Source voltage	$V_{GSS}$	$\pm 30$	V	
Avalanche energy, single pulse <sup>2)</sup>	$E_{AS}$	245	mJ	
Avalanche current, repetitive <sup>3)</sup>	$I_{AR}$	11	A	
Power Dissipation	$P_D$	90	W	
( $T_C = 25^{\circ}C$ )		0.72	W/ $^{\circ}C$	
Power Dissipation		( $T_C = 25^{\circ}C$ )	31.8	W
		- Derate above 25 $^{\circ}C$	0.26	W/ $^{\circ}C$
Operating and Storage Temperature Range	$T_J, T_{STG}$	-55 to +150	$^{\circ}C$	
Continuous diode forward current	$I_S$	11	A	
Diode pulse current	$I_{S,pulse}$	30	A	

■ THERMAL CHARACTERISTICS

Parameter	Symbol	Value	Unit
Thermal Resistance, Junction-to-Case	$R_{\theta JC}$	1.39	$^{\circ}C/W$
Thermal Resistance, Junction-to-Ambient	$R_{\theta JA}$	45	$^{\circ}C/W$

**■ ELECTRICAL CHARACTERISTICS**

Parameter	Symbol	Test conditions	Min.	Typ.	Max.	Unit
<b>Static characteristics</b>						
Drain-source breakdown voltage	$BV_{DSS}$	$V_{GS}=0\text{ V}, I_D=0.25\text{ mA}$	650	-	-	V
Gate threshold voltage	$V_{GS(th)}$	$V_{DS}=V_{GS}, I_D=0.25\text{ mA}$	2.5	3.5	4.5	V
Drain cut-off current	$I_{DSS}$	$V_{DS}=650\text{ V}, V_{GS}=0\text{ V}, T_j = 25^\circ\text{C}$			1	$\mu\text{A}$
		$T_j = 125^\circ\text{C}$	-	10		
Gate leakage current, Forward	$I_{GSSF}$	$V_{GS}=30\text{ V}, V_{DS}=0\text{ V}$	-	-	100	nA
Gate leakage current, Reverse	$I_{GSSR}$	$V_{GS}=-30\text{ V}, V_{DS}=0\text{ V}$	-	-	-100	nA
Drain-source on-state resistance	$R_{DS(on)}$	$V_{GS}=10\text{ V}, I_D=5.5\text{ A}, T_j = 25^\circ\text{C}$	-	0.33	0.38	$\Omega$
		$T_j = 150^\circ\text{C}$	-	0.9	-	
Gate resistance	$R_G$	$f=1\text{ MHz}, \text{open drain}$	-	5.7	-	$\Omega$
<b>Dynamic characteristics</b>						
Input capacitance	$C_{iss}$	$V_{DS} = 25\text{ V}, V_{GS} = 0\text{ V},$ $f = 1\text{ MHz}$	-	560	-	$\mu\text{F}$
Output capacitance	$C_{oss}$		-	216	-	
Reverse transfer capacitance	$C_{rss}$		-	1.2	-	
Turn-on delay time	$t_{d(on)}$	$V_{DD} = 400\text{ V}, I_D = 5.5\text{ A}$ $R_G = 10\Omega, V_{GS}=15\text{ V}$	-	20.6	-	ns
Rise time	$t_r$		-	32	-	
Turn-off delay time	$t_{d(off)}$		-	62	-	
Fall time	$t_f$		-	12.5	-	
<b>Gate charge characteristics</b>						
Gate to source charge	$Q_{gs}$	$V_{DD}=400\text{ V}, I_D=5.5\text{ A},$ $V_{GS}=0\text{ to }10\text{ V}$	-	4.8	-	nC
Gate to drain charge	$Q_{gd}$		-	4.7	-	
Gate charge total	$Q_g$		-	14.7	-	
Gate plateau voltage	$V_{plateau}$		-	6	-	V
<b>Reverse diode characteristics</b>						
Diode forward voltage	$V_{SD}$	$V_{GS}=0\text{ V}, I_F=5.5\text{ A}$	-	1.2	-	V
Reverse recovery time	$t_{rr}$	$V_R=400\text{ V}, I_F=5.5\text{ A},$ $dI_F/dt=100\text{ A}/\mu\text{s}$	-	234	-	ns
Reverse recovery charge	$Q_{rr}$		-	4.4	-	$\mu\text{C}$
Peak reverse recovery current	$I_{rrm}$		-	18.7	-	A

**Notes:**

- Limited by maximum junction temperature, maximum duty cycle is 0.75.
- $I_{AS} = 3\text{ A}, V_{DD} = 60\text{ V}, \text{Starting } T_j = 25^\circ\text{C}.$
- Repetitive Rating: Pulse width limited by maximum junction temperature.

■ ELECTRICAL CHARACTERISTICS DIAGRAMS




Figure 1. On-Region Characteristics




Figure 2. Transfer Characteristics




Figure 3. On-Resistance Variation vs. Drain Current




Figure 4. Threshold Voltage vs. Temperature




Figure 5. Breakdown Voltage vs. Temperature




Figure 6. On-Resistance vs. Temperature

■ ELECTRICAL CHARACTERISTICS(Cont.)




Figure 7. Capacitance Characteristics




Figure 8. Gate Charge Characteristic




Figure 9.1 Maximum Safe Operating Area




Figure 9.2 Maximum Safe Operating Area




Figure 10.1 Power Dissipation vs. Temperature








Figure 10.2 Power Dissipation vs. Temperature



■ TEST CIRCUITS AND WAVEFORMS



Switching Test Circuit & Waveforms



Unclamped Inductive Switching Test Circuit & Waveforms



■ TO-252-2L PACKAGE OUTLINE DIMENSIONS

