ב ב ב ב ב ב ב ב ב ב ב ב ב ב ב ב ב ב ב	т (г	D		0	Φ	⊳]	
	ØS			LAYOUT SHO	WN AS EXAMPLE			4	
				LATOUT SHO	WIN AS LAAWIF LL				
	Keying Shown as example								
CHARACTERISTICS -Standard : Based on MIL-DTL-38999 Series III	Connector dime Dim	ension Nominal							
-Shell Material : Composite -Shell Plating : Nickel -Insulator : Thermoplastic -Contacts : Copper Alloy -Seals & Grommet : Silicon Elastomer -Contact Plating : Gold over copper Alloy 0.8μm minimum	-Shell Material : Composite -Shell Material : Composite -Shell Plating : Nickel -Shell Plating : Nickel -Insulator : Thermoplastic -Contacts : Copper Alloy -Seals & Grommet : Silicon Elastomer							2	
-Durability : 500 Mating cycles -Delivered with Souriau contacts and Accessories	-Durability : 500 Mating cycles				PN: 8D523M35AD				
-Temperature Range : -65°C to +200°C -Salt Spray : 2000 hours			A 07-10-2016	First Release					
			ISS DATE	Latest modification - by			MOD N°	<u> </u>	
		De	esigned By:	Date: CUSTOMER DRAWING Composite Plug 8D series					
BASIC SERIES: 8D 5 - 23 M HELL TYPE : Plug with RFI Shielding	1 35 A D		SCALE NA	[-(⊕) Toler	al linear g ances: :	NPRDS / PROJECT 859		1	
CONTACT TYPE : Standard Crimp Contact SHELL SIZE : 23 CONTACT TYPE : PIN(500 Matings)			SOURIAU WWW.SOURIAU.COM This document is the property of SOURIAU it must not be reproduced or communicated without permission						
PLATING : M = Nickel		CONTACT LATOOT . 23-33	FORMAT		RIAU DRG N°		SHEET		
			A3		23M35AD-C		1/2	J	
H G I	F I E	D		C	В	I A			

