

## ■ PRODUCT CHARACTERISTICS


VDSS	650V
R <sub>DS(on)Typ(@V<sub>GS</sub> =10 V)</sub>	1.3Ω
Qg@type	29nC
ID	7A

## ■ APPLICATIONS


- High efficiency switch mode power supplies
- Electronic lamp ballasts based on half bridge
- LED power supplies

## ■ FEATURES

- \* Ultra low gate charge
- \* Low reverse transfer Capacitance
- \* Fast switching capability
- \* Avalanche energy tested
- \* Improved dv/dt capability, high ruggedness



TO-252



TO-251

## ■ ORDER INFORMATION

Order codes		Package	Packing
Halogen-Free	Halogen		
N/A	MOT7N65AD	TO-252	2500 pieces /Reel
N/A	MOT7N65AC	TO-251	70 pieces/Tube

## ■ ABSOLUTE MAXIMUM RATINGS (T<sub>C</sub>=25°C, unless otherwise specified)

PARAMETER		SYMBOL	RATINGS	UNIT
Drain-Source Voltage		V <sub>DSS</sub>	650	V
Gate-Source Voltage		V <sub>GSS</sub>	±30	V
Avalanche Current (Note 2)		I <sub>AR</sub>	7	A
Drain Current	Continuous	I <sub>D</sub>	7	A
	Pulsed (Note 2)	I <sub>DM</sub>	29.6	A
Avalanche Energy	Single Pulsed (Note 3)	E <sub>AS</sub>	530	mJ
	Repetitive (Note 2)	E <sub>AR</sub>	14.2	mJ
Peak Diode Recovery dv/dt (Note 4)		dv/dt	4.5	V/ns
Power Dissipation	TO-252/251	P <sub>D</sub>	120	W
Junction Temperature		T <sub>J</sub>	+150	°C
Storage Temperature		T <sub>STG</sub>	-55 ~ +150	°C

Notes: 1. Absolute maximum ratings are those values beyond which the device could be permanently damaged.

Absolute maximum ratings are stress ratings only and functional device operation is not implied.

2. Repetitive Rating : Pulse width limited by maximum junction temperature

3. L = 19.5mH, I<sub>AS</sub> = 7A, V<sub>DD</sub> = 50V, R<sub>G</sub> = 25 Ω, Starting T<sub>J</sub> = 25°C

4. I<sub>SD</sub>≤7A, di/dt≤200A/μs, V<sub>DD</sub>≤BV<sub>DSS</sub>, Starting T<sub>J</sub> = 25°C


■ ELECTRICAL CHARACTERISTICS ( $T_J=25^\circ\text{C}$ , unless otherwise specified)

PARAMETER	SYMBOL	TEST CONDITIONS	MIN	TYP	MAX	UNIT
Off characteristics						
Drain-Source Breakdown Voltage	$\text{BV}_{\text{DSS}}$	$V_{\text{GS}} = 0\text{V}, I_{\text{D}} = 250\mu\text{A}$	650	-	-	V
Drain-Source Leakage Current	$I_{\text{DSS}}$	$V_{\text{DS}} = 650\text{V}, V_{\text{GS}} = 0\text{V}$	-	-	1	$\mu\text{A}$
Gate- Source Leakage Current	Forward	$V_{\text{GS}} = 30\text{V}, V_{\text{DS}} = 0\text{V}$	-	-	100	nA
	Reverse	$V_{\text{GS}} = -30\text{V}, V_{\text{DS}} = 0\text{V}$	-	-	-100	nA
Breakdown Voltage Temperature Coefficient	$\Delta \text{BV}_{\text{DSS}}/\Delta T_J$	$I_{\text{D}}=250\mu\text{A}$ , Referenced to $25^\circ\text{C}$	-	0.67	-	$\text{V}/^\circ\text{C}$
On characteristics						
Gate Threshold Voltage	$V_{\text{GS(TH)}}$	$V_{\text{DS}} = V_{\text{GS}}, I_{\text{D}} = 250\mu\text{A}$	2.0	-	4.0	V
Static Drain-Source On-State Resistance	$R_{\text{DS(ON)}}$	$V_{\text{GS}} = 10\text{V}, I_{\text{D}} = 3.5\text{A}$	-	1.3	1.5	$\Omega$
Dynamic characteristics						
Input Capacitance	$C_{\text{ISS}}$	$V_{\text{DS}}=25\text{V}, V_{\text{GS}}=0\text{V}, f=1.0\text{ MHz}$	-	1400	-	pF
Output Capacitance	$C_{\text{OSS}}$		-	180	-	pF
Reverse Transfer Capacitance	$C_{\text{RSS}}$		-	16	-	pF
Switching characteristics						
Turn-On Delay Time	$t_{\text{D(ON)}}$	$V_{\text{DD}} = 325\text{V}, I_{\text{D}} = 7.4\text{A}, R_{\text{G}} = 25\Omega$ (Note 1, 2)	-	90	-	ns
Turn-On Rise Time	$t_{\text{R}}$		-	120	-	ns
Turn-Off Delay Time	$t_{\text{D(OFF)}}$		-	95	-	ns
Turn-Off Fall Time	$t_{\text{F}}$		-	60	-	ns
Switching characteristics						
Total Gate Charge	$Q_{\text{G}}$	$V_{\text{DS}}=520\text{V}, I_{\text{D}} = 7\text{A}, V_{\text{GS}}=10\text{ V}$ (Note 1, 2)	-	29	-	nC
Gate-Source Charge	$Q_{\text{GS}}$		-	7	-	nC
Gate-Drain Charge	$Q_{\text{GD}}$		-	14.5	-	nC
Drain-source diode characteristics and maximum ratings						
Drain-Source Diode Forward Voltage	$V_{\text{SD}}$	$V_{\text{GS}} = 0\text{V}, I_{\text{S}} = 7\text{A}$	-	-	1.4	V
Maximum Continuous Drain-Source Diode Forward Current	$I_{\text{S}}$		-	-	7	A
Maximum Pulsed Drain-Source Diode Forward Current	$I_{\text{SM}}$		-	-	29.6	A
Reverse Recovery Time	$t_{\text{rr}}$	$V_{\text{GS}} = 0\text{V}, I_{\text{S}} = 7\text{A}, dI_{\text{F}} / dt = 100\text{A}/\mu\text{s}$ (Note 1)	-	320	-	ns
Reverse Recovery Charge	$Q_{\text{RR}}$		-	2.4	-	$\mu\text{C}$


Notes: 1. Pulse Test: Pulse width  $\leq 300\mu\text{s}$ , Duty cycle  $\leq 2\%$

2. Essentially independent of operating temperature

## ■ TEST CIRCUITS AND WAVEFORMS









**Peak Diode Recovery dv/dt Test Circuit**




**Peak Diode Recovery dv/dt Waveforms**

## ■ TEST CIRCUITS AND WAVEFORMS(Cont.)



**Switching Test Circuit**
**Switching Waveforms**

**Gate Charge Test Circuit**

**Gate Charge Waveform**

**Unclamped Inductive Switching Test Circuit**

**Unclamped Inductive Switching Waveforms**

## ■ ELECTRICAL CHARACTERISTICS


### On-Region Characteristics




**On-Resistance Variation vs.  
Drain Current and Gate Voltage**




**Capacitance Characteristics**




**Breakdown Voltage Variation  
vs. Temperature**




### Transfer Characteristics




**Body Diode Forward Voltage Variation  
vs. Source Current and Temperature**




**Gate Charge Characteristics**



**On-Resistance Variation  
vs. Temperature**



■ TO-251 PACKAGE OUTLINE DIMENSIONS



## ■ TO-252 PACKAGE OUTLINE DIMENSIONS

