

■ PRODUCT CHARACTERISTICS

VDSS	650V
R _{DS(on)} Typ(@V _{GS} =10V)	1.1Ω
Qg@type	29nC
ID	7A



■ APPLICATIONS

- High efficiency switch mode power supplies
- Electronic lamp ballasts based on half bridge
- LED power supplies

■ FEATURES

- * Ultra low gate charge
- * Low reverse transfer Capacitance
- * Fast switching capability
- * Avalanche energy tested
- * Improved dv/dt capability, high ruggedness

Symbol



■ ORDER INFORMATION

Order codes		Package	Packing
Halogen-Free	Halogen		
N/A	MOT7N65AF	TO-220F	50 pieces/Tube
N/A	MOT7N65A	TO-220	50 pieces/Tube

■ ABSOLUTE MAXIMUM RATINGS (T_C = 25°C, unless otherwise specified)

PARAMETER		SYMBOL	RATINGS	UNIT
Drain-Source Voltage		V _{DSS}	650	V
Gate-Source Voltage		V _{GSS}	±30	V
Avalanche Current (Note 2)		I _{AR}	7	A
Drain Current	Continuous	I _D	7	A
	Pulsed (Note 2)	I _{DM}	29.6	A
Avalanche Energy	Single Pulsed (Note 3)	E _{AS}	530	mJ
	Repetitive (Note 2)	E _{AR}	14.2	mJ
Peak Diode Recovery dv/dt (Note 4)		dv/dt	4.5	V/ns
Power Dissipation	TO-220	P _D	142	W
	TO-220F		48	W
Junction Temperature		T _J	+150	°C
Storage Temperature		T _{STG}	-55 ~ +150	°C

Notes: 1. Absolute maximum ratings are those values beyond which the device could be permanently damaged.

Absolute maximum ratings are stress ratings only and functional device operation is not implied.

2. Repetitive Rating : Pulse width limited by maximum junction temperature

3. L = 19.5mH, I_{AS} = 7A, V_{DD} = 50V, R_G = 25 Ω, Starting T_J = 25°C

4. I_{SD}≤7A, di/dt≤200A/μs, V_{DD}≤BV_{DSS}, Starting T_J = 25°C


■ ELECTRICAL CHARACTERISTICS ($T_C = 25^\circ\text{C}$, unless otherwise specified)

PARAMETER	SYMBOL	TEST CONDITIONS	MIN	TYP	MAX	UNIT
<hr/>						
Drain-Source Breakdown Voltage	BV_{DSS}	$\text{V}_{\text{GS}} = 0\text{V}, \text{I}_D = 250\mu\text{A}$	650	-	-	V
Drain-Source Leakage Current	I_{DSS}	$\text{V}_{\text{DS}} = 650\text{V}, \text{V}_{\text{GS}} = 0\text{V}$	-	-	1	μA
Gate- Source Leakage Current	Forward	$\text{V}_{\text{GS}} = 30\text{V}, \text{V}_{\text{DS}} = 0\text{V}$	-	-	100	nA
	Reverse	$\text{V}_{\text{GS}} = -30\text{V}, \text{V}_{\text{DS}} = 0\text{V}$	-	-	-100	nA
Breakdown Voltage Temperature Coefficient	$\triangle \text{BV}_{\text{DSS}}/\triangle T_J$	$\text{I}_D=250\mu\text{A}$, Referenced to 25°C	-	0.67	-	$\text{V}/^\circ\text{C}$
On characteristics						
Gate Threshold Voltage	$\text{V}_{\text{GS(TH)}}$	$\text{V}_{\text{DS}} = \text{V}_{\text{GS}}, \text{I}_D = 250\mu\text{A}$	2.0	-	4.0	V
Static Drain-Source On-State Resistance	$\text{R}_{\text{DS(ON)}}$	$\text{V}_{\text{GS}} = 10\text{V}, \text{I}_D = 3.5\text{A}$	-	1.1	1.2	Ω
Dynamic characteristics						
Input Capacitance	C_{ISS}	$\text{V}_{\text{DS}}=25\text{V}, \text{V}_{\text{GS}}=0\text{V},$ $f=1.0 \text{ MHz}$	-	1400	-	pF
Output Capacitance	C_{OSS}		-	180	-	pF
Reverse Transfer Capacitance	C_{RSS}		-	16	-	pF
Switching characteristics						
Turn-On Delay Time	$t_{\text{D(ON)}}$	$\text{V}_{\text{DD}} = 325\text{V}, \text{I}_D = 7.4\text{A},$ $\text{R}_G = 25\Omega$ (Note 1, 2)	-	70	-	ns
Turn-On Rise Time	t_R		-	170	-	ns
Turn-Off Delay Time	$t_{\text{D(OFF)}}$		-	140	-	ns
Turn-Off Fall Time	t_F		-	130	-	ns
Switching characteristics						
Total Gate Charge	Q_G	$\text{V}_{\text{DS}}=520\text{V}, \text{I}_D = 7\text{A},$ $\text{V}_{\text{GS}}=10 \text{ V}$ (Note 1, 2)	-	29	-	nC
Gate-Source Charge	Q_{GS}		-	7	-	nC
Gate-Drain Charge	Q_{GD}		-	14.5	-	nC
Drain-source diode characteristics and maximum ratings						
Drain-Source Diode Forward Voltage	V_{SD}	$\text{V}_{\text{GS}} = 0\text{V}, \text{I}_S = 7\text{A}$	-	-	1.4	V
Maximum Continuous Drain-Source Diode Forward Current	I_S		-	-	7	A
Maximum Pulsed Drain-Source Diode Forward Current	I_{SM}		-	-	29.6	A
Reverse Recovery Time	t_{rr}	$\text{V}_{\text{GS}} = 0\text{V}, \text{I}_S = 7\text{A},$ $d\text{I}_F / dt = 100\text{A}/\mu\text{s}$ (Note 1)	-	320	-	ns
Reverse Recovery Charge	Q_{RR}		-	2.4	-	μC


Notes: 1. Pulse Test: Pulse width $\leq 300\mu\text{s}$, Duty cycle $\leq 2\%$

2. Essentially independent of operating temperature

■ TEST CIRCUITS AND WAVEFORMS









Peak Diode Recovery dv/dt Test Circuit




Peak Diode Recovery dv/dt Waveforms

■ TEST CIRCUITS AND WAVEFORMS(Cont.)



Switching Test Circuit
Switching Waveforms

Gate Charge Test Circuit
Gate Charge Waveform

Unclamped Inductive Switching Test Circuit
Unclamped Inductive Switching Waveforms

■ ELECTRICAL CHARACTERISTICS


On-Region Characteristics




On-Resistance Variation vs. Drain Current and Gate Voltage




Capacitance Characteristics




Breakdown Voltage Variation vs. Temperature




Transfer Characteristics




Body Diode Forward Voltage Variation vs. Source Current and Temperature




Gate Charge Characteristics



On-Resistance Variation vs. Temperature



■ TO-220F-3L PACKAGE OUTLINE DIMENSIONS



■ TO-220-3L PACKAGE OUTLINE DIMENSIONS

