


 REVISIONS

 REV
 ECO
 DESCRIPTION
 DATE
 BY
 APPR

 A1
 RELEASE NEW DRAWING
 20/APR/22
 MILO
 TOMMY



NOTES: UNLESS OTHERWISE SPECIFIED

1. MATERIAL:

HOUSING: THERMOPLASTIC; BLACK SEAL: SILICONE RUBBER THREADED INSERT: STAINLESS STEEL

- 2. MODIFICATIONS: BACKSHELL RING ADAPTER (BRA); STANDARD DIA. WIRE SEAL; SEALED PANEL MOUNT
- 3. SPECIFICATIONS:
 - 3.1 OPERATING TEMPERATURE: -55°C TO +125°C.
 - 3.2 DIELECTRIC WITHSTANDING VOLTAGE: LESS THAN 2 MILLIAMPS CURRENT LEAKAGE @ 1500 VOLTS AC.
 - 3.3 INSULATION RESISTANCE: 1000 MEGOHM MIN @ 25°C.
 - 3.4 MOISTURE RESISTANCE:


IP68(IM OF WATER FOR A PERIOD OF 24 HOURS,MATED CONDITION):

IP69K (MATED CONDITION)

- 3.5 MATING CYCLE DURABILITY: 100 CYCLES
- 3.6 RoHS COMPLIANT
- 4. MATING PART: AHDP06-18-21S* (* = SEAL TYPE)
- 5. ALL DIMENSIONS ARE FOR REFERENCE USE ONLY.


6 CONTACT SIZE AND WIRE RANGE:

CONTACT	MIN. INSUL	MAX. INSUL	TYPICAL	CURRENT
SIZE	O.D.	O.D.	WIRE RANGE	RATING
20	1.02 mm (.040 in)	2.41 mm (.095 in)	16-22 AWG (1.5-0.35mm²)	7.5 AMPS



RECOMMENDED PANEL MOUNTING HOLE

RECOMMENDED PANEL THICKNESS:1.6 TO 4.7MM



		AUDE02-1	0-ZIFIN-DRA									
	QUANTITY	PART NUMBER			DESCRIPTION						ITEM	
MATERIALS LIST												
UNLESS OTHERWISE SPEC			DRAWN: MLO		DATE	1 Amabar			\overline{a}			
	1) All dimensions are in metric(m 2) Tolerances are as follows: 1 PL DEC ±0.30 Fractions ±:				20/APR/22	Amphenol						
	2 PL DEC ±0.15 3 PL DEC ±0.08	Angles ±1	CHECKED:	SULLEN	21/APR/22	Sine Systems - www.amphenol-sir				com	_	
	3) Note reference	ENGINEER:			44724 Morley Drive Clinton Township, MI 48036							
	MATERIAL SPECIFICA	TIONS:	APPROVAL:	TOMMY	22/APR/22			Clinton Township, IVII 46	130			
	WEIGH'	T: 53.7g	CUSTOMER:		•	21F	OS, RE	CEPT, PIN, PANELMA		OP SIZE	18,	
			SHOWN HEREON ARE THE PROPERTY OF THE AMPHENOL CORPORATION. NO RIGHTS OF REPRODUCTION ARE IMPLIED. ALL DIMENSIONS ARE SUBJECT TO MORAM			NORMAL SEAL, BRA						
	PROCESS SPECIFICA	B				C-	ÄHDP02-18-2	1PN-E	BRA	A1		
	NEXT ASS'Y:		MANUFACTUR	RING VARIATION	8.	SCALE: N	ONE	DURAMATE	SHEET	1 or	1	