



Rotary Joint Operating to 18 GHz 2.92mm Female 2.92mm Female Connectors

TECHNICAL DATA SHEET

PE1402

Configuration

Connector 1 Impedance 1 Connector 2 Impedance 2 Adapter Design Body Style Mount Method 2.92mm Female 50 Ohms 2.92mm Female 50 Ohms Standard Straight Bulkhead

Electrical Specifications (Values at 25°C, sea level)

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		18	GHz
VSWR			1.4:1	
Input Power		A	30	Watts
Peak Power			3	KWatts

Specifications by Frequency

Description	F1	F2	F3	F4	F5	Units
Range	DC to 6	6 to 12.4	12.4 to 18			GHz
VSWR	1.15:1	1.3:1	1.4:1			
VSWR Rotational Variance	0.01:1	0.02:1	0.03:1			
Insertion Loss	0.3	0.4	0.6			dB
Insertion Loss Rotational Variance	0.03	0.05	0.1			dB
Phase Rotational Variance	0.5	1	1.5			Degrees

Electrical Specification Notes: Average Power: 1 GHz @ 200W

Mechanical Specifications

	Description	Minimum	Typical	Maximum	Units
Speed			100		RPM

Temperature

Operating Range -40 to +70 deg C

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: Rotary Joint Operating to 18 GHz 2.92mm Female 2.92mm Female Connectors PE1402

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 Phone: (866) 727-8376 or (949) 261-1920 • Fax: (949) 261-7451

Sales@Pasternack.com • Techsupport@Pasternack.com





Rotary Joint Operating to 18 GHz 2.92mm Female 2.92mm Female Connectors

TECHNICAL DATA SHEET

PE1402

Size

 Length
 1.37 in [34.8 mm]

 Width
 1 in [25.4 mm]

 Weight
 0.062 lbs [28.12 g]

Connectors

Description	Connector 1	Connector 2	
Туре	2.92mm Female	2.92mm Female	
Inner Conductor Material and Plating	Beryllium Copper, Gold	Beryllium Copper, Gold	
Inner Conductor Plating Specification	4μ IN Minimum	4μ IN Minimum	
Outer Conductor Material and Plating	Passivated Stainless Steel	Passivated Stainless Steel	
Body Material and Plating	Passivated Stainless Steel	Passivated Stainless Steel	
Dielectric Type	PTFE	PTFE	

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: Rotary Joint Operating to 18 GHz 2.92mm Female 2.92mm Female Connectors PE1402

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451

Sales@Pasternack.com • Techsupport@Pasternack.com






Rotary Joint Operating to 18 GHz 2.92mm Female 2.92mm Female Connectors

TECHNICAL DATA SHEET

PE1402

Outline Drawing



Rotary Joint Operating to 18 GHz 2.92mm Female 2.92mm Female Connectors from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: Rotary Joint Operating to 18 GHz 2.92mm Female 2.92mm Female Connectors PE1402

URL: https://www.pasternack.com/rotary-joint-18-ghz-2.92mm-female-2.92mm-female-connectors-pe1402-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 Phone: (866) 727-8376 or (949) 261-1920 • Fax: (949) 261-7451