


Pressure sensor SPAN-P10R-G18M-PN-PN-L1

Part number: 8035544

FESTO



Data sheet

Feature	Value
Symbol	00995686
Certification	RCM compliance mark c UL us - Listed (OL)
CE marking (see declaration of conformity)	As per EU EMC directive As per EU RoHS directive
UKCA marking (see declaration of conformity)	To UK instructions for EMC To UK RoHS instructions
Certificate issuing authority	UL E322346
Note on materials	RoHS-compliant
Measured variable	Relative pressure
Method of measurement	Piezoresistive pressure sensor
Pressure measuring range initial value	0 MPa
Pressure measuring range initial value	0 bar
Pressure measuring range initial value	0 psi
Pressure measuring range end value	1 MPa
Pressure measuring range end value	10 bar
Pressure measuring range end value	145 psi
Max. overload pressure	15 bar
Overload pressure	1.5 MPa
Overload pressure	15 bar
Overload pressure	217.5 psi
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4] Inert gas
Information on operating and pilot media	Operation with oil lubrication possible
Temperature of medium	0 °C ... 50 °C
Ambient temperature	0 °C ... 50 °C
Accuracy in ± % FS	1.5 %FS
Repetition accuracy in ± %FS	0.3 %FS
Temperature co-efficient in ± %FS/K	0.05 %FS/K
Switching output	2 x PNP or 2 x NPN switchable
Switching function	Window comparator Threshold value comparator Auto difference monitoring
Switching element function	N/C contact/N/O contact switchable
Max. output current	100 mA
Short-circuit protection	yes
DC operating voltage range	15 V ... 30 V

Feature	Value
Reverse polarity protection	for all electrical connections
Electrical connection 1, connection type	Plug
Electrical connection 1, connection technology	Connection diagram L1J
Electrical connection 1, number of pins/wires	4
Electrical connection for input 1, connection pattern	00995428
Type of mounting	Front panel mounting With thread With wall/surface bracket
Mounting position	Any
Pneumatic connection	External thread G1/8 Internal thread M5
Product weight	46 g
Housing material	PA-reinforced
Materials in contact with the media	FPM High-alloy stainless steel
Display type	Illuminated LCD
Displayable unit(s)	MPa bar inH2O inHg kPa kgf/cm ² mbar mmHg psi
Setting options	Teach-in Via display and pushbuttons
Protection against tampering	PIN code
Setting range threshold value	0 % ... 100 %
Setting range hysteresis	0 % ... 90 %
Degree of protection	IP40
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Suitability for the production of Li-ion batteries	Metals with more than 1% copper, zinc or nickel by mass are excluded from use. Exceptions are nickel in steel, chemically nickel-plated surfaces, printed circuit boards, cables, electrical plug connectors and coils
Cleanroom class	Class 4 according to ISO 14644-1