

### 28 x 9 mm Miniature Speaker – 8 Ohm Part No:

SPKM.289.8.A

#### **Description:**

28 x 9mm Miniature Speaker - 8 Ohm 500mW RMS Compact design for integration in a wide range of products

#### **Features:**

8 Ohm Impedance Rated Input Power 500mW RMS Max Input Power 1W peak High Sensitivity Dimensions: 28 x 9 x 3.5 mm Connector: Wire Lead RoHS & Reach Compliant



1.	Introduction	3
2.	Specifications	4
3.	Speaker Measurement Conditions	6
4.	Speaker Characteristics	7
5.	Mechanical Drawing	8
6.	Packaging	9
	Changelog	10

Taoglas makes no warranties based on the accuracy or completeness of the contents of this document and reserves the right to make changes to specifications and product descriptions at any time without notice. Taoglas reserves all rights to this document and the information contained herein. Reproduction, use or disclosure to third parties without express permission is strictly prohibited.

Copyright © Taoglas Ltd





### 1. Introduction



Featuring a compact design, enabling ease of integration in a wide range of electronics products, including IoT devices, with high levels of long-term reliability and best in class performance Taoglas products are known for.

Our 28 x 9 mm Miniature Speaker offers frequency response of 100 Hz - 10 kHz and high sensitivity, with 8 Ohm impedance and power handling of 0.5W RMS and 1W peak. Proven performance in demanding applications where the accurate reproduction of voice communications is required. Taoglas added miniature speakers to our product portfolio to provide both reliable connectivity and high-quality audio solutions from one trusted company.

Please contact your regional Taoglas customer support team for more information or installation guidelines.

The table below shows a guide to help select the best speaker for your application based on size requirements:

Part Number	Dimensions
SPKM.10.8.A	Ø10 x 3.5 mm
SPKM.15.8.A	Ø15 x 3.7 mm
SPKM.17.8.A	Ø17 x 4.4 mm
SPKM.20.8.A	Ø20 x 4.3 mm
SPKM.23.8.A	Ø23 x 6 mm
SPKM.28.8.A	Ø28 x 5.1 mm
SPKM.2030.8.A	30 x 20 x 5.1 mm
SPKM.2413.8.A	24 x 13 x 8.7 mm
SPKM.289.8.A	28 x 9 x 3.8 mm
SPKM.50.8.A	Ø50 x 8.3 mm



# Specifications

	Electroacoustic
Sound Pressure Level	88 dB SPL (±3dB) @1000 Hz (0 dB SPL= 20 μPa) Measuring Condition: 0.5W (Sine wave) @ 0.1 m with baffle
Impedance	$8\Omega$ (±15%) @ 2 kHz with 1 V input signal and without baffle in place
Frequency Response	100 Hz – 10 kHz
Resonant Frequency	1000 Hz (±20 %) Typical frequency @ 1 V
Nominal Input Power	500 milliwatts
Maximum Input Power	1 Watt
Distortion	Less than 10% @ 1 kHz, with input levels up to 2 V RMS
	Mechanical
Height	3.5 mm
Length	28 mm
Width	9 mm
Weight	0.005 Kg
Connector	Wire leads - AWG#32 (UL1571)
Material	PEI diaphragm with Neodymium Magnet, (without enclosure)
	Environmental
Temperature Range	-40°C to 80°C
Humidity	Non-condensing up to 95% Relative Humidity @ up to 65°C




Reliability Testing			
High Temperature Test	High Temp	+80°C (±2°C)	
night remperature rest	Duration	96 Hours	
<b>T</b>	Low Temp	-40°C (±2°C)	
Low Temperature Test	Duration	96 Hours	
	High Temp	+75°C (±2°C)	
	Low Temp	-40°C (±2°C)	
Heat Shock Test	Changeover time	<30 Seconds	
	Duration	1 Hour	
	Cycle	100 cycles	
	Temp	+40°C (±2°C)	
Humidity Test	Relative humidity	90 - 95 %	
	Duration	96 Hours	
	Temp	-40°C to +75°C	
Temperature Cycle Test	Duration	45 minutes	
Temperature cycle rest	Temperature gradient	1°C to 3°C / minute	
	Cycle	25 cycles	
	Mounted with dummy set mass	10 g	
Drop Test	Height	1 m	
	Cycle	6 cycles	
Load Test	White noise (EIA filter) for 96 hours @ 0.5 W (2 V) input power		
LUAU TEST	White noise (EIA filter) for 1 minute @ 0.8 W (2.5 V) input power		

\* SPL (Sound Pressure Level) as specified did not deviate more than ±3 dB from initial value, with no significant damage after testing.




# 3. Speaker Mesurement Conditions




Standard Test Fixture Conditions			
Input Power	0.5W(2V)		
Mode	TSR		
Potentiometer Range	50dB		
Sweep Time	0.5 seconds		


### 3.2 Measurement Fixture Diagram








4.1 SPL



dBSPL vs. Frequency






	Name	Material	Finish	QTY
1	28x9X2.8mm Frame	PBT+Fe	Black+Zinc Plated—Blue White	1
2	12.8X3.8X1.2H 8Ω Voice coil	Cu	Natural	1
3	12.2x3.2x0.9mm Magnet	Nd-Fe-B	Zinc Plated	1
4	8.2x27.2x25 $\mu$ Diaphragm	PEN	Natural	1
5	Gasket	T=1mm(Fe)	Zinc Plated—Blue White	1
6	UL1571 32AWG Lead wire	PVC	Black	1
7	UL1571 32AWG Lead wire	PVC	Red	1

5.




## 6. Packaging

1 pcs SPKM.289.8.A per Blister Dimensions – 95 x 42 x 17mm 95mm



160 pcs SPKM.289.8.A per EPE Tray 6 Trays SPKM.289.8.A per Carton 7 pcs SPKM.289.8.A per Layer Board

960 pcs SPKM.289.8.A per Carton Dimensions – 560 x 450 x 330mm





### SPE-22-8-002 - SPKM.289.8.A

Revision: D		
Date:	18-11-2022	
Changes:	Mechanical Drawings Updated to Rev D02	
Changes Made by:	Carlos Gomes	

#### **Previous Revisions**

Revision: A			Revision: B	
Date:	18-02-2022	1	Date:	17-05-2022
Changes:	Initial release		Changes:	Sound Pressure Level Updated
Changes Made by:	Jack Conroy		Changes Made by:	Paul Doyle

Revision: C			
Date:	15-08-2022		
Changes:	Cover updated Introduction updated Specifications updated Reliability test updated		
Changes Made by:	Carlos Gomes		

Date:	17-05-2022
Changes:	Sound Pressure Level Updated
Changes Made by:	Paul Doyle



# www.taoglas.com