## SIEMENS

## Data sheet

## US2:17GUG92BL13



Non-reversing motor starter, Size 2 1/2, Three phase full voltage, Solidstate overload relay, OLR amp range 25-100A, 240V 50Hz / 277V 60Hz coil, Combination type, 60A fusible disconnect, 60A/600V fuse clip, Enclosure NEMA type 1, Indoor general purpose use, Standard width enclosure

Fi	a	ur	e	si	m	ii.	ar
	3	~	~	~.			

product brand name	Class 17			
design of the product	Non-reversing motor starter with fusible disconnect			
special product feature	ESP200 overload relay; Half-size controller			
General technical data				
weight [lb]	49 lb			
Height x Width x Depth [in]	24 × 20 × 8 in			
touch protection against electrical shock	NA for enclosed products			
installation altitude [ft] at height above sea level maximum	6560 ft			
ambient temperature [°F]				
<ul> <li>during storage</li> </ul>	-22 +149 °F			
<ul> <li>during operation</li> </ul>	-4 +104 °F			
ambient temperature				
<ul> <li>during storage</li> </ul>	-30 +65 °C			
<ul> <li>during operation</li> </ul>	-20 +40 °C			
country of origin	USA			
Horsepower ratings				
yielded mechanical performance [hp] for 3-phase AC motor				
• at 200/208 V rated value	0 hp			
• at 220/230 V rated value	0 hp			
• at 460/480 V rated value	0 hp			
• at 575/600 V rated value	30 hp			
Contactor				
size of contactor	Controller half size 2 1/2			
number of NO contacts for main contacts	3			
operating voltage for main current circuit at AC at 60 Hz maximum	600 V			
operational current at AC at 600 V rated value	60 A			
mechanical service life (switching cycles) of the main contacts typical	1000000			
Auxiliary contact				
number of NC contacts at contactor for auxiliary contacts	0			
number of NO contacts at contactor for auxiliary contacts	1			
number of total auxiliary contacts maximum	7			
contact rating of auxiliary contacts of contactor according to UL	10A@600VAC (A600), 5A@600VDC (P600)			
Coil				
type of voltage of the control supply voltage	AC			
control supply voltage				

	04014			
at AC at 50 Hz rated value	240 V			
at AC at 60 Hz rated value	277 V			
holding power at AC minimum	8.6 W			
apparent pick-up power of magnet coil at AC	218 VA			
apparent holding power of magnet coil at AC	25 VA			
operating range factor control supply voltage rated value of magnet coil	0.85 1.1			
percental drop-out voltage of magnet coil related to the input voltage	50 %			
ON-delay time	19 29 ms			
OFF-delay time	10 24 ms			
Overload relay				
product function				
<ul> <li>overload protection</li> </ul>	Yes			
<ul> <li>phase failure detection</li> </ul>	Yes			
<ul> <li>asymmetry detection</li> </ul>	Yes			
<ul> <li>ground fault detection</li> </ul>	Yes			
test function	Yes			
external reset	Yes			
reset function	Manual, automatic and remote			
trip class	CLASS 5 / 10 / 20 (factory set) / 30			
adjustable current response value current of the current- dependent overload release	25 100 A			
tripping time at phase-loss maximum	3 s			
relative repeat accuracy	1 %			
product feature protective coating on printed-circuit board	Yes			
number of NC contacts of auxiliary contacts of overload relay	1			
number of NO contacts of auxiliary contacts of overload relay	1			
operational current of auxiliary contacts of overload relay				
• at AC at 600 V	5 A			
• at DC at 250 V	1 A			
contact rating of auxiliary contacts of overload relay according to UL	5A@600VAC (B600), 1A@250VDC (R300)			
insulation voltage (Ui)				
<ul> <li>with single-phase operation at AC rated value</li> </ul>	600 V			
<ul> <li>with multi-phase operation at AC rated value</li> </ul>	300 V			
Disconnect Switch				
response value of switch disconnector	60A / 600V			
design of fuse holder	Class R fuse clips			
operating class of the fuse link	Class R fuse clips			
Enclosure				
	1			
degree of protection NEMA rating	1			
design of the housing	indoors, usable on a general basis			
Mounting/wiring				
mounting position	vertical			
fastening method	Surface mounting and installation			
type of electrical connection for supply voltage line-side	Box lug			
tightening torque [lbf·in] for supply	35 35 lbf·in			
type of connectable conductor cross-sections at line-side at AWG cables single or multi-stranded	1x (14 2 AWG)			
temperature of the conductor for supply maximum permissible	75 °C			
material of the conductor for supply	AL or CU			
type of electrical connection for load-side outgoing feeder	Box lug			
tightening torque [lbf·in] for load-side outgoing feeder	45 45 lbf·in			
type of connectable conductor cross-sections at AWG cables for load-side outgoing feeder single or multi- stranded	1x (14 2 AWG)			
temperature of the conductor for load-side outgoing feeder maximum permissible	75 °C			

material of the conductor for load-side outgoing feeder	AL or CU			
type of electrical connection of magnet coil	Screw-type terminals			
tightening torque [lbf·in] at magnet coil	5 12 lbf·in			
type of connectable conductor cross-sections of magnet coil at AWG cables single or multi-stranded	2x (16 12 AWG)			
temperature of the conductor at magnet coil maximum permissible	75 °C			
material of the conductor at magnet coil	CU			
type of electrical connection for auxiliary contacts	Screw-type terminals			
tightening torque [lbf·in] at contactor for auxiliary contacts	10 15 lbf·in			
type of connectable conductor cross-sections at contactor at AWG cables for auxiliary contacts single or multi- stranded	1x (12 AWG), 2x (16 14 AWG), 2x (18 16 AWG)			
temperature of the conductor at contactor for auxiliary contacts maximum permissible	75 °C			
material of the conductor at contactor for auxiliary contacts	CU			
type of electrical connection at overload relay for auxiliary contacts	Screw-type terminals			
tightening torque [lbf·in] at overload relay for auxiliary contacts	7 10 lbf·in			
type of connectable conductor cross-sections at overload relay at AWG cables for auxiliary contacts single or multi- stranded	2x (20 14 AWG)			
temperature of the conductor at overload relay for auxiliary contacts maximum permissible	75 °C			
material of the conductor at overload relay for auxiliary contacts	CU			
Short-circuit current rating				
design of the fuse link for short-circuit protection of the main circuit required	10kA@600V (Class H or K); 100kA@600V (Class R or J)			
certificate of suitability	NEMA ICS 2; UL 508; CSA 22.2, No.14			
Further information				
Industrial Controls - Product Overview (Catalogs, Brochures,) www.usa.siemens.com/iccatalog Industry Mall (Online ordering system) <u>https://mall.industry.siemens.com/mall/en/us/Catalog/product?mlfb=US2:17GUG92BL13</u> Service&Support (Manuals, Certificates, Characteristics, FAQs,)				
https://support.industry.siemens.com/cs/US/en/ps/US2:17GUG92BL13 Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros,) http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=US2:17GUG92BL13⟨=en				
Certificates/approvals https://support.industry.siemens.com/cs/US/en/ps/US2:17GUG92BL13/certificate				

last modified:

1/25/2022 🖸