24 V 35 W 1 Phase / PMC-24V035W1A



PMC

Highlights & Features

- Universal AC input range
- Power will not de-rate for the entire input voltage range
- Full corrosion resistant aluminium casing
- High MTBF > 700,000 hrs. as per Telcordia SR-332
- Safety approval according to IEC/UL 60950-1, IEC/EN/UL 62368-1
- Also available: IP20 and Front Face connectors

Safety Standards









CB Certified for worldwide use

Model Number: Unit Weight: Dimensions (L x W x H): 128 x 97 x 38 mm

PMC-24V035W1A□ 0.24 kg (0.53 lb) (5.04 x 3.82 x 1.50 inch)

General Description

Delta's PMC series of panel mount power supply offers a nominal output voltage of 24 V, a wide temperature range from -10°C to +70°C and a highly dependable minimum hold-up time. The state-of-the-art design is made to withstand harsh industrial environments. What makes the product stands out from the crowd is its lightweight full aluminum body design, which can withstand shock and vibration according to IEC 60068-2-6. The PMC series also offers overvoltage and overload protection. Using a wide input voltage range design, it is compatible worldwide. The input also includes DC operating voltage from 125-375 Vdc. Best of all, this excellent design and quality does not come with a big price tag.

Model Information

PMC Panel Mount Power Supply

Model Number	Input Voltage Range	Rated Output Voltage	Rated Output Current
PMC-24V035W1A□	85-264Vac (125-375 Vdc)	24 Vdc	1.46 A

Model Numbering

PM	C -	24V	035W	1	Α	
Panel Mount	Product Type C – Enclosed	Output Voltage	Output Power	Single Phase	No PFC	Connector Type A – Terminal Block J – IP20 Connector* L – Front Face*

*Options









24 V 35 W 1 Phase / PMC-24V035W1A

Specifications

Input Ratings / Characteristics

Nominal Input Voltage		100-240 Vac	
Input Voltage Range		85-264 Vac	
Nominal Input Frequency		50-60 Hz	
Input Frequency Range		47-63 Hz	
Nominal DC Input Voltage*		125-250 Vdc	
DC Input Voltage Range*		125-375 Vdc	
Input Current		< 0.75 A @ 115 Vac, < 0.50 A @ 230 Vac	
Efficiency at 100% Load		> 85% @ 115 Vac & 230 Vac	
Max Power Dissipation	0% load	< 0.95 W @ 115 Vac, < 1.70 W @ 230 Vac	
	100% load	< 6.15 W @ 115 Vac & 230 Vac	
Max Inrush Current (Cold Start)		< 30 A @ 115 Vac, < 60 A @ 230 Vac	
Leakage Current		< 1 mA @ 240 Vac	

^{*}Safety approval according to IEC/UL 60950-1 and IEC/EN/UL 62368-1.

Output Ratings / Characteristics**

Nominal Output Voltage	24 Vdc
Factory Set Point Tolerance	24 Vdc ± 2%
Output Voltage Adjustment Range	22-28 Vdc
Output Current	1.46 A (35 W max.)
Output Power	35 W
Line Regulation	< 0.5% (@ 85-264 Vac input, 100% load)
Load Regulation	< 1.0% (@ 85-264 Vac input, 0-100% load)
PARD*** (20 MHz)	< 150 mVpp
Rise Time	< 30 ms @ nominal input (100% load)
Start-up Time	< 2500 ms @ nominal input (100% load)
Hold-up Time	> 15 ms @ 115 Vac, > 80 ms @ 230 Vac (100% load)
Dynamic Response (Overshoot & Undershoot O/P Voltage)	± 5% @ 85-264 Vac input, 0-100% load (Slew Rate: 0.1 A/µs, 50% duty cycle @ 5 Hz to 100 Hz)
Start-up with Capacitive Loads	8,000 μF Max

^{**}For power de-rating from 50°C to 70°C, see power de-rating on page 3.



^{***}PARD is measured with an AC coupling mode, 5cm wires, and in parallel with 0.1 μ F ceramic capacitor & 47 μ F electrolytic capacitor.

24 V 35 W 1 Phase / PMC-24V035W1A

Mechanical

Case Chassis / Cover		Aluminium
Dimensions (L x W x H)		128 x 97 x 38 mm (5.04 x 3.82 x 1.50 inch)
Unit Weight		0.24 kg (0.53 lb)
Indicator		Green LED (DC OK)
Cooling System		Convection
Terminal	PMC-24V035W1A <u>A</u>	M3.5 x 5 Pins (Rated 300 V/15 A)
	PMC-24V035W1A <u>J</u>	M3.5 x 5 Pins (Rated 300 V/20 A)
	PMC-24V035W1A <u>L</u>	M3.5 x 5 Pins (Rated 300 V/20 A)
Wire		AWG 20-12
Noise (1 Meter from power supply)		Sound Pressure Level (SPL) < 40 dBA

Environment

Surrounding Air Temperature	Operating	-10°C to +70°C	
	Storage	-25°C to +85°C	
Power De-rating		> 50°C de-rate power by 2.5% / °C	
Operating Humidity		5 to 95% RH (Non-Condensing)	
Operating Altitude		0 to 3,000 Meters (9,840 ft.)	
Shock Test	Non-Operating	IEC 60068-2-27, 30G (300 m/S²) for a duration of 18 ms, 3 times per direction, 18 times in total	
Vibration Non-Opera		IEC 60068-2-6, 10 Hz to 150 Hz @ 50 m/S² (5G peak); 90 min per axis for all X, Y, Z direction	
Over Voltage Category		II	
Pollution Degree		2	

Protections

Overvoltage	< 32 V ±10%, SELV Output, Hiccup Mode, Non-Latching (Auto-Recovery)
Overload / Overcurrent	> 120% of rated load current, Hiccup Mode, Non-Latching (Auto-Recovery)
Over Temperature	< 75°C Surrounding Air Temperature @ 100% load, Non-Latching (Auto-Recovery)
Short Circuit	Hiccup Mode, Non-Latching (Auto-Recovery when the fault is removed)
Degree of Protection	IP20 (PMC-24V035W1A <u>J</u>)
Protection Against Shock	Class I with PE* connection

^{*}PE: Primary Earth

Reliability Data

	> 700,000 hrs. as per Telcordia SR-332 I/P: 115 Vac, O/P: 100% load, Ta: 25°C
Expected Cap Life Time	10 years (115 Vac & 230 Vac, 50% load @ 40°C)



24 V 35 W 1 Phase / PMC-24V035W1A

Safety Standards / Directives

Safety Entry Low Voltage		SELV (IEC 60950-1)
Electrical Safety	SIQ Bauart	EN 62368-1
	UL/cUL recognized	UL 60950-1 and CSA C22.2 No. 60950-1 (File No. E191395) UL 62368-1 and CSA C22.2 No. 62368-1 (File No. E191395)
	CB Scheme	IEC 60950-1, IEC 62368-1
	UKCA	BS EN 62368-1
CCC		GB/T9254, GB17625.1 and GB4943.1 仅适用于海拔 2000m 以下地区安全使用
CE		In conformance with EMC Directive 2014/30/EU and Low Voltage Directive 2014/35/EU
UKCA		In conformance with Electrical Equipment (Safety) Regulations 2016 No. 1011 and The Electromagnetic Compatibility Regulations 2016 No. 1091
Galvanic Isolation	Input to Output	3.0 KVac
	Input to Ground	1.5 KVac
	Output to Ground	0.5 KVac

EMC

Emissions (CE & RE)		Generic Standards: CISPR 32, EN/BS EN 55032, FCC Title 47: Class B, GB9254.1
Immunity		Generic Standards: EN/BS EN 55024
Electrostatic Discharge	IEC 61000-4-2	Level 4 Criteria A ¹⁾ Air Discharge: 15 kV Contact Discharge: 8 kV
Radiated Field	IEC 61000-4-3	Level 3 Criteria A ¹⁾ 80 MHz-1 GHz, 10 V/M with 1 kHz tone / 80% modulation
Electrical Fast Transient / Burst	IEC 61000-4-4	Level 3 Criteria A ¹⁾ 2 kV
Surge	IEC 61000-4-5	Level 3 Criteria A ¹⁾ Common Mode ²⁾ : 2 kV Differential Mode ³⁾ : 2 kV
Conducted	IEC 61000-4-6	Level 3 Criteria A ¹⁾ 150 kHz-80 MHz, 10 Vrms
Power Frequency Magnetic Fields	IEC 61000-4-8	Criteria A ¹⁾ 10 A/Meter
Voltage Dips and Interruptions	IEC 61000-4-11	100% dip; 1 cycle (20 ms); Self Recoverable
Low Energy Pulse Test (Ring Wave)	IEC 61000-4-12	Level 3 Criteria A ¹⁾ Common Mode ²⁾ : 2 kV Differential Mode ³⁾ : 1 kV
Harmonic Current Emission		IEC/EN/BS EN 61000-3-2, Class A
Voltage Fluctuation and Flicker		IEC/EN/BS EN 61000-3-3

¹⁾ Criteria A: Normal performance within the specification limits




²⁾ Asymmetrical: Common mode (Line to earth)


³⁾ Symmetrical: Differential mode (Line to line)

24 V 35 W 1 Phase / PMC-24V035W1A

Block Diagram



Device Description




- 1) Input & Output terminal block connector
- 2) DC voltage adjustment potentiometer
- 3) DC OK control LED (Green)




24 V 35 W 1 Phase / PMC-24V035W1A

Dimensions

L x W x H: 128 x 97 x 38 mm (5.04 x 3.82 x 1.50 inch) (PMC-24V035W1AA and PMC-24V035W1AJ)



L x W x H: 128 x 97 x 38 mm (5.04 x 3.82 x 1.50 inch) (PMC-24V035W1AL)





24 V 35 W 1 Phase / PMC-24V035W1A

Engineering Data

Output Load De-rating VS Surrounding Air Temperature





Fig. 1 De-rating for Vertical and Horizontal Mounting Orientation > 50°C de-rate power by 2.5% / °C

Note

- Power supply components may degrade, or be damaged, when the power supply is continuously used outside the shaded region, refer to the graph shown in Fig. 1.
- 2. If the output capacity is not reduced when surrounding air temperature exceeds its specification as defined on Page 3 under "Environment",, the device will run into Over Temperature Protection. When activated, the output voltage will go into bouncing mode and will recover when the surrounding air temperature is lowered or the load is reduced as far as necessary to keep the device in working condition.
- In order for the device to function in the manner intended, it is also necessary to keep a safety distance as recommended in the safety instructions while the device is in operation.
- Depending on the surrounding air temperature and output load delivered by the power supply, the device can be very hot!
- If the device has to be mounted in any other orientation, please contact info@deltapsu.com for more details.

Output Load De-rating VS Input Voltage




No output power de-rating across the entire input voltage range



24 V 35 W 1 Phase / PMC-24V035W1A


Assembly & Installation

- Mounting holes for power supply assembly onto the mounting surface.
 The power supply shall be mounted on minimum 2 mounting holes using M3 screw minimum 5mm (0.20 inch) length.
- B This surface belongs to customer's end system or panel where the power supply is mounted.
- © Connector



- Use flexible cable (stranded or solid) of AWG No. 20-12.
- The torque at the Connector shall not exceed 13 Kgf.cm (11.23 lb.in). The insulation stripping length should not exceed 0.275" or 7 mm.

Installation of Mounting Accessories



- I Only use M3 screw ≤ 6 mm (0.23 inch) through the base mounting holes. This is to keep a safety distance between the screw and internal components.
- Recommended mounting tightening torque: 4~8 Kgf.cm (3.47~6.94 lbf.in).

Safety Instructions


- To ensure sufficient convection cooling, always maintain a safety distance of ≥ 20 mm (0.79 inch) from all ventilated surfaces while the device is in operation.
- The device is not recommended to be placed on surface with low thermal conductivity, such as plastics, for example.
- Note that the enclosure of the device can become very hot depending on the ambient temperature and load of the power supply.
 Do not touch the device while it is in operation or immediately after power is turned OFF. Risk of burning!
- Do not touch the terminals while power is being supplied. Risk of electric shock.
- Prevent any foreign metal, particles or conductors from entering the device through the openings during installation. It may cause:
 Electric shock; Safety Hazard; Fire; Product failure
- The appliance is not to be used by persons (including children) with reduced physical, sensory or mental capabilities, or lack of experience and knowledge, unless they have been given supervision or instruction.
- Warning: When connecting the device, secure Earth connection before connecting L and N. When disconnecting the device, remove L and N connections before removing the Earth connection.
- The device is earthed and must be inaccessible.



24 V 35 W 1 Phase / PMC-24V035W1A

Functions

■ Graph illustrating the Start-up Time, Rise Time, and Hold-up Time



Start-up Time

The time required for the output voltage to reach 90% of its final steady state set value, after the input voltage is applied.

Rise Time


The time required for the output voltage to change from 10% to 90% of its final steady state set value.

Hold-up Time

Time between the collapse of the AC input voltage, and the output falling to 95% of its steady state set value.


Inrush Current

Inrush current is the peak, instantaneous, input current measured and, occurs when the input voltage is first applied. For AC input voltages, the maximum peak value of inrush current will occur during the first half cycle of the applied AC voltage. This peak value decreases exponentially during subsequent cycles of AC voltage.



Dynamic Response

The power supply output voltage will remains within ±5% of its steady state value, when subjected to a dynamic load from 0% to 100% of its rated current.






24 V 35 W 1 Phase / PMC-24V035W1A□

Overload & Overcurrent Protections (Auto-Recovery)

The power supply's Overload (OLP) and Overcurrent (OCP) Protections will be activated when output current (Io) exceeds its specification as defined on Page 3 under "Protections". In such occurrence, the output voltage (V_0) will start to droop and once the power supply has reached its maximum power limit, the protection is activated and the power supply will go into "Hiccup mode" (Auto-Recovery). The power supply will recover once the fault condition of the OLP and OCP is removed and Io is back within the specifications.




It is not recommended to prolong the duration of l_0 when it is less than OLP/OCP point, but greater than 100%, since it may cause damage to the PSU.

Short Circuit Protection (Auto-Recovery)

The power supply's output OLP/OCP function also provides protection against short circuits. When a short circuit is applied, the output current will operate in "Hiccup mode", as shown in the illustration in the OLP/OCP section on this page. The power supply will return to normal operation after the short circuit is removed.

Overvoltage Protection (Auto-Recovery)

The power supply's overvoltage circuit will be activated when its internal feedback circuit fails. The output voltage shall not exceed its specifications defined on Page 3 under "Protections".



Over Temperature Protection (Auto-Recovery)

As described in load de-rating section, the power supply also has Over Temperature Protection (OTP). In the event of a higher operating temperature at 100% load, the power supply will run into OTP when the operating temperature is beyond what is recommended in the de-rating graph. When activated, the output voltage will go into bouncing mode until the temperature drops to its normal operating temperature as recommended in the de-rating graph.



24 V 35 W 1 Phase / PMC-24V035W1A

Operating Mode

Redundant Operation

In order to ensure proper redundant operation for the power supply units (PSUs), the output voltage difference between the two units must be kept at 0.45~0.50 V for these 24V supplies. Follow simple steps given below to set them up for the redundant operation:

Step 1.

Measure output voltage of PSU 1 and PSU 2. If PSU 1 is the master unit, then V_0 of PSU 1 must be higher than PSU 2. In order to set the output voltage, individually connect each power supply to 50% of rated load at any line voltage from 85-264Vac, and set the PSU 1 and PSU 2 output voltage.

Step 2.

Connect the power supply units PSU 1 and PSU 2 to Vin 1 & Vin 2, respectively, of the DRR-20N (or 20A) module shown on the right of above diagram.




Fig. 3 Redundancy Operation Connection Diagram

Itage Vout from DRR module will be = Vo (output voltage of power supply) – Vdrop* (in DRR module).

*Vdrop will vary from 0.60V to 0.90V (Typical 0.65V) depending on the load current and surrounding air temperature.

■ Parallel Operation

The power supply units (PSUs) can also be used for parallel operation in order to increase the output power. The difference in output voltage between the two units must be kept to within 25mV of each other. This difference must be verified with the same output load connected independently to each unit.

Parameters such as EMI, inrush current, leakage current, PARD, start up time will be different from those on the datasheet, when two units are connected in parallel. The user will need to verify that any differences will still allow the two power supplies connected in parallel will work properly in their product/application.




Fig. 4 Parallel Operation Connection Diagram



24 V 35 W 1 Phase / PMC-24V035W1A□

Others

Attention

Delta provides all information in the datasheets on an "AS IS" basis and does not offer any kind of warranty through the information for using the product. In the event of any discrepancy between the information in the catalog and datasheets, the datasheets shall prevail (please refer to **www.DeltaPSU.com** for the latest datasheets information). Delta shall have no liability of indemnification for any claim or action arising from any error for the provided information in the datasheets. Customer shall take its responsibility for evaluation of using the product before placing an order with Delta.

Delta reserves the right to make changes to the information described in the datasheets without notice.

Manufacturer and Authorized Representatives Information

Manufacturer

<u>Thailand</u>
Delta Electronics (Thailand) PCL.
909 Pattana 1 Rd., Muang, Samutprakarn, 10280 Thailand

Authorized Representatives

<u>The Netherlands</u>
Delta Greentech (Netherlands) B.V.
Zandsteen 15, 2132 MZ Hoofddorp, The Netherlands

<u>Taiwan</u>
Delta Electronics, Inc.
3 Tungyuan Road, Chungli Industrial Zone, Taoyuan County
32063, Taiwan

<u>United Kingdom</u>
Delta Electronics Europe Limited
1 Redwood Court, Peel Park Campus,
East Kilbride, Glasgow, G74 5PF, United Kingdom



24 V 35 W 1 Phase / PMC-24V035W1A

Document Revision Record

Date	Item	Content Revised	Page Affected	Rev
14 Mar 16	1	Revises "Highlights & Features" @ bullet 3 rd by add altitude and correct typo from "-20°C to +50°C" to "-20°C to +45°C".	1	02
	2	Revises "General Description".	1	
	3	Revises model numbering for connector type.	1	
	4	Reduces "Input Current", from "< 2.50A @ 115Vac, < 1.75A @ 230Vac" to "< 2.20A @ 115Vac, < 1.2A @ 230Vac".	2	
	5	Corrects "Max Inrush Current (Cold Start)", from "< 45A @ 115Vac, < 60A @ 230Vac" to "< 60A @ 115Vac, < 120A @ 230Vac".	2	
	6	Increases margin for "Leakage Current", from "< 0.9mA @ 264Vac" to "<1mA @ 264Vac".	2	
	7	 Output Ratings / Characteristics: Add "**" and remark under the table for power de-rating information. PARD and Rise Time: Revises and adds more information to entire operation temp. 	2	
	8	Increase margin for "Start-up Time", from "< 600ms @ 240Vac (100% load)" to "< 800ms @ 240Vac (100% load)".	2	
	9	Dynamic Response (Overshoot & Undershoot O/P Voltage) adds duty cycle and frequency.	2	
	10	 Terminal and Wire: Add more model numbers. Vibration: Adds displacement value. Bump: Adds. Overvoltage: deletes SELV and move to "Safety Standard/Directives". Adds "Degree of Protection". 	3	
	11	- Adds "Safety Entry Low Voltage" Revises 'Galvanic Isolation".	4	
	12	Revises "Block Diagram".Revises 'Device Description" by add more suffix at model name.	6	
	13	Assembly & Installation: Add more model numbers at table of cable sizes.	8	
	14	Changes illustrate of "Dynamic Response".	10	
14 Dec 17	1	- Update CE to EMC Directive 2014/30/EU and Low Voltage Directive 2014/35/EU - Replace CISPR22, EN55022 to CISPR32, EN55032	4	03
8 Nov 18	1	Add attention 1 paragraph	13	04
	2	Change dynamic response graph and content	10	
		By Netkamol		
4 Jun 18	1	Change "Nemko" logo to "SIQ" logo. Safety standard / Directives change "Nemko Bauart" to "SIQ Bauart" By: Warat	1 4	05
06 Nov 20	1 2 3 4	 Update 62368-1 Revise dimension "D" to "H" Remove RoHS Update AWG size by thanatsorn 	1,2,4 1,3,6 4,13 8	06
11 Nov 20	1 2 3	 Update product image Updated General description Add connector option picture 	1 1 1	
18 Oct 21	1	Add UKCA Logo Add UKCA safety detail Add UKCA address Add BS EN after safety standard in EMC part By Warat	1 4 10 4	07



24 V 35 W 1 Phase / PMC-24V035W1A

Date	Item	Content Revised	Page Affected	Rev
22 Oct 21	1	- remove "EN 60950-1" in Highlights & Features & safety section - add Max Power Dissipation - update Load/Line Regulation - add Over Voltage Category - add SELV - add UKCA info in safety section - add "and Interruptions" in Voltage dips - add Harmonic Current Emission - add Voltage Fluctuation and Flicker - update Note of de-rating info - update dynamic info - update OCP/OLP description BY Tassanai	1, 4 2 2 3 4 4 4 4 7 9	07

