

Model V480 Omnidirectional Antenna

Key Features



Unity Gain Wide Bandwidth Omni



Compact size, pole mounting available




Heavy wall fiberglass radome




Flexible pigtail termination



| Electrical Specifications | V480 |
|------------------------------------|-----------------------------|
| Frequency Range, MHz | 470-490 |
| Polarization | Vertical |
| Gain, dBi | Unity |
| Pattern, Degrees | 360 |
| VSWR (50 Ohms) | 1.2:1 typical |
| 1.5:1 Bandwidth MHz | 20 minimum |
| 3 dB Beamwidth E/H Planes, degrees | 77/360 |
| Maximum Power, watts | 100* |
| Termination, feet (m), coax | N Female, 1 (.3), RG58 type |





| Mechanical Specifications | V480 |
|-----------------------------|------------------------|
| Overall Length, feet (m) | 24 (61) |
| Radome Material | Fiberglass |
| Radiator Material | Brass |
| Mast Diameter, inches, (cm) | 1.25-2.00 (3.2-5.1) |
| Mounting Hardware | Base to mast, supplied |
| Wind Surface Areas, feet | .14 (.013) |
| Wind Survival, mph (kph) | 125 (200) |
| Weight, pounds (kg) | 2.0 (.9) |