





COAXIAL TERMINATION SMA MALE 6 GHZ 30W

PAGE 1/2 ISSUE 07-11-19B SERIES TERMINATION PART NUMBER R404754000





All dimensions are in mm. Tolerances according ISO 2768 m-H



COMPONENTS	MATERIALS	PLATING (μm)
Body Center contact Outer contact Insulator	STAINLESS STEEL BERYLLIUM COPPER STAINLESS STEEL PTFE	PASSIVATED GOLD 0.5 OVER NICKEL PHOSPHORUS 2 PASSIVATED
Gasket Substrate Resistor	SILICONE RUBBER ALUMINIUM NITRIDE THICK FILM	
Others parts	ALUMINIUM	BLACK ANODIZATION





COAXIAL TERMINATION SMA MALE 6 GHZ 30W

PAGE 2/2	ISSUE 07-11-19B	SERIES TERMINATION	PART NUMBER R404754000
-----------------	-----------------	-----------------------	-------------------------------

ELECTRICAL CHARACTERISTICS

Frequency (GHz)	DC - 3	3 - 6
V.S.W.R (≤)	1.20	1.40

Operating Frequency Range	DC - 6	GHz
Impedance	50	Ω
DC Resistance	50	Ω ± 5%
Peak power at 25°C (1µs, 1‰)	2000	W
Average power at 25°C	30	W (Free Air Cooled)
		W (Conduction Cooled)
		W (Conduction Coole


MECHANICAL CHARACTERISTICS

Connectors	SMA	Male	MIL C39012
Weight	187,3200 g		

ENVIRONMENTAL CHARACTERISTICS

Operating temperature range	-55/+125	°C
Storage temperature range	-55/+125	°C

Power derating Versus temperature



SPECIFICATION

OTHER CHARACTERISTICS

MOUNTED WITH VERTICAL COOLING FINS AND NATURAL CONVECTION