





6GHZ 1W 10DB QMA ATTENUATOR

PAGE 1/2 ISSUE 21-11-16D SERIES PART NUMBER R411710124





All dimensions are in mm.



COMPONENTS	MATERIALS	PLATING (μm)
Body	BRASS	BBR
Male center contact Female center contact	BRASS BERYLLIUM COPPER	GOLD OVER COPPER GOLD OVER COPPER
Outer contact	BRONZE	BBR
Insulator	PTFE	
Gasket	-	
Substrate	ALUMINA	
Resistor	THICK FILM	
Others parts	-	-



6GHZ 1W 10DB QMA ATTENUATOR



PAGE 2/2	ISSUE 21-11-16D	SERIES	DADT NUMBER BAAA740404
PAGE Z/Z	13305 21-11-160	ATTENUATEUR	PART NUMBER R411710124

ELECTRICAL CHARACTERISTICS

Frequency (GHz)	DC - 2	2 - 6
V.S.W.R (≤)	1.20	1.30
Deviation(±dB)	0.5	0.5

DC - 6	GHz
50	Ω
10	dB
100	W
1	W (Free Air Cooled)
	W (Conduction Cooled)
	50 10


MECHANICAL CHARACTERISTICS

Connectors	QMA	Male Female	
Weight	6,2500 g		

ENVIRONMENTAL CHARACTERISTICS

Operating temperature range	-40/+85	°C
Storage temperature range	-40/+85	°C

Power derating Versus temperature



SPECIFICATION

OTHER CHARACTERISTICS