






N ATTENUATOR 6 DB 3 GHZ 50W

PAGE 1/2 ISSUE 10-03-16B SERIES PART NUMBER R417006110

SCALE 1:2







All dimensions are in mm.



| COMPONENTS                  | MATERIALS                           | PLATING (μm)                                    |  |
|-----------------------------|-------------------------------------|---|--|
| Body<br>Male center contact | STAINLESS STEEL<br>BERYLLIUM COPPER | PASSIVATED<br>GOLD 0.5 OVER NICKEL PHOSPHORUS 2 |  |
| Female center contact       | BERYLLIUM COPPER                    | GOLD 0.5 OVER NICKEL PHOSPHORUS 2               |  |
| Outer contact               | -                                   | -   |  |
| Insulator                   | PTFE                                |   |  |
| Gasket                      | SILICONE RUBBER                     |   |  |
| Substrate                   | ALUMINA                             |   |  |
| Resistor                    | THICK FILM                          |   |  |
| Others parts                | ALUMINIUM                           | BLACK PAINTING                                  |  |





N ATTENUATOR 6 DB 3 GHZ 50W

| PAGE <b>2/2</b> | ISSUE 10-03-16B | SERIES<br>ATTENUATOR | PART NUMBER <b>R417006110</b> |
|-----------------|-----------------|----------------------|-------------------------------|
|-----------------|-----------------|----------------------|-------------------------------|

## **ELECTRICAL CHARACTERISTICS**

| Frequency (GHz) | DC - 1 | 1 -2 | 2 -3 |
|-----------------|--------|------|------|
| V.S.W.R (≤)     | 1.10   | 1.25 | 1.35 |
| Deviation(±dB)  | 0.70   | 0.70 | 0.70 |

| Operating Frequency Range    | DC - 3 GHz | GHz                   |
|------------------------------|------------|-----------------------|
| Impedance                    | 50         | Ω                     |
| Nominal Attenuation          | 6          | dB                    |
| Peak power at 25°C (1µs, 1‰) | 5000       | W                     |
| Average power at 25°C        | 50         | W (Free Air Cooled)   |
|                              |            | W (Conduction Cooled) |


### MECHANICAL CHARACTERISTICS

| Connectors | N                 | Male Female | MIL C39012 |
|------------|-------------------|-------------|------------|
| Weight     | <b>431,8200</b> g |             |            |

## **ENVIRONMENTAL CHARACTERISTICS**

| Operating temperature range | -55 /+125 | °C |
|-----------------------------|-----------|----|
| Storage temperature range   | -55 /+125 | °C |

#### Power derating Versus temperature



## SPECIFICATION

# OTHER CHARACTERISTICS