The products in this catalog are not recommended for new design

EMC Components

Common mode filters High-speed differential signal line (USB2.0, LVDS, etc.) TCM-G series



FEATURES


TCM0605G type

- O Thin-film common mode filter based on the thin-film processing techniques and material technology cultivated from HDD head manufacturing.
- Has EMC suppression by achieving wide frequency range (cutoff frequency of 3GHz or higher) differential mode transmission while ensuring common mode impedance with virtually no affect on the high-speed differential transmission line signal.
- \bigcirc This is the compact 0605 size (0.65×0.50×0.30mm) type.
- Operating temperature range: -25 to +85°C

APPLICATION

- Noise countermeasure for high-speed differential interfaces (USB2.0, LVDS, MIPI, etc.) for mobile devices and general consumer products such as smart phones, tablets, digital cameras, and portable music players.
- O Application guides: Smart phones/tablets

PART NUMBER CONSTRUCTION



CHARACTERISTICS SPECIFICATION TABLE

Common mode impedance		DC resistance	Rated current	Rated voltage	Insulation resistance	Part No.
[at 100MHz]		[1 line]				
(Ω)	Tolerance	(Ω)	(A)max.	(V)max.	(MΩ)min.	
65	±20%	2.7±30%	0.1	10	10	TCM0605G-650-2P-T201
90	±20%	3.0±30%	0.1	10	10	TCM0605G-900-2P-T201

Measurement equipment

Measurement item	Product No.	Manufacturer
Common mode impedance	4291A	Keysight Technologies
DC resistance	4338A	Keysight Technologies
Insulation resistance	4339A	Keysight Technologies

* Equivalent measurement equipment may be used.




cmf_commercial_signal_tcm0605g_en

EMC Components


TCM0605G type

IMPEDANCE VS. FREQUENCY CHARACTERISTICS



Measurement equipment					
Product No.	Manufacturer				
E4991A	Keysight Technologies				
* Equivalent measurement equipment may be used.					

INSERTION LOSS VS. FREQUENCY CHARACTERISTICS



* Equivalent measurement equipment may be used.


A Please be sure to request delivery specifications that provide further details on the features and specifications of the products for proper and safe use. Please note that the contents may change without any prior notice due to reasons such as upgrading. (2/4)

*****<u>⊗</u>TDK*


EMC Components

TCM0605G type

SHAPE & DIMENSIONS





PACKAGING STYLE




Dimensions in mm

TAPE DIMENSIONS







Dimensions in mm

PACKAGE QUANTITY

Package quantity

10,000 pcs/reel

TEMPERATURE RANGE, INDIVIDUAL WEIGHT


	Operating temperature range	Storage temperature range*	Individual weight		
_	–25 to +85 °C	–25 to +85 °C	0.5 mg		
* T	* The storage temperature range is for after the assembly.				

RECOMMENDED LAND PATTERN




Dimensions in mm

CIRCUIT DIAGRAM



RECOMMENDED REFLOW PROFILE



A Please be sure to request delivery specifications that provide further details on the features and specifications of the products for proper and safe use. Please note that the contents may change without any prior notice due to reasons such as upgrading. (3/4)

EMC Components

⊗TDK

REMINDERS FOR USING THESE PRODUCTS

Before using these products, be sure to request the delivery specifications.

SAFETY REMINDERS

Please pay sufficient attention to the warnings for safe designing when using this products.

▲ REMINDERS ○ The storage period is within 6 months. Be sure to follow the storage conditions (temperature: 5 to 40°C, humidity: 20 to 70% RH or less). If the storage period elapses, the soldering of the terminal electrodes may deteriorate. O Do not use or store in locations where there are conditions such as gas corrosion (salt, acid, alkali, etc.). Before soldering, be sure to preheat components. The preheating temperature should be set so that the temperature difference between the solder temperature and chip temperature does not exceed 150°C. O Soldering corrections after mounting should be within the range of the conditions determined in the specifications. If overheated, a short circuit, performance deterioration, or lifespan shortening may occur. O When embedding a printed circuit board where a chip is mounted to a set, be sure that residual stress is not given to the chip due to the overall distortion of the printed circuit board and partial distortion such as at screw tightening portions. Self heating (temperature increase) occurs when the power is turned ON, so the tolerance should be sufficient for the set thermal design. Carefully lay out the coil for the circuit board design of the non-magnetic shield type. A malfunction may occur due to magnetic interference. ○ Use a wrist band to discharge static electricity in your body through the grounding wire. O Do not expose the products to magnets or magnetic fields. O Do not use for a purpose outside of the contents regulated in the delivery specifications. O The products listed on this catalog are intended for use in general electronic equipment (AV equipment, telecommunications equipment, home appliances, amusement equipment, computer equipment, personal equipment, office equipment, measurement equipment, industrial robots) under a normal operation and use condition. The products are not designed or warranted to meet the requirements of the applications listed below, whose performance and/or quality require a more stringent level of safety or reliability, or whose failure, malfunction or trouble could cause serious damage to society, person or property. If you intend to use the products in the applications listed below or if you have special requirements exceeding the range or conditions set forth in the each catalog, please contact us. (1) Aerospace/aviation equipment (8) Public information-processing equipment (2) Transportation equipment (cars, electric trains, ships, etc.) (9) Military equipment (3) Medical equipment (10) Electric heating apparatus, burning equipment (4) Power-generation control equipment (11) Disaster prevention/crime prevention equipment (12) Safety equipment (5) Atomic energy-related equipment (6) Seabed equipment (13) Other applications that are not considered general-purpose (7) Transportation control equipment applications When designing your equipment even for general-purpose applications, you are kindly requested to take into consideration securing protection circuit/device or providing backup circuits in your equipment.

Please be sure to request delivery specifications that provide further details on the features and specifications of the products for proper and safe use. (4/4)
Please note that the contents may change without any prior notice due to reasons such as upgrading.