SIEMENS

Data sheet 3RQ3055-2SM30



Output coupler Optocoupler 1 NO, Transistor, 24 V DC Output max. 30 V DC, 5 A short circuit-proof Spring-type terminal (push-in) Overall width 6.2 mm Thermal current 5A

product category product designation Coupling relays with semiconductor output (not plug-in) design of the product product type designation 3RQ3 General technical data display version LED yes product component • relay output • semi-conductor output consumed active power insulation voltage for overvoltage category III according to IEC 60664 with degree of pollution 3 rated value surge voltage resistance rated value successions sinusoidal half-wave 15g / 11 ms vibration resistance	
design of the product product type designation General technical data display version LED product component • relay output • semi-conductor output consumed active power insulation voltage for overvoltage category III according to IEC 60664 with degree of pollution 3 rated value surge voltage resistance rated value protection class IP shock resistance • acc. to IEC 60068-2-27 Output coupling link 3RQ3 Yes No Yes 0.3 W 50 V 50 V IP20 sinusoidal half-wave 15g / 11 ms	
product type designation General technical data display version LED product component • relay output • semi-conductor output consumed active power insulation voltage for overvoltage category III according to IEC 60664 with degree of pollution 3 rated value surge voltage resistance rated value protection class IP shock resistance • acc. to IEC 60068-2-27 sinusoidal half-wave 15g / 11 ms	
display version LED product component • relay output • semi-conductor output consumed active power insulation voltage for overvoltage category III according to IEC 60664 with degree of pollution 3 rated value surge voltage resistance rated value protection class IP shock resistance • acc. to IEC 60068-2-27 Yes No No So V So V 2.5 kV IP20 sinusoidal half-wave 15g / 11 ms	
display version LED product component • relay output • semi-conductor output consumed active power insulation voltage for overvoltage category III according to IEC 60664 with degree of pollution 3 rated value surge voltage resistance rated value protection class IP shock resistance • acc. to IEC 60068-2-27 Yes No Yes 50 V 50 V 150 V 1	
product component • relay output • semi-conductor output Consumed active power insulation voltage for overvoltage category III according to IEC 60664 with degree of pollution 3 rated value surge voltage resistance rated value protection class IP shock resistance • acc. to IEC 60068-2-27 No No 50 V 50 V 50 V IP20 IP20 shock resistance as in IP20 sinusoidal half-wave 15g / 11 ms	
 relay output semi-conductor output Yes consumed active power insulation voltage for overvoltage category III according to IEC 60664 with degree of pollution 3 rated value surge voltage resistance rated value protection class IP shock resistance acc. to IEC 60068-2-27 No Yes 50 V IP20 shock resistance acc. to IEC 60068-2-27 sinusoidal half-wave 15g / 11 ms 	
semi-conductor output Consumed active power insulation voltage for overvoltage category III according to IEC 60664 with degree of pollution 3 rated value surge voltage resistance rated value protection class IP shock resistance acc. to IEC 60068-2-27 yes 0.3 W 50 V 1920 1920 1920 shock resistance sinusoidal half-wave 15g / 11 ms	
consumed active power insulation voltage for overvoltage category III according to IEC 60664 with degree of pollution 3 rated value surge voltage resistance rated value protection class IP shock resistance • acc. to IEC 60068-2-27 sinusoidal half-wave 15g / 11 ms	
insulation voltage for overvoltage category III according to IEC 60664 with degree of pollution 3 rated value surge voltage resistance rated value protection class IP IP20 shock resistance • acc. to IEC 60068-2-27 sinusoidal half-wave 15g / 11 ms	
IEC 60664 with degree of pollution 3 rated value surge voltage resistance rated value protection class IP IP20 shock resistance • acc. to IEC 60068-2-27 sinusoidal half-wave 15g / 11 ms	
protection class IP shock resistance • acc. to IEC 60068-2-27 sinusoidal half-wave 15g / 11 ms	
shock resistance • acc. to IEC 60068-2-27 sinusoidal half-wave 15g / 11 ms	
• acc. to IEC 60068-2-27 sinusoidal half-wave 15g / 11 ms	
vibration resistance	
• acc. to IEC 60068-2-6 6 150 Hz: 2 g	
switching frequency 100 Hz	
thermal current 5 A	
reference code acc. to IEC 81346-2	
Control circuit/ Control	
control supply voltage at DC	
• rated value 11 30 V	
operating range factor control supply voltage rated value at DC	
• initial value 1	
• full-scale value 1	
switch ON delay time	
• at DC maximum 0.2 ms	
OFF delay time 0.3 ms	
product component plug-in socket No	
Auxiliary circuit	
type of switching contact NO contact	
number of NO contacts for auxiliary contacts 1	
Main aireuit	
Main circuit	

Inputs/ Outputs	
property of the output short-circuit proof	Yes
Outputs	
ampacity of the semiconductor output at DC	5 mA 5 A
Electromagnetic compatibility	
EMC emitted interference acc. to IEC 60947-1	ambience A (industrial sector)
EMC immunity acc. to IEC 60947-1	corresponds to degree of severity 3
conducted interference	,
• due to burst acc. to IEC 61000-4-4	2 kV
 due to conductor-earth surge acc. to IEC 61000-4-5 	2 kV
 due to conductor-conductor surge acc. to IEC 61000-4-5 	1 kV
field-based interference acc. to IEC 61000-4-3	10 V/m
electrostatic discharge acc. to IEC 61000-4-2	6 kV contact discharge / 8 kV air discharge
Display	
display version as status display by LED	LED green
Connections/ Terminals	
product function removable terminal	No
type of electrical connection for auxiliary and control circuit	spring-loaded terminals (push-in)
wire length	
at DC maximum	1 000 m
type of connectable conductor cross-sections	4 (0.05 0.05 0.00
• solid	1x (0.25 2.5 mm²)
finely stranded with core end processing	1x (0.25 1.5 mm²)
finely stranded without core end processing	1x (0.25 2.5 mm²)
at AWG cables solidat AWG cables stranded	1 x (20 14)
	1x (20 14)
connectable conductor cross-section solid	0.25 2.5 mm²
connectable conductor cross-section finely stranded with core end processing	0.25 1.5 mm ²
connectable conductor cross-section finely stranded without core end processing	0.25 2.5 mm ²
 AWG number as coded connectable conductor cross section solid 	20 14
 AWG number as coded connectable conductor cross section stranded 	20 14
Installation/ mounting/ dimensions	
mounting position	any
fastening method	snap-on mounting
height	93 mm
width	6.2 mm
depth	72.5 mm
required spacing	
with side-by-side mounting	
— forwards	0 mm
— backwards	0 mm
— upwards — downwards	0 mm 0 mm
— downwards — at the side	0 mm
for grounded parts	VIIIII
— forwards	0 mm
— lorwards — backwards	0 mm
— upwards	0 mm
— at the side	0 mm
— downwards	0 mm
• for live parts	
— forwards	0 mm
— backwards	0 mm

— upwards	0 mm		
— downwards	0 mm		
— at the side	0 mm		
Ambient conditions			
installation altitude at height above sea level maximum	2 000 m		
ambient temperature during operation	-25 +60 °C		
ambient temperature during storage	-40 +85 °C		
ambient temperature during transport	-40 +85 °C		
relative humidity during operation	10 95 %		
Certificates/ approvals			
General Product Approval		EMC	Declaration of Conformity











Miscellaneous

Declaration of Conformity

Marine / Shipping

other





Confirmation

Information- and Downloadcenter (Catalogs, Brochures,...)

https://www.siemens.com/ic10

Industry Mall (Online ordering system)

https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3RQ3055-2SM30

Cax online generator


http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RQ3055-2SM30


Service&Support (Manuals, Certificates, Characteristics, FAQs,...) https://support.industry.siemens.com/cs/ww/en/ps/3RQ3055-2SM30

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...) http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3RQ3055-2SM30&lang=en

Characteristic: Derating

https://support.industry.siemens.com/cs/ww/en/ps/3RQ3055-2SM30/manual





last modified: 10/24/2020 🖸