


Data Sheet

Description

SSC4S701 is a single channel low-side gate driver, and drives a power transistor such as an IGBT and a power MOSFET. The IC has the undervoltage lockout for power supply and the overcurrent protection. When these protections are activated, the IC outputs the fault signal whose width is adjustable by an external capacitor.

The IC is provided in the compact and low profile SOIC8 package.

Package SOIC8



Not to scale

Features

- Single Input and Output
- Fault Signal Output at Abnormal Condition
- Adjustable Fault Signal Output Time
- Protections
 Undervoltage Lockout for Power Supply
 Overcurrent Protection


Specifications

- Power Supply Voltage, V_{CC}: 24 V (Recommended Value is 15 V)
- OUT Pin Peak Source Current: -0.8 A
- OUT Pin Peak Sink Current: 1.75 A

Applications

- Inverter Air Conditioners
- Refrigerators
- Industrial Equipment
- Server, etc.

Typical Application



Contents

De	scription1	l
Co	ntents2	2
1.	Absolute Maximum Ratings3	3
2.	Recommended Operating Range3	3
3.	Electrical Characteristics	1
	Performance Curves64.1. Thermal Derating Curve	
5.	Block Diagram	1
6.	Pin Configuration Definitions	7
7.	Typical Application	3
8.	Physical Dimensions)
9.	Marking Diagram9)
1	Operational Description 16 10.1. Fault Signal Output 16 10.2. Startup Operation 16 10.3. Undervoltage Lockout for Power Supply 11 10.4. Overcurrent Protection 11	0
Im	portant Notes 12)

1. Absolute Maximum Ratings

Current polarities are defined as follows: current going into the IC (sinking) is positive current (+); current coming out of the IC (sourcing) is negative current (-).

Unless otherwise specified, $T_A = 25$ °C.

Parameter	Symbol	Conditions	Pins	Rating	Unit
CIN Pin Voltage	V_{CIN}		1 – 6	−0.3 to 7	V
CFO Pin Voltage	V_{CFO}		2-6	-0.3 to 7	V
FO Pin Voltage	V_{FO}		3 – 6	−0.3 to 7	V
FO Pin Current	I_{FO}		3 – 6	1.0	mA
IN Pin Voltage	V _{IN}		4 – 6	-0.3 to 7	V
VCC Pin Voltage	V_{CC}		5 – 6	-0.3 to 24	V
OUT Pin Voltage	V_{OUT}		7 – 6	$V_{NO} - 0.3$ to $V_{CC} + 0.3$	V
OUT Pin Peak Source Current	I _{OUT(SRC)}		7 – 6	-0.8	A
OUT Pin Peak Sink Current	$I_{\text{OUT(SNK)}}$		7 – 6	1.75	A
VNO Pin Voltage	V_{NO}		8 – 6	$-5 \text{ to } V_{CC} + 0.3$	V
Power Dissipation	P_D		_	0.78	W
Operating Ambient Temperature	T_{OP}			-40 to 100	°C
Storage Temperature	T_{STG}			-40 to 150	°C
Junction Temperature	T_{J}			150	°C

2. Recommended Operating Range

Current polarities are defined as follows: current going into the IC (sinking) is positive current (+); current coming out of the IC (sourcing) is negative current (-).

Unless otherwise specified, $T_A = 25$ °C.

Parameter	Symbol	Conditions	Min.	Max.	Unit
IN Pin Voltage	V_{IN}	$V_{CC} = 15 \text{ V}$	0	5	V
VCC Pin Voltage	V _{CC}		13.5	16.5	V
VNO Pin Voltage	V _{NO}	$V_{CC} = 15 \text{ V}$	-5	5	V

3. Electrical Characteristics

Current polarities are defined as follows: current going into the IC (sinking) is positive current (+); current coming out of the IC (sourcing) is negative current (-).

Unless otherwise specified, $T_A = 25$ °C, $V_{CC} = 15$ V and $V_{NO} = 0$ V.

Parameter	Symbol	Conditions	Pins	Min.	Typ.	Max.	Unit
Power Supply Operation							
Operation Start Voltage	V _{CC(ON)}	The FO pin increases low- to	5 – 6	11.20	11.90	12.70	V
Operation Stop Voltage	$V_{\text{CC(OFF)}}$	high- level, or decreases high- to low-level.	5 – 6		11.40		V
Operation Start Stop Hysteresis	$V_{\text{CC(HYS)}}$	$R_{FO} = 5 \text{ k}\Omega, V_S = 5 \text{ V}$	5 – 6		0.50		V
Circuit Current in Operation	$I_{\text{CC(ON)}}$	$V_{IN} = 0 V$	5 – 6		0.40	1.70	mA
Filtering Time	t_{VCC_UV}	V _{CC} decreases 15 V to 10 V.	5 – 6	_	10	_	μs
CIN Pin Operation							
CIN Trip Voltage	V _{CIN}	The FO pin increases low- to high- level, or decreases high- to low-level.	1 – 6	0.45	0.50	0.55	V
CIN Voltage Delay Time	t_{CIN_1}	See Figure 3-1.	1 – 6	_		500	ns
CIN Filtering Time	$t_{\rm CIN_2}$	The CIN pin maximum pulse width that the FO pin does not response. See Figure 3-1.	1 – 6	80	180	240	ns
CFO Pin Operation							
Fault Output Time	t_{WFOP}	$C_{CFO} = 1 \text{ nF}$	2 – 6	75	110	180	μs
CFO Threshold Voltage	V_{CFH}	The FO pin increases low- to high-level.	2 – 6	2.4	2.7	3.0	V
CFO Pin Source Current	I_{CFO}	$V_{CFO} = 0 V$	2 – 6	-40	-25	-15	μA
FO Pin Operation							
FO Pin High Level Output Voltage	V_{FOH}	$ \begin{array}{l} V_{CIN} = 0 \ \ V, \ R_{FO} = 5 \ \ k\Omega, \\ V_{S} = 5 \ V \end{array} \label{eq:cin} $	3 – 6	4.50	5.00		V
FO Pin Low Level Output Voltage	V_{FOL}	$V_{CIN} = 1 \text{ V}, I_{FO} = 1 \text{ mA}$	3 – 6	_	_	0.95	V
FO Pin Leakage Current	I_{FO}	$V_{CIN} = 0 \text{ V}, V_{FO} = 5 \text{ V}$	3 – 6	—		1.0	μA
IN Pin Operation							
High Level Input Threshold Voltage	V_{INH}	The OUT pin increases low-to high-level.	4 – 6	_	2.10	2.60	V
Low Level Input Threshold Voltage	V_{INL}	The OUT pin decreases high- to low-level.	4 – 6	_	1.30		V
Input Hysteresis Voltage	V_{INHYS}		4 – 6	0.35	0.80		V
Input Pull-down Current	$I_{\rm IN}$	$V_{IN} = 5 \text{ V}$	4 – 6	0.24	0.33	0.50	mA
OUT Pin Operation							
High Level Output Threshold Voltage	V_{OUTH}	$I_{OUT} = 0 \text{ mA}$	7 – 6	14.50	15.00	_	V
Low Level Output Threshold Voltage	V_{OUTL}	$I_{OUT} = 0 \text{ mA}$	7 – 6	_	0.00	0.10	V
Turn-on Delay Matching	$t_{\rm dLH}$	C _{OUT} = 1000 pF, see Figure 3-2	7 – 6	_	_	300	ns

SSC4S701

Parameter	Symbol	Conditions	Pins	Min.	Тур.	Max.	Unit
Turn-off Delay Matching	$t_{ m dHL}$	C _{OUT} = 1000 pF, see Figure 3-2	7 – 6	_	_	300	ns
Output Rise Time	$t_{\rm r}$	C _{OUT} = 1000 pF, see Figure 3-2	7 – 6	_	_	150	ns
Output Fall Time	t_{f}	C _{OUT} = 1000 pF, see Figure 3-2	7 – 6			75	ns
VNO Pin Operation							
VNO Pin Current 1	I_{VNO1}	$V_{NO} = -5 \text{ V}$	8 – 6	-7.0	-5.0	-3.0	mA
VNO Pin Current 2	I_{VNO2}	$V_{CC} = 24 \text{ V}, V_{NO} = 15 \text{ V}$	8 – 6		15	_	μΑ




Figure 3-1. CIN Voltage Delay Time and CIN Filtering Time




Figure 3-2. Input and Output Waveforms

4. Performance Curves

4.1. Thermal Derating Curve






Figure 4-1. Thermal Derating Curve

5. Block Diagram



6. Pin Configuration Definitions



Pin Number	Pin Name	Description
1	CIN	Input for overcurrent protection
2	CFO	Capacitor connection for setting a fault signal output time
3	FO	Fault signal output
4	IN	Signal input
5	VCC	Power supply input
6	GND	Ground
7	OUT	Gate drive signal output
8	VNO	Drive current return pin (For example, IGBT emitter is connected)

7. Typical Application

Figure 7-1 shows the PFC circuit example using the SSC4S701.






Figure 7-1. PFC Circuit Example Using SSC4S701

8. Physical Dimensions


• SOIC8 Package



• SOIC8 Land Pattern Example



9. Marking Diagram



10. Operational Description

All the characteristic values given in this section are typical values, unless they are specified as minimum or maximum. Current polarities are defined as follows: current going into the IC (sinking) is positive current (+); current coming out of the IC (sourcing) is negative current (-).

Figure 10-1 shows the SSC4S701 peripheral circuit and the meaning of the symbols used in Section 10.




Figure 10-1. SSC4S701 Peripheral Circuit

10.1. Fault Signal Output

When the undervoltage lockout for power supply or the overcurrent protection is activated, the FO pin outputs the fault signal that is low level. Then, the capacitor, C_{CFO} , connected to the CFO pin is charged by the CFO Pin Source Current, I_{CFO} . When a CFO pin voltage, V_{CFO} , increases to the CFO Threshold Voltage, V_{CFH} , C_{CFO} is discharged. If the fault condition is removed during the fault output time, t_{WFOP} , the FO pin becomes high level. Then, a OUT pin signal, V_{OUT} , operates according to an input signal, V_{IN} .

The fault output time, t_{WFOP} , is determined by the value of C_{CFO} . The approximate value of t_{WFOP} is calculated by the following equation.

$$t_{WFOP} = \frac{C_{CFO} \times V_{CFH}}{|I_{CFO}|},$$
 (1)

where:

 C_{CFO} is the CFO pin capacitor value, V_{CFH} is the CFO Threshold Voltage (= 2.7 V), and I_{CFO} is the CFO Pin Source Current (= -25 μ A).

The FO pin should be connected to an external power supply by the pull-up resister, R_{FO} . If the external power supply voltage is 5 V, R_{FO} is about 5 k Ω .

10.2. Startup Operation

Figure 10-2 and Figure 10-3 show the startup waveforms. The VCC pin voltage, V_{CC} , is added from an external power supply.

While V_{CC} increases to the internal circuit start voltage from 0 V (period A described in Figure 10-2 and Figure 10-3), the FO pin voltage becomes $V_F + V_{CC}$ (where V_F is a forward voltage of an internal protection diode). When the internal circuit operates, the FO pin becomes low level and outputs the fault signal. If V_{CC} is the Operation Start Voltage, $V_{CC(ON)}$, or more for the fault output time, t_{WFOP} , the IC discharges C_{CFO} , and turns the FO pin status into high (see Figure 10-2).

The approximate value of the fault output time, t_{WFOP} , is calculated by Equation (1) (see Section 10.1).

On the other hand, when V_{CC} is less than $V_{CC(ON)}$ for the fault output time, t_{WFOP} , the IC keeps to charge C_{CFO} until V_{CC} increases to $\geq V_{CC(ON)}$ (see Figure 10-3). When V_{CC} becomes $\geq V_{CC(ON)}$, the IC discharges C_{CFO} , and turns the FO pin status into high. Then, the OUT pin outputs the signals according to the IN pin signal after the next rising edge of an IN pin signal.




Figure 10-2. Startup Waveforms 1




Figure 10-3. Startup Waveforms 2

10.3. Undervoltage Lockout for Power Supply

The undervoltage lockout (UVLO) circuit for power supply has a filter circuit to prevent the malfunction caused by the rapid decrease of the power supply, which is caused by noise, etc. The Filtering Time, t_{VCC_UV} , is $10~\mu s$.

Figure 10-4 shows the UVLO operational waveforms. The UVLO is activated when all the following conditions are fulfilled.

- The VCC pin voltage, V_{CC}, decreases to the Operation Stop Voltage, V_{CC(OFF)}, or less after the IC operates.
- Then, V_{CC} remains less than the Operation Start Voltage, $V_{CC(ON)}$ for t_{VCC_UV} .

While the UVLO is activated, the IC turns the FO pin status into low, and stops the output of the OUT pin signal. The subsequent operations are explained in Section 10.1.




Figure 10-4. Undervoltage Lockout for Power Supply Operational Waveforms

10.4. Overcurrent Protection

The CIN pin is the input of overcurrent signals. When the CIN pin detects the voltage of $\geq\!V_{CIN}$ for $\geq t_{CIN_2}$, the overcurrent protection is activated after t_{CIN_1} . Where: V_{CIN} is the CIN Trip Voltage of 0.50 V, t_{CIN_2} is the CIN Filtering Time of 180 ns, and t_{CIN_1} is the CIN Voltage Delay Time of 500 ns (max.).

While the overcurrent protection is activated, the IC turns the FO pin status into low, and stops the output of the OUT pin signal. When the CIN pin voltage decreases to <V_{CIN} for the fault output time, t_{WFOP} , from overcurrent protection activation, the IC discharges C_{CFO} ,

and turns the FO pin status into high (see Figure 10-5). The approximate value of t_{WFOP} is calculated by Equation (1) (see Section 10.1).

On the other hand, when the CIN pin voltage is more than V_{CIN} for t_{WFOP} , the IC keeps to charge C_{CFO} until the CIN pin voltage decreases to $<\!V_{\text{CIN}}$ (see Figure 10-6). When the CIN pin voltage becomes $<\!V_{\text{CIN}}$, the IC discharges C_{CFO} , and turns the FO pin status into high. Then, the OUT pin outputs the signals according to the IN pin signal after the next rising edge of an IN pin signal.




Figure 10-5. Overcurrent Protection Operational Waveforms 1




Figure 10-6. Overcurrent Protection Operational Waveforms 2

Important Notes

- All data, illustrations, graphs, tables and any other information included in this document (the "Information") as to Sanken's products listed herein (the "Sanken Products") are current as of the date this document is issued. The Information is subject to any change without notice due to improvement of the Sanken Products, etc. Please make sure to confirm with a Sanken sales representative that the contents set forth in this document reflect the latest revisions before use.
- The Sanken Products are intended for use as components of general purpose electronic equipment or apparatus (such as home appliances, office equipment, telecommunication equipment, measuring equipment, etc.). Prior to use of the Sanken Products, please put your signature, or affix your name and seal, on the specification documents of the Sanken Products and return them to Sanken. When considering use of the Sanken Products for any applications that require higher reliability (such as transportation equipment and its control systems, traffic signal control systems or equipment, disaster/crime alarm systems, various safety devices, etc.), you must contact a Sanken sales representative to discuss the suitability of such use and put your signature, or affix your name and seal, on the specification documents of the Sanken Products and return them to Sanken, prior to the use of the Sanken Products. The Sanken Products are not intended for use in any applications that require extremely high reliability such as: aerospace equipment; nuclear power control systems; and medical equipment or systems, whose failure or malfunction may result in death or serious injury to people, i.e., medical devices in Class III or a higher class as defined by relevant laws of Japan (collectively, the "Specific Applications"). Sanken assumes no liability or responsibility whatsoever for any and all damages and losses that may be suffered by you, users or any third party, resulting from the use of the Sanken Products in the Specific Applications or in manner not in compliance with the instructions set forth herein.
- In the event of using the Sanken Products by either (i) combining other products or materials or both therewith or (ii) physically, chemically or otherwise processing or treating or both the same, you must duly consider all possible risks that may result from all such uses in advance and proceed therewith at your own responsibility.
- Although Sanken is making efforts to enhance the quality and reliability of its products, it is impossible to completely avoid the occurrence of any failure or defect or both in semiconductor products at a certain rate. You must take, at your own responsibility, preventative measures including using a sufficient safety design and confirming safety of any equipment or systems in/for which the Sanken Products are used, upon due consideration of a failure occurrence rate and derating, etc., in order not to cause any human injury or death, fire accident or social harm which may result from any failure or malfunction of the Sanken Products. Please refer to the relevant specification documents and Sanken's official website in relation to derating.
- No anti-radioactive ray design has been adopted for the Sanken Products.
- The circuit constant, operation examples, circuit examples, pattern layout examples, design examples, recommended examples, all
 information and evaluation results based thereon, etc., described in this document are presented for the sole purpose of reference of
 use of the Sanken Products.
- Sanken assumes no responsibility whatsoever for any and all damages and losses that may be suffered by you, users or any third party, or any possible infringement of any and all property rights including intellectual property rights and any other rights of you, users or any third party, resulting from the Information.
- No information in this document can be transcribed or copied or both without Sanken's prior written consent.
- Regarding the Information, no license, express, implied or otherwise, is granted hereby under any intellectual property rights and any other rights of Sanken.
- Unless otherwise agreed in writing between Sanken and you, Sanken makes no warranty of any kind, whether express or implied, including, without limitation, any warranty (i) as to the quality or performance of the Sanken Products (such as implied warranty of merchantability, and implied warranty of fitness for a particular purpose or special environment), (ii) that any Sanken Product is delivered free of claims of third parties by way of infringement or the like, (iii) that may arise from course of performance, course of dealing or usage of trade, and (iv) as to the Information (including its accuracy, usefulness, and reliability).
- In the event of using the Sanken Products, you must use the same after carefully examining all applicable environmental laws and regulations that regulate the inclusion or use or both of any particular controlled substances, including, but not limited to, the EU RoHS Directive, so as to be in strict compliance with such applicable laws and regulations.
- You must not use the Sanken Products or the Information for the purpose of any military applications or use, including but not limited to the development of weapons of mass destruction. In the event of exporting the Sanken Products or the Information, or providing them for non-residents, you must comply with all applicable export control laws and regulations in each country including the U.S. Export Administration Regulations (EAR) and the Foreign Exchange and Foreign Trade Act of Japan, and follow the procedures required by such applicable laws and regulations.
- Sanken assumes no responsibility for any troubles, which may occur during the transportation of the Sanken Products including the falling thereof, out of Sanken's distribution network.
- Although Sanken has prepared this document with its due care to pursue the accuracy thereof, Sanken does not warrant that it is
 error free and Sanken assumes no liability whatsoever for any and all damages and losses which may be suffered by you resulting
 from any possible errors or omissions in connection with the Information.
- Please refer to our official website in relation to general instructions and directions for using the Sanken Products, and refer to the relevant specification documents in relation to particular precautions when using the Sanken Products.
- All rights and title in and to any specific trademark or tradename belong to Sanken and such original right holder(s).

DSGN-CEZ-16003