SIEMENS

Data sheet

US2:83DUC950F



Duplex starter w/o alternator, Size 1, Three phase full voltage, Solid-state overload relay, OLR amp range 3-12A, 110V 50Hz / 120V 60Hz coil, Non-combination type, Enclosure NEMA type 12, Dust/drip proof for indoors

Fi	g	ur	e	si	m	ilar	
	-						

product brand name	Class 83		
design of the product	Duplex controller without alternator		
special product feature	ESP200 overload relay		
General technical data			
weight [lb]	40 lb		
Height x Width x Depth [in]	20 × 16 × 6 in		
touch protection against electrical shock	NA for enclosed products		
installation altitude [ft] at height above sea level maximum	6560 ft		
ambient temperature [°F]			
 during storage 	-22 +149 °F		
 during operation 	-4 +104 °F		
ambient temperature			
 during storage 	-30 +65 °C		
during operation	-20 +40 °C		
country of origin	USA		
Horsepower ratings			
yielded mechanical performance [hp] for 3-phase AC motor			
• at 200/208 V rated value	2 hp		
• at 220/230 V rated value	2 hp		
• at 460/480 V rated value	5 hp		
• at 575/600 V rated value	5 hp		
Contactor			
size of contactor	NEMA controller size 1		
number of NO contacts for main contacts	3		
operating voltage for main current circuit at AC at 60 Hz maximum	600 V		
operational current at AC at 600 V rated value	27 A		
mechanical service life (switching cycles) of the main contacts typical	1000000		
Auxiliary contact			
number of NC contacts at contactor for auxiliary contacts	0		
number of NO contacts at contactor for auxiliary contacts	1		
number of total auxiliary contacts maximum	8		
contact rating of auxiliary contacts of contactor according to UL	10A@600VAC (A600), 5A@600VDC (P600)		
Coil			
type of voltage of the control supply voltage	AC		
control supply voltage			


• at DC rated value 0 0 V • at AC at 50 Hz rated value 110 110 V • at AC at 60 Hz rated value 120 120 V holding power at AC minimum 8.6 W	
• at AC at 60 Hz rated value 120 120 V	
holding power at AC minimum 8.6 W	
apparent pick-up power of magnet coil at AC 218 VA	
apparent holding power of magnet coil at AC 25 VA	
operating range factor control supply voltage rated value of magnet coil 0.85 1.1	
percental drop-out voltage of magnet coil related to the 50 % input voltage	
ON-delay time 19 29 ms	
OFF-delay time 10 24 ms	
Overload relay	
product function	
overload protection Yes	
phase failure detection Yes	
asymmetry detection Yes	
ground fault detection Yes	
• test function Yes	
external reset Yes	
reset function Manual, automatic and remote	
adjustable current response value current of the current- dependent overload release 3 12 A	
tripping time at phase-loss maximum 3 s	
relative repeat accuracy 1 %	
product feature protective coating on printed-circuit board Yes	
number of NC contacts of auxiliary contacts of overload 1 relay	
number of NO contacts of auxiliary contacts of overload 1 relay	
operational current of auxiliary contacts of overload relay	
• at AC at 600 V 5 A	
• at DC at 250 V 1 A	
contact rating of auxiliary contacts of overload relay according to UL 5A@600VAC (B600), 1A@250VDC (R300)	
insulation voltage (Ui)	
with single-phase operation at AC rated value 600 V	
with multi-phase operation at AC rated value 300 V	
Enclosure	
degree of protection NEMA rating of the enclosure NEMA 12 enclosure	
design of the housing dute choised dute the design of the housing dute choised dute dute the design of the housing dute choised dute dute the design of the housing dute choised dute dute dute dute dute dute dute du	
Mounting/wiring	
mounting position Vertical	
fastening method Surface mounting and installation	
type of electrical connection for supply voltage line-side Screw-type terminals	
tightening torque [lbf-in] for supply 35 35 lbf-in	
type of connectable conductor cross-sections at line-side at AWG cables single or multi-stranded 1x (14 2 AWG)	
temperature of the conductor for supply maximum 75 °C permissible	
material of the conductor for supply AL or CU	
type of electrical connection for load-side outgoing feeder Screw-type terminals	
tightening torque [lbf·in] for load-side outgoing feeder 35 35 lbf·in	
type of connectable conductor cross-sections at AWG cables for load-side outgoing feeder single or multi- stranded 1x (14 2 AWG)	
temperature of the conductor for load-side outgoing feeder 75 °C maximum permissible	
material of the conductor for load-side outgoing feeder AL or CU	
type of electrical connection of magnet coil Screw-type terminals	
tightening torque [lbf-in] at magnet coil 5 12 lbf-in	
type of connectable conductor cross-sections of magnet coil at AWG cables single or multi-stranded 2x (16 12 AWG)	


	-				
temperature of the conductor at magnet coil maximum permissible	75 °C				
material of the conductor at magnet coil	CU				
type of electrical connection at contactor for auxiliary contacts	Screw-type terminals				
tightening torque [lbf·in] at contactor for auxiliary contacts	10 15 lbf·in				
type of connectable conductor cross-sections at contactor at AWG cables for auxiliary contacts single or multi- stranded	1x (12 AWG), 2x (16 14 AWG), 2x (18 16 AWG)				
temperature of the conductor at contactor for auxiliary contacts maximum permissible	75 °C				
material of the conductor at contactor for auxiliary contacts	CU				
type of electrical connection at overload relay for auxiliary contacts	Screw-type terminals				
tightening torque [lbf·in] at overload relay for auxiliary contacts	7 10 lbf·in				
type of connectable conductor cross-sections at overload relay at AWG cables for auxiliary contacts single or multi- stranded	2x (20 14 AWG)				
temperature of the conductor at overload relay for auxiliary contacts maximum permissible	75 °C				
material of the conductor at overload relay for auxiliary contacts	CU				
Short-circuit current rating					
design of the fuse link for short-circuit protection of the main circuit required	10kA@600V (Class H or K); 100kA@600V (Class R or J)				
design of the short-circuit trip	Thermal magnetic circuit breaker				
breaking capacity maximum short-circuit current (Icu)					
• at 240 V	14 kA				
• at 480 V	10 kA				
• at 600 V	10 kA				
certificate of suitability	NEMA ICS 2; UL 508; CSA 22.2, No.14				
Further information					
Industrial Controls - Product Overview (Catalogs, Brochures,)					
www.usa.siemens.com/iccatalog					
Industry Mall (Online ordering system) https://mall.industry.siemens.com/mall/en/us/Catalog/product?mlfb=US2:83DUC950F					
Service&Support (Manuals, Certificates, Characteristics, FAQs,)					
https://support.industry.siemens.com/cs/US/en/ps/US2:83DL					
Image database (product images 2D dimension drawings 3D models, device circuit diagrams, EPI AN macros					

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...) http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=US2:83DUC950F&lang=en

Certificates/approvals

https://support.industry.siemens.com/cs/US/en/ps/US2:83DUC950F/certificate





last modified:

1/25/2022 🖸