8501XMO40V02

NEMA Control Relay, Type X, master, 10A resistive at 600VAC, 4 normally open contacts, 110/120VAC 50/60Hz coil





Main	
Range	8501X
Relay Type	Master
Product	Relay
Current Rating	20 A AC
Contact Configuration	4 NO 4 master contact cartridges
Number of Poles	4P
Coil Voltage	110 V AC 50 Hz 120 V AC 60 Hz
Voltage Rating	600 V AC
Mounting Type	Panel
Operating Temperature	-40160 °F (-4071 °C)
Electrical Connection	Screw clamp terminals
Certifications	CE UL Listed CSA

15 ms - pick-up 16 ms - drop-out

3.5 in (88.90 mm)

2.23 in (56.64 mm)

3.95 in (100.33 mm)

Ordering and shipping details

Category	21158-8501 XO (AC)	
Discount Schedule	CP2	
GTIN	785901743446	
Nbr. of units in pkg.	1	
Package weight(Lbs)	33.62 oz (952.998 g)	
Returnability	Yes	
Country of origin	MX	

Operating Time

Height

Width

Depth

Packing Units

Unit Type of Package 1	PCE	
Package 1 Height	8.89 in (22.581 cm)	
Package 1 width	3.50 in (8.89 cm)	
Package 1 Length	22.58 in (57.355 cm)	
Unit Type of Package 2	PAL	
Number of Units in Package 2	360	
Package 2 Weight	782.00 lb(US) (354.709 kg)	
Package 2 Height	40.00 in (101.6 cm)	
Package 2 width	40.00 in (101.6 cm)	
Package 2 Length	48.00 in (121.92 cm)	

Offer Sustainability

Sustainable offer status	Green Premium product	
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov	
REACh Regulation	☑ REACh Declaration	
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration	
Mercury free	Yes	
RoHS exemption information	₫Yes	
China RoHS Regulation	China RoHS Declaration	
Environmental Disclosure	Product Environmental Profile	
Circularity Profile	☑ End Of Life Information	

Contractual warranty

	,
Warranty	18 months