፲ ፲ ፲ ፲ ፲ ፲ ፲ ፲ ፲ ፲ ፲ ፲ ፲ ፲ ፲ ፲ ፲ ፲ ፲				0	œ		
Z' ØS							
				LAYOUT SHO	WN AS EXAMPLE		
	Keying Shown as example						
CHARACTERISTICS	Connector dimensi	on					
Standard : Based on MIL-DTL-38999 Series III	Dim No	minal 4 Max					
-Shell Material : Composite		5 Max			ble for any non-conformity or o		
-Shell Plating : Nickel	VV THREAD M1	8x1-6g			oducts which does not comply veither of the Parties or by a th		
-Insulator : Thermoplastic					mmendation, technical notice.		
-Contacts : Copper Alloy -Seals & Grommet : Silicon Elastomer							
-Contact Plating : Gold over copper Alloy 0.8µm minimum						n & Control List t Listed	
-Durability : 500 Mating cycles		ſ					
-Delivered without Souriau contacts				PN: 8D	513M26PNL		
-Temperature Range65°C to +200°C							
-Salt Spray : 2000 hours		A	18-10-2016	First Release			
-Mass : 16.2 g ± 10%		ISS		Latest modification - by Date:		STOMER DRAWING	MOD N°
			TITLE		Composite Plug 8D se	eries	
BASIC SERIES: 8D 5 - 13 M 2	26 P N L	SC/	CALE		al linear Jances:	NPRDS / PROJECT	
SHELL TYPE : Plug with RFI Shielding	De	elivered W/O Contacts N	NA			859	
CONTACT TYPE : Standard Crimp Contact		ORIENTATION : N	DURIAU			This document is the proper SOURIAU	
SHELL SIZE : 13	CONTACT TY	/PE : PIN(500 Matings)	JURIAU	WWW.SOUR		it must not be reproduced communicated without permi	
PLATING : M = Nickel			RMAT		RIAU DRG N°		SHEET
			43		13M26PNL-C		1/2
					A CONTRACTOR OF A CONTRACT OF		

		G	г П	m		0
		Contact Layout				
4		26				
		2#12 6#22D 13-26]			
ى	Ctc A B C D E F 1 2	X Y 0 3.47 2.47 4.34 2.47 -4.34 0 -3.47 -2.47 -4.34 -2.47 4.34 3.25 0 -3.25 0				
						SOURIAU shall not be liable for an due to a use of the Products wh the Specifications issued by either or
2						(professional recommendat Countr FR
					A 18-10-20 ISS DATE Designed By:	PN: 8D513N 116 First Release Latest modification - by Date:
					TITLE SCALE	General linear Tolerances:
→					SOURIA	
		<u></u>	F	r (FORMAT A3	SOURIAU 8D513M2
	Н	l G		E	D	C

