BASIC SERIES: 8D 5 - 15 J 15 P A L Composite Plug 8D series BASIC SERIES: 8D 5 - 15 J 15 P A L Series SCALE M Image: Composite Plug 8D series 859 CONTACT TYPE: Plug with RFI Shielding Image: Contact ORIENTATION : A SOURIAU SOURIAU SOURIAU This document is the property of SOURIAU.COM SOURIAU Image: Contact WWW.SOURIAU.COM Image: Contact Without permission PLATING J = ONTACT TYPE : PIN(500 Matings) CONTACT TYPE : PIN(500 Matings) FORMAT SOURIAU DRG N° SHEET		п	m	t	D	0			A	
LANDUT SHOWN AS EXAMPLE CHARACTERISTICS Shell Mandrid : Based on Millor 13:899 Series III Shell Mandrid : Based on Millor 13:899 Series III Shell Mandrid : Based on Millor 13:899 Series III Shell Mandrid : Based on Millor 13:899 Series III Shell Mandrid : Based on Millor 13:899 Series III Shell Mandrid : Based on Millor 13:899 Shell Mandrid : Based on Millor 13:899 Shell Similar Collance (Mathrid) Cellance (
CHARACTERISTICS -Standard: Based on MIL-DT-38999 Series III -Shell Material : Composite -Shell Material : Shell State -Shell TYPE	s					LAY	OUT SHOWN AS EXAMP	LE		
Standard : Based on ML-DTL-38999 Series III Dimetud Mindows Shell Material :: Composite Shell Material :: Composite Shell Material : Composite Source Coper Alloy : Source Coper Alloy 0.8µm minimum Source Coper Alloy 0.8µm minimum : Composite - Ourability : Source Coper Alloy 0.8µm minimum - Ourability : Source Coper Alloy 0.8µm minimum - Durability		Keying Shown	as example							
Shell Material Composite Shell Material Composite Shell Material Composite Shell Material Composite Shell Plating Clive drab Cadmium Insulator Thermoplastic Contacts Composite Source composite Silcon Elastomer Contact Plating Sold over copper Alloy 0.8µm minimum Ourability Stop of the Parties on a products which does not comply with the Specifications issued by either of the Parties or buy a third party (professional recommendation, technical notice). Ourability Stop of the Parties on a product which does not comply with the Specifications issued by either of the Parties or buy a third party (professional recommendation, technical notice). Ourability Stop of the Parties or buy a third party (professional recommendation, technical notice). Ourability Stop of the Parties or buy a third party (professional recommendation, technical notice). Phile addition to contacts Phile addition the party is participant.		[
 Contact Plating :: Gold over copper Alloy 0.8µm minimum Durability :: S00 Mating cycles Delivered without Souriau contacts Temperature Range :: -65°C to +175°C Salt Spray :: 2000 hours Mass :: 19.9 g ± 10% Mass :: 19.9 g ± 10% A 19-10-2016 First Release MOD N° Delivered W/O Contact SHELL TYPE :: Plug with RFI Shielding CONTACT TYPE :: Standard Crimp Contact SHELL SIZE :: 15 PLATING :: J = Olive drab Cadmium CONTACT TYPE :: PIN(500 Matings) CONTACT TYPE :: PIN(500 Matings) CONTACT LAYOUT :: 15:15 CONTACT LAYOUT :: 15:15 SHEEL SIZE :: 15 CONTACT LAYOUT :: 15:15 CONTACT MINE A CONTACT LAYOUT :: 15:15 CONTACT MINE A CONTACT LAYOUT :: 15:15 CONTACT LAYOUT :: 15:15 	-Shell Material: Composite-Shell Plating: Olive drab Cadmium-Insulator: Thermoplastic-Contacts: Copper Alloy		Z' 31.5 Ma	x		due to a use o the Specifications	of the Products which do issued by either of the F onal recommendation, t	pes not comply wit Parties or by a thirc echnical notice.)	th d party	
-Delivered without Souriau contacts -Temperature Range : -65°C to +175°C. -Salt Spray : 2000 hours -Mass : 19.9 g ± 10% BASIC SERIES: 80 5 - 15 J 15 P SHELL TYPE : Plug with RFI Shielding Delivered W/O Contacts SHELL SIZE : 15 CONTACT TYPE : Standard Crimp Contact NPRDS / PROJECT SHELL SIZE : 15 CONTACT TYPE : Plug with RFI Shielding This document is the property of status to the reproduced or communicated without permission SHELL SIZE : 15 CONTACT TYPE : PlN(500 Matings) CONTACT TYPE : PlN(500 Matings) PLATING : J = Olive drab Cadmium CONTACT TYPE : PlN(500 Matings) SOURIAU WWW.SOURIAU.COM FORMAT SOURIAU DRG N° SHEET							FR]
-Salt Spray : 2000 hours -Mass : 19.9 g ± 10% BASIC SERIES: 8D 5 15 J 15 J 15 P A L BASIC SERIES: 8D 5 15 J 15 P A L CONTACT TYPE : Standard Crimp Contact SHELL SIZE : 15 PLATING : J = Olive drab Cadmium CONTACT LAYOUT : 15-15 CONTACT TYPE : J = Olive drab Cadmium State Contact A Contact Layout : 15-15 CONTACT LA						Р	N: 8D515J15F	PAL		
-Salt Spray : 2000 hours -Mass : 19.9 g ± 10% BASIC SERIES: 8D 5 - 15 J 15 P A L BASIC SERIES: 8D 5 - 15 J 15 P A L CONTACT TYPE : Plug with RFI Shielding CONTACT TYPE : Standard Crimp Contact SHELL SIZE : 15 PLATING : J = Olive drab Cadmium CONTACT LAYOUT : 15-15 CONTACT LAYOUT : 15-15 CO					A 19-1	0-2016 First Release				·
BASIC SERIES: 8D 5 15 J J P A L SCALe General linear NPRDS / PROJECT SHELL TYPE : Plug with RFI Shielding Delivered W/O Contacts Delivered W/O Contacts NA Image: Contact Type : Standard Crimp Contact State NA Image: Contact Type : Standard Crimp Contact State				-	ISS D	ATE Latest modification	n - by	сизто	OMER DRAWING	MOD N°
BASIC SERIES. ab 3 1 1 P A C Tolerances: B59 SHELL TYPE : Plug with RFI Shielding CONTACT TYPE : Standard Crimp Contact ORIENTATION : A NA Tolerances: B59 SHELL SIZE : 15 CONTACT TYPE : PIN(500 Matings) CONTACT TYPE : PIN(500 Matings) This document is the property of SOURIAU.COM SOURIAU This document is the property of source or communicated without permission PLATING : J = Olive drab Cadmium CONTACT LAYOUT : 15-15 FORMAT SOURIAU DRG N° SHEET					TITLE Composite Plug 8D series			es		
CONTACT TYPE : Standard Crimp Contact ORIENTATION : A SHELL SIZE : 15 CONTACT TYPE : PIN(500 Matings) PLATING : J = Olive drab Cadmium CONTACT LAYOUT : 15-15 FORMAT SOURIAU FORMAT SOURIAU FORMAT SOURIAU CONTACT TYPE : PIN(500 Matings)		J 15 P A		ed W/O Contacts			Tolerances:		859	
PLATING : J = Olive drab Cadmium CONTACT LAYOUT : 15-15 FORMAT SOURIAU DRG N° SHEET					SOUR	IAU WWW.	SOURIAU.CON	1	SOURIAU it must not be reproduc	ed or
					FORMAT		SOURIALI DR			
8D515J15PAL-C		I			A3		8D515J15P/			1/2

_	I	۵	ال	m		0	
4		Contact Layout $\begin{pmatrix} & & & & & \\ & & & & \\ $					
-	Contact position ID A + 100 (254)	Contacts (Insert arrangement 15-15) ation Location Y-axis (mm) Contact position ID Location *225 (5.72) J -244 (6.20) +014 (0.36)					
	Shell Arrangement Nun size no. cor	+ (14) (3.56) K - 202 (5.13) + (14) (3.56) + 0.14 (0.36) L - 100 (2.54) + 225 (5.72) - 113 (2.87) M + 000 (0.00) + 140 (3.56) - 209 (5.31) N + 110 (2.79) + 040 (1.02) - 245 (6.72) P + 000 (0.00) - 077 (1.96) - 209 (5.31) R - 110 (2.79) + 040 (1.02) - 113 (2.87) - 113 (2.87) nber of tatast Service contacts rating location Supersedes 1 16 I P MS20052-15 14 20 I All other MS20052-15					
ω							
						SOURIAU shall not be liab due to a use of the Pro the Specifications issued by (professional recor	oducts w v either c
N						PN: 8D	Count FR 0515.
					A 19-10-20 ISS DATE Designed By: TITLE	Date:	Compo
					SCALE NA	Genera Tolera ±	al linear ances: ±
					FORMAT A3	SOU	
L	Н	G	F	E	D	C	

