	Т		G	П	ſ	П		0	D	A		
4			G	ØS								4
ω		<u> </u>		Keying Show	wn as example			LAYO	OUT SHOWN AS EXAMPLE			3
	-Shell Material -Shell Plating -Insulator -Contacts	Standard : Based on MIL-DTL-38999 Series IIIDimNominalShell Material: CompositeØS48 MaxShell Plating: NickelZ'31.5 MaxInsulator: ThermoplasticVV THREADM37x1-6g					SOURIAU shall not be liable for any non-conformity or damage due to a use of the Products which does not comply with the Specifications issued by either of the Parties or by a third party (professional recommendation, technical notice.)					
N	-Seals & Grommet -Contact Plating -Durability -Delivered without So	: 500 Mating cyc	per Alloy 0.8µm minim	num				PN	I: 8D525M35PAL	sdiction & Control List Not Listed		2
	-Temperature Range -Salt Spray -Mass	 -65°C to +200° 2000 hours 38.4 g ± 10% 	C				A 07-10-201 ISS DATE Designed By:	6 First Release Latest modification Date:	n - by	CUSTOMER DRAWING	MOD N°	-
				, , , , ,			TITLE		Composite Plug			
_	BASIC SERIES: SHELL TYPE : Plug wit			M 35 P A	L	Delivered W/O Contacts	-		General linear Tolerances: ±	NPRDS / PROJECT 859 This document is the pr	operty of	1
	CONTACT TYPE : Standard Crimp Contact SHELL SIZE : 25 CONTACT TYPE : PIN(500 Matings)							WWW.SOURIAU.COM		SOURIAU it must not be reprod		
	PLATING : M =	Nickel				CONTACT LAYOUT : 25-35	FORMAT A3		SOURIAU DRG N 8D525M35PAL-0		SHEET 1/2	
Ľ	Н		G	F		E	D	С	В	A		-

	т		۵	П	ш	D	C	Φ	A		_
		Contact	Layout								
4											4
_			terment 25-35) Location X-axis (mm) (mm) 65 +.000 (0.00) 047 (1.19)								_
c.	$\begin{array}{cccccccccccccccccccccccccccccccccccc$	$\begin{array}{rrrrrrrrrrrrrrrrrrrrrrrrrrrrrrrrrrrr$	$\begin{array}{cccccccccccccccccccccccccccccccccccc$								3
	30 249 (t 31 249 (t 32 249 (t 33 249 (t 34 249 (t 35 249 (t 36 160 (t 37 166 (t 38 166 (t	6.32) 095 (2.41) 6.32) 190 (4.83) 6.32) 285 (7.24) 6.32) 380 (9.65) 6.32) 475 (12.07) 4.06) +.531 (13.49) 4.22) +.427 (10.85) 4.22) +.237 (6.02)	$\begin{array}{cccc} 93 & +.166 (4.22) &522 (13.26) \\ 94 & +.249 (6.32) & +.496 (12.60) \\ 95 & +.249 (6.32) & +.380 (9.65) \\ 96 & +.249 (6.32) & +.285 (7.24) \\ 97 & +.249 (6.32) & +.190 (4.83) \\ 98 & +.249 (6.32) & +.095 (2.41) \\ 99 & +.249 (6.32) &095 (2.41) \\ 100 & +.249 (6.32) &190 (4.83) \\ 102 & +.249 (6.32) &285 (7.24) \\ 103 & +.249 (6.32) &285 (7.24) \\ 103 & +.249 (6.32) &380 (9.65) \\ 104 & +.249 (6.32) &475 (12.07) \\ \end{array}$				SOURIAU shall not be liable due to a use of the Produ the Specifications issued by e (professional recomm	ucts which does not com	ply with a third party		
N	41166 (4 42166 (4 43166 (4 44166 (4 45166 (4 46166 (4	4.22) +.047 (1.19) 4.22) 047 (1.19) 4.22) 142 (3.61) 4.22) 237 (6.02) 4.22) 332 (8.43) 4.22) 327 (10.85)	105 +.332 (8.43) +.444 (11.28) 106 +.332 (8.43) +.332 (8.43) 107 +.332 (8.43) +.237 (6.02) 108 +.332 (8.43) +.142 (3.61) 109 +.332 (8.43) +.047 (1.19) 110 +.332 (8.43) 047 (1.19)						tion & Control List Not Listed		2
	48083 (2 49083 (2 50083 (2 51083 (2 52083 (2 53083 (2 53083 (2	2.11) +.190 (4.83) 2.11) +.095 (2.41) 2.11) +.000 (0.00)	$\begin{array}{c ccccccccccccccccccccccccccccccccccc$					25M35PAL			_
	34083 (55083 (56083 (57083 (58083 (2.11) 190 (4.83) 2.11) 285 (7.24) 2.11) 380 (9.65)	118 +.415 (10.54) +.000 (0.00) 119 +.415 (10.54) 095 (2.41) 120 +.415 (10.54) 190 (4.83) 121 +.424 (10.77) 357 (9.07) 122 +.479 (12.17) +.279 (7.09)				LO-2016 First Release DATE Latest modification - by			MOD N°	
	59 +.000 (0 60 +.000 (0 61 +.000 (0 62 +.000 (0	0.00) +.522 (13.26) 0.00) +.427 (10.85) 0.00) +.332 (8.43)	123 +.520 (13.21) +.190 (4.83) 124 +.546 (13.87) +.095 (2.41) 125 +.555 (14.10) +.000 (0.00) 126 +.546 (13.87) 095 (2.41)			Designed By:	· · ·		CUSTOMER DRAWING		_
	63 +.000 (0 64 +.000 (0		127 +.520 (13.21) 190 (4.83) 128 +.479 (12.17) 279 (7.09)			TITL	.E Co	omposite Plug 8D	series		
<u> </u>	Shell sizeArrangeme no.25-35	(Applicable to MIL- ent Number of Size contacts contact 128 22D	ts rating location			SCALE	General Toleran ±		NPRDS / PROJECT 859		1
						SOUR	WWW.SOURI	AU.COM	This document is the pr SOURIAU it must not be reprod communicated without p	uced or	
						FORMAT		IAU DRG N° 5M35PAL-C		SHEET	
	Н		G	F	E	D	C	B	A		