
Specification for AB-3535CJ Series

AB-3535CJ-F4F

3535 Ceramic 1.0W, 940 nm, 120° 3V IR LED



Features:

- Top view infrared LED
- High power infrared LED
- Low thermal resistance
- Pb-free reflow soldering application
- RoHS and REACH compliant

Applications:

- Infrared Illumination for cameras
- Surveillance systems
- Proximity sensor
- Auto Focus
- Gaming Notebook
- Large Size Touch Panel
- Car Sensors
- Virtual Reality

1 | Page

Absolute Maximum Ratings (T_j=25°C)

Item	Symbol	Absolute Max. Rating	Unit
Forward Current	I _F	1000	mA
Pulse Forward Current	I _{FP}	1200	mA
Power Dissipation	PD	3.6	W
Reverse Voltage	V_R	5	V
Operating Temperature	T _{opr}	-40~ +85	°C
Storage Temperature	T _{stg}	-40~ +105	°C
Junction Temperature	Tj	115	°C
Soldering Temperature	T _{sld}	Reflow soldering: 230°C or 260°C for 10 sec	

^{*} IFP condition with Pulse: Width≤100µs, Duty cycle≤1/10

Electrical/Optical Characteristics (T_i=25°C)

Item	Symbol	Min.	Тур.	Max.	Unit	Condition
Forward Voltage	V_{F}	2.6	3.0	3.6	>	I _f = 350mA
Reverse Current	I _R	-	-	10	μΑ	$V_R = 5V$
Radiant Flux	Фе	-	560	-	mW	$I_f = 350 \text{mA}$
Radiant Intensity	l _e	-	160	-	mW/Sr	I _f = 350mA
Peak Wavelength	λ_{p}		950	-	nm	I _f = 350mA
Viewing Angle	2θ _{1/2}	1	120	-	0	I _f = 350mA
Thermal Resistance	R _{th} j-sp	-	5.3	-	°C/W	I _f = 350mA
Electrostatic Discharge	ESD	6000	-	-	V	HBM

^{*} Tolerance of measurements of the Forward Voltage is ±0.1V

Naming System:

AB-3535CJ-F4F-yyy

yyy: bin code

^{*} LED's properties might be different from suggested values like above and below tables if operation condition will be exceeded our parameter range. Care is to be taken that power dissipation does not exceed the absolute maximum rating of the product

^{*} All measurements were made under the standardized environment of American Bright LED

^{*} Tolerance of measurements of the Radiant Flux is ±7%

^{*} $2\theta_{1/2}$ is the off-axis where the luminous intensity is 1/2 of the peak intensity

^{*} Tolerance of measurements of Peak Wavelength is ±2.0nm

^{*} R_{th} j-sp is the thermal resistance from LED junction to solder point on MCPCB with electrical power

BIN Structure

Radiant Flux BINs ($I_F = 350 \text{mA}$, $T_j = 25 ^{\circ}\text{C}$)

Radiant Flux			
BIN code	Min.	Max.	Unit
JNO	315	390	mW
JPO	390	490	mW
JQO	490	610	mW
JRO	610	770	mW
JSO	770	960	mW

^{*} Tolerance of meJSOasurements of the Luminous Flux is ±7%

Peak Wavelength Bins ($I_F = 350$ mA, $T_j = 25$ °C)

BIN code	Min.	Max.	Unit
XJ0	920	940	nm
XK0	940	960	nm
XLO	960	980	nm

^{*} Tolerance of measurements of the peak wavelength is ±2.0nm

Forward Voltage Ranks (I_F = 150mA, T_j =25°C)

BIN Code	Min.	Max.	Unit
AB6	2.6	2.8	V
AC3	2.8	3.0	V
AC4	3.0	3.2	V
AC5	3.2	3.4	V
AC6	3.4	3.6	V

^{*} Tolerance of measurements of the Forward Voltage is ±0.1V

Typical Characteristics Curves

Fig 1. Color Spectrum (T_j=25°C)




Fig 3. Forward Current vs. Relative Voltage, T_j =25°C




Fig 5. Typical Viewing Angle =60°, $T_i = 25$ °C




Fig 2. Forward Current vs. Relative Intensity, $T_j = 25^{\circ}C$




Fig 4. Ambient Temperature vs. Relative Output Flux,I_f=350mA






Fig 6. Soldering Temperature vs. Maximum Forward Current






Package Dimensions




^{*} The tolerance unless mentioned is ±0.1mm, unit = mm

Recommended Solder Pad








Recommeded Stencil Pattern


^{*} The tolerance unless mentioned is ± 0.1 mm, unit = mm

Reflow Soldering Characteristics




Reflow Soldering			
Temperature min (T _{s, min})	150°C		
Temperature Max (T _{s, Max)}	200°C		
Time (t _s) from (T _{s, min} to T _{s, Max})	60-120 s		
Ramp-up rate (T _L to T _p)	3°C/s Max		
Liquidous temperature (T _L)	217°C		
Time (T _L) maintained above T _L	60-150 s		
Peak package body temperature	260°C Max		
Time (T _p) within 5°C of the specified classification temperature (T _c)	30 s Max		
Ramp-down rate (Tp to Tl)	6°C/s Max		
Time 25°C to peak temperature	8 min. Max		

Package Dimensions of Tape




- * Quantity: Max 500pcs/Reel
- * Cumulative Tolerance: Cumulative Tolerance/10 pitches to be ±0.25mm
- * Package: P/N, Manufacturing data Code No. and Quantity to be indicated on a waterproof Package.
- * unit = mm

Package Dimensions of Reel






Packaging



* Capacity 4 or 8 reels per box.



* Capacity 48 or 64 reels per box.



Caution

- 1. Reflow soldering is recommended not to be done more than two times. In the case of more than 24 hours passed soldering after first, LEDs will be damaged.
- 2. Repairs should not be done after the LEDs have been soldered. When repair is unavoidable, suitable tools must be used.
- 3. Die slug is to be soldered.
- 4. When soldering, do not put stress on the LEDs during heating.
- 5. After soldering, do not warp the circuit board.

Notes on American Bright AB-3535CJ Series soldering:

- 1. Recommend to use reflow machine.
- 2. Recommend to use heating plate soldering.
- 3. Manual soldering is not recommended.

Notes on reflow process:

- 1. To confirm whether the actual temperature curve in the reflow soldering conditions comply with recommended conditions. LEDs are guaranteed for one time reflow.
- 2. During reflow process do not apply force on LED active area.
- 3. After reflow process, PCB board should be cooled down before packing or storage.

Precaution for use

Storage

- 1. Before opening the package: The LED should be kept at 30°C or less and 90%RH or less.
- 2. After opening the package: The LED's lifetime is 168Hrs @30°C or 60%RH. If unused LED remain, it should be stored in moisture proof packages JEDEC (MSL 3).
- 3.If the moisture absorbent material (silica gel) has faded away or the LEDs have exceeded the storage time, baking treatment should be performed using the following conditions: baking treatment: 60±5°C for 24 hours.