



Figure similar

Non-reversing motor starter, Size 00, Three phase full voltage, Solid-state overload relay, OLR amp range 0.75-3.4A, Non-combination type, Enclosure type 1, Indoor general purpose use, Standard width enclosure

|   |  |
|---|--|
| product brand name  | Class 14                                 |
| design of the product   | Full-voltage non-reversing motor starter |
| special product feature   | ESP200 overload relay                    |
| <b>General technical data</b>   |  |
| weight [lb]   | 8 lb                                     |
| Height x Width x Depth [in]   | 11 × 7 × 5 in                            |
| touch protection against electrical shock                               | (NA for enclosed products)               |
| installation altitude [ft] at height above sea level maximum            | 6560 ft                                  |
| ambient temperature [°F]  |  |
| • during storage  | -22 ... +149 °F                          |
| • during operation  | -4 ... +104 °F                           |
| ambient temperature   |  |
| • during storage  | -30 ... +65 °C                           |
| • during operation  | -20 ... +40 °C                           |
| country of origin   | USA                                      |
| <b>Horsepower ratings</b>   |  |
| yielded mechanical performance [hp] for 3-phase AC motor                |  |
| • at 200/208 V rated value  | 0.5 hp                                   |
| • at 220/230 V rated value  | 0.75 hp                                  |
| • at 460/480 V rated value  | 1.5 hp                                   |
| • at 575/600 V rated value  | 2 hp                                     |
| <b>Contactors</b>   |  |
| size of contactor   | NEMA controller size 00                  |
| number of NO contacts for main contacts                                 | 3  |
| operating voltage for main current circuit at AC at 60 Hz maximum       | 600 V                                    |
| operational current at AC at 600 V rated value                          | 9 A                                      |
| mechanical service life (switching cycles) of the main contacts typical | 10000000                                 |
| <b>Auxiliary contact</b>  |  |
| number of NC contacts at contactor for auxiliary contacts               | 0  |
| number of NO contacts at contactor for auxiliary contacts               | 1  |
| number of total auxiliary contacts maximum                              | 8  |
| contact rating of auxiliary contacts of contactor according to UL       | 10A@600VAC (A600), 5A@600VDC (P600)      |
| <b>Coil</b>   |  |
| type of voltage of the control supply voltage                           | AC                                       |
| control supply voltage  |  |

|  |               |
|--|---------------|
| <ul style="list-style-type: none"> <li>• at AC at 50 Hz rated value</li> <li>• at AC at 60 Hz rated value</li> </ul> | 550 V         |
| holding power at AC minimum  | 575 ... 600 V |
| apparent pick-up power of magnet coil at AC  | 8.6 W         |
| apparent holding power of magnet coil at AC  | 218 VA        |
| operating range factor control supply voltage rated value of magnet coil   | 25 VA         |
| percental drop-out voltage of magnet coil related to the input voltage   | 0.85 ... 1.1  |
| ON-delay time  | 50 %          |
| OFF-delay time   | 19 ... 29 ms  |
|  | 10 ... 24 ms  |

### Overload relay

|  |                                      |
|--|--------------------------------------|
| product function   |                                      |
| <ul style="list-style-type: none"> <li>• overload protection</li> <li>• phase failure detection</li> <li>• asymmetry detection</li> <li>• ground fault detection</li> <li>• test function</li> <li>• external reset</li> </ul> | Yes                                  |
| reset function   | Yes                                  |
| trip class   | Yes                                  |
| adjustable current response value current of the current-dependent overload release  | Yes                                  |
| tripping time at phase-loss maximum  | Yes                                  |
| relative repeat accuracy   | Yes                                  |
| product feature protective coating on printed-circuit board  | Manual, automatic and remote         |
| number of NC contacts of auxiliary contacts of overload relay  | CLASS 5 / 10 / 20 (factory set) / 30 |
| number of NO contacts of auxiliary contacts of overload relay  | 0.75 ... 3.4 A                       |
| operational current of auxiliary contacts of overload relay  | 3 s                                  |
| <ul style="list-style-type: none"> <li>• at AC at 600 V</li> <li>• at DC at 250 V</li> </ul>   | 1 %                                  |
| contact rating of auxiliary contacts of overload relay according to UL   | Yes                                  |
| insulation voltage (Ui)  | 1                                    |
| <ul style="list-style-type: none"> <li>• with single-phase operation at AC rated value</li> <li>• with multi-phase operation at AC rated value</li> </ul>  | 1                                    |
|  | 5 A                                  |
|  | 1 A                                  |
|  | 5A@600VAC (B600), 1A@250VDC (R300)   |
|  | 600 V                                |
|  | 300 V                                |

### Enclosure

|                                  |                            |
|----------------------------------|----------------------------|
| degree of protection NEMA rating | 1                          |
| design of the housing            | Indoor general purpose use |

### Mounting/wiring

|   |                                   |
|---|-----------------------------------|
| mounting position   | Vertical                          |
| fastening method  | Surface mounting and installation |
| type of electrical connection for supply voltage line-side  | Screw-type terminals              |
| tightening torque [lbf-in] for supply   | 20 ... 20 lbf-in                  |
| type of connectable conductor cross-sections at line-side at AWG cables single or multi-stranded                  | 1x(14 - 2 AWG)                    |
| temperature of the conductor for supply maximum permissible   | 75 °C                             |
| material of the conductor for supply  | AL or CU                          |
| type of electrical connection for load-side outgoing feeder   | Screw-type terminals              |
| tightening torque [lbf-in] for load-side outgoing feeder  | 20 ... 24 lbf-in                  |
| type of connectable conductor cross-sections at AWG cables for load-side outgoing feeder single or multi-stranded | 2 x (14 - 10 AWG)                 |
| temperature of the conductor for load-side outgoing feeder maximum permissible                                    | 75 °C                             |
| material of the conductor for load-side outgoing feeder   | CU                                |
| type of electrical connection of magnet coil  | screw-type terminals              |
| tightening torque [lbf-in] at magnet coil   | 5 ... 12 lbf-in                   |
| type of connectable conductor cross-sections of magnet coil at AWG cables single or multi-stranded                | 2 x (16 - 12 AWG)                 |

|  |  |
|--|--|
| temperature of the conductor at magnet coil maximum permissible  | 75 °C  |
| material of the conductor at magnet coil   | CU   |
| type of electrical connection for auxiliary contacts   | screw-type terminals                               |
| tightening torque [lbf·in] at contactor for auxiliary contacts   | 10 ... 15 lbf·in                                   |
| type of connectable conductor cross-sections at contactor at AWG cables for auxiliary contacts single or multi-stranded      | 1 x (12 AWG), 2 x (16 - 14 AWG), 2 x (18 - 16 AWG) |
| temperature of the conductor at contactor for auxiliary contacts maximum permissible   | 75 °C  |
| material of the conductor at contactor for auxiliary contacts  | CU   |
| type of electrical connection at overload relay for auxiliary contacts   | screw-type terminals                               |
| tightening torque [lbf·in] at overload relay for auxiliary contacts  | 7 ... 10 lbf·in                                    |
| type of connectable conductor cross-sections at overload relay at AWG cables for auxiliary contacts single or multi-stranded | 2 x (20 - 14 AWG)                                  |
| temperature of the conductor at overload relay for auxiliary contacts maximum permissible                                    | 75 °C  |
| material of the conductor at overload relay for auxiliary contacts   | CU   |

#### Short-circuit current rating

|   |   |
|---|---|
| design of the fuse link for short-circuit protection of the main circuit required | 10kA@600V (Class H or K); 100kA@600V (Class R or J) |
| design of the short-circuit trip  | Thermal magnetic circuit breaker                    |
| breaking capacity maximum short-circuit current (I <sub>cu</sub> )                |   |
| • at 240 V  | 14 kA   |
| • at 480 V  | 10 kA   |
| • at 600 V  | 10 kA   |
| certificate of suitability  | NEMA ICS 2; UL 508; CSA 22.2, No.14                 |

#### Further information

**Industrial Controls - Product Overview (Catalogs, Brochures,...)**

[www.usa.siemens.com/iccatalog](http://www.usa.siemens.com/iccatalog)

**Industry Mall (Online ordering system)**

<https://mall.industry.siemens.com/mall/en/us/Catalog/product?mlfb=US2:14BUB32BE>

**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**


<https://support.industry.siemens.com/cs/US/en/ps/US2:14BUB32BE>

**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)**

[http://www.automation.siemens.com/bilddb/cax\\_de.aspx?mlfb=US2:14BUB32BE&lang=en](http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=US2:14BUB32BE&lang=en)

**Certificates/approvals**

<https://support.industry.siemens.com/cs/US/en/ps/US2:14BUB32BE/certificate>



| LETTER | KNOCKOUT & CONDUIT SIZE             |
|--------|-------------------------------------|
| A      | ø22.2 FOR 12.7 CONDUIT              |
| B      | ø22.2 X ø28.6 FOR 12.7 & 19 CONDUIT |
| C      | ø28.6 X ø34.9 FOR 19 & 25.4 CONDUIT |

last modified:

11/29/2021