SIEMENS

Data sheet

3RA2115-0BA15-1AK6



Fuseless motor starter Direct start 600VAC Size S00 0.14-0.2a 110/120VAC 50/60HZ screw connection For screw mounting Or 35 mm rail-mounting Type of coordination 2 IQ = 150 KA Also full fills type Of coordination 1 1NO+1NC (MSP) 1NO (contactor)

product brand name	SIRIUS			
product designation	non-fused motor starter 3RA2			
design of the product	direct starter			
manufacturer's article number				
 of the supplied contactor 	<u>3RT2015-1AK61</u>			
 of the supplied circuit-breakers 	3RV2011-0BA15			
 of the supplied link module 	<u>3RA1921-1DA00</u>			
General technical data				
size of the circuit-breaker	S00			
size of load feeder	S00			
product extension auxiliary switch	Yes			
insulation voltage with degree of pollution 3 at AC rated value	690 V			
degree of pollution	3			
surge voltage resistance rated value	6 kV			
shock resistance according to IEC 60068-2-27	6g / 11 ms			
mechanical service life (switching cycles) of contactor typical	30 000 000			
type of assignment	2			
Ambient conditions				
ambient temperature				
 during operation 	-20 +60 °C			
 during storage 	-50 +80 °C			
 during transport 	-55 +80 °C			
Main circuit				
number of poles for main current circuit	3			
design of the switching contact	electromechanical			
adjustable current response value current of the current-dependent overload release	0.14 0.2 A			
operating voltage				
rated value	690 V			
 at AC-3 rated value maximum 	690 V			
at AC-3 rated value maximum operating frequency rated value	690 V 50 60 Hz			
operating frequency rated value	50 60 Hz			
operating frequency rated value operational current at AC-3 at 400 V rated value	50 60 Hz			
operating frequency rated value operational current at AC-3 at 400 V rated value operating power at AC-3	50 60 Hz 0.2 A			
operating frequency rated valueoperational current at AC-3 at 400 V rated valueoperating power at AC-3• at 400 V rated value	50 60 Hz 0.2 A 60 W			
operating frequency rated value operational current at AC-3 at 400 V rated value operating power at AC-3 • at 400 V rated value • at 500 V rated value	50 60 Hz 0.2 A 60 W 60 W			

• at 50 Hz rated value	110 V		
• at 50 Hz rated value	93.5 121 V		
• at 60 Hz rated value	120 V		
at 60 Hz rated value	96 132 V		
apparent holding power of magnet coil at AC	4.8 VA		
inductive power factor with the holding power of the coil	0.25		
Auxiliary circuit			
number of NC contacts for auxiliary contacts	1		
number of NO contacts for auxiliary contacts	2		
Protective and monitoring functions			
trip class	CLASS 10		
design of the overload release	thermal (bimetallic)		
response value current of instantaneous short-circuit trip unit	2.6 A		
Short-circuit protection			
product function short circuit protection	Yes		
design of the short-circuit trip	magnetic		
conditional short-circuit current (Iq)			
 at 690 V according to IEC 60947-4-1 rated value 	100 000 A		
• at 400 V according to IEC 60947-4-1 rated value	153 000 A		
 at 500 V according to IEC 60947-4-1 rated value at 500 V according to IEC 60947-4-1 rated value 	100 000 A		
Installation/ mounting/ dimensions			
mounting position	vertical		
fastening method	Snap-mounted to DIN rail or	screw-mounted with a	ditional push-in lug
height	167.2 mm	Sciew-mounted with ad	lutional push-in lug
width	45 mm		
depth	- 97.1 mm		
required spacing	07.111111		
 for grounded parts 			
— forwards	0 mm		
— backwards	0 mm		
— upwards	20 mm		
— at the side	9 mm		
— downwards	10 mm		
• for live parts			
— forwards	0 mm		
— backwards	0 mm		
— upwards	20 mm		
— downwards	10 mm		
— at the side	9 mm		
Connections/ Terminals			
	scrow type terminale		
type of electrical connection for main current circuit type of connectable conductor cross-sections	screw-type terminals		
for main contacts stranded	$0.5 \ 4 \ mm^2 \ 2v \ (0.75 \ 0.5)$	mm^2	
at AWG cables for main contacts	0.5 4 mm², 2x (0.75 2.5 mm²) 2x (20 16), only for contactor 2x (18 14), 2x 12		
connectable conductor cross-section for main contacts	0.5 2.5 mm ²	5101 ZA (10 14), ZX 12	
finely stranded with core end processing	0.0 2.0 11111		
Safety related data	4 000 005		
B10 value with high demand rate according to SN 31920	1 000 000		
proportion of dangerous failures with high demand rate according to SN 31920	73 %		
protection class IP on the front according to IEC 60529	IP20		
touch protection on the front according to IEC 60529	finger-safe, for vertical conta	act from the front	
Certificates/ approvals			
General Product Approval		For use in hazard- ous locations	Declaration of Conformity

St.	<u>Confirmation</u>	(UL)	EAC	KEx ATEX	CE EG-Konf.		
Declaration of Conformity	Test Certificates		Marine / Shipping				
UK CA	<u>Special Test Certific-</u> <u>ate</u>	<u>Type Test Certific-</u> ates/Test Report	ABS	B U R E A U VERITAS	Llovd's Register uts		
Marine / Shipping				other	Railway		
PRS	RINA	RMRS	DIVIGL	<u>Confirmation</u>	Vibration and Shock		
Further information Information- and Downloadcenter (Catalogs, Brochures,) https://www.siemens.com/ic10 Industry Mall (Online ordering system) https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3RA2115-0BA15-1AK6							
Cax online generator http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RA2115-0BA15-1AK6 Service&Support (Manuals, Certificates, Characteristics, FAQs,) https://support.industry.siemens.com/cs/ww/en/ps/3RA2115-0BA15-1AK6							
Image database (pro http://www.automatio Characteristic: Trip https://support.indust Further characterist	ry.siemens.com/cs/ww/e oduct images, 2D dime on.siemens.com/bilddb/ca ping characteristics, I ² f ry.siemens.com/cs/ww/e tics (e.g. electrical endo on.siemens.com/bilddb/in	nsion drawings, 3D n ax_de.aspx?mlfb=3RA t, Let-through current n/ps/3RA2115-0BA15 urance, switching fre	nodels, device circuit (2115-0BA15-1AK6&lan t -1AK6/char quency)	<u>g=en</u>			

last modified:

12/15/2020 🖸