SIEMENS

Data sheet

3RA2120-0HD23-0BB4



Fuseless motor starter Direct start 600VAC Size S0 0.55-0.8A 24V DC screw connection For snapping onto 60 mm busbar systems Type of coordination 2 IQ = 150 KA Also full fills type Of coordination 1 1NO+1NC (contactor)

product brand name	SIRIUS			
product designation	non-fused motor starter 3RA2			
design of the product	direct starter			
manufacturer's article number				
 of the supplied contactor 	3RT2023-1BB40			
 of the supplied circuit-breakers 	3RV2011-0HA10			
 of the supplied busbar adapter 	8US1251-5NT10			
 of the supplied link module 	3RA2921-1BA00			
General technical data				
size of the circuit-breaker	S00			
size of load feeder	S0			
product extension auxiliary switch	Yes			
insulation voltage with degree of pollution 3 at AC rated value	690 V			
degree of pollution	3			
surge voltage resistance rated value	6 kV			
shock resistance according to IEC 60068-2-27	6g / 11 ms			
mechanical service life (switching cycles) of contactor typical	10 000 000			
type of assignment	2			
Substance Prohibitance (Date)	03/01/2017			
Ambient conditions				
ambient temperature				
 during operation 	-20 +60 °C			
 during storage 	-50 +80 °C			
 during transport 	-55 +80 °C			
Main circuit				
number of poles for main current circuit	3			
design of the switching contact	electromechanical			
adjustable current response value current of the current-dependent overload release	0.55 0.8 A			
operating voltage				
rated value	690 V			
at AC-3 rated value maximum	690 V			
operating frequency rated value	50 60 Hz			
operational current at AC-3 at 400 V rated value	0.6 A			
operating power at AC-3				
operating power at AC-3 ■ at 400 V rated value	180 W			
	180 W 250 W			

Control circuit/ Control							
control supply voltage at DC							
rated value		24 V					
holding power of magnet coil at DC		5.9 W					
Auxiliary circuit							
number of NC contacts for auxiliary conta	icts	1					
number of NO contacts for auxiliary conta	icts	1					
Protective and monitoring functions							
trip class		CLAS	SS 10				
design of the overload release		thermal (bimetallic)					
response value current of instantaneous sho	rt-circuit trip	10.4 A					
unit	·						
Short-circuit protection							
product function short circuit protection		Yes					
design of the short-circuit trip		magn	etic				
conditional short-circuit current (Iq)							
 at 400 V according to IEC 60947-4-1 ra 	ated value	153 0	00 A				
Installation/ mounting/ dimensions							
mounting position		vertic	al				
fastening method			for snapping onto 60 mm busbar systems				
height			260 mm				
width		45 mm					
depth		165 mm					
required spacing		. 100 11					
for grounded parts							
— forwards		10 mm					
— backwards		10 mm					
— upwards		0 mm					
— upwards — at the side		30 mm					
— at the side — downwards		9 mm					
		10 mm					
• for live parts		40					
— forwards		10 mm					
— backwards			0 mm				
— upwards		30 mm					
— downwards		10 mr					
— at the side		9 mm					
Connections/ Terminals							
type of electrical connection for main current		screw	-type terminals				
type of connectable conductor cross-sect	tions						
 for main contacts stranded 			0 mm², 2x (2.5 6 mr	m²)			
at AWG cables for main contacts			6 12), 2x (14 8)				
connectable conductor cross-section for main finely stranded with core end processing	n contacts	1 6 mm²					
Safety related data							
B10 value with high demand rate according t	o SN 31920	1 000 000					
proportion of dangerous failures with high de according to SN 31920	mand rate	73 %	73 %				
protection class IP on the front according 60529	to IEC	IP20	IP20				
touch protection on the front according to IEC 60529		finger	finger-safe, for vertical contact from the front				
Certificates/ approvals							
	For use in ha	azard-	Declaration of				
General Product Approval	ous location		Conformity	other	Dangerous Good		
<u>Confirmation</u>				Confirmation	Transport Informa-		
EHI	⟨£x⟩	•	CE		<u>tion</u>		
LIIL	ATEX		EG-Konf.				

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

https://www.siemens.com/ic10

Industry Mall (Online ordering system)

https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3RA2120-0HD23-0BB4

Cax online generator

http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RA2120-0HD23-0BB4

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

https://support.industry.siemens.com/cs/ww/en/ps/3RA2120-0HD23-0BB4

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3RA2120-0HD23-0BB4&lang=en

Characteristic: Tripping characteristics, I2t, Let-through current

https://support.industry.siemens.com/cs/ww/en/ps/3RA2120-0HD23-0BB4/char

Further characteristics (e.g. electrical endurance, switching frequency)

http://www.automation.siemens.com/bilddb/index.aspx?view=Search&mlfb=3RA2120-0HD23-0BB4&objecttype=14&gridview=view1

last modified: 12/15/2020 ☑