
Technical Data Sheet



COAXIAL TERMINAISON TNC MALE 6 GHZ 50W



This document contains proprietary information and such information shall not be disclosed to any third party for any purpose whatsoever or used for manufacturing purposes without prior written agreement from Radiall. The data defined in this document are given as an indication, in the effort to improve our products; we reserve the right to make any changes judged necessary.

Technical Data Sheet

COAXIAL TERMINAISON TNC MALE 6 GHZ 50W



2/2	ISSUE OB	SUE 08-11-19B SERIES TERMINAT		N	PART NU	JMBER	R404762000
				TRICAL CHA	RACTERISTICS		
Frequency (GHz)			DC - 3	3 - 6	-		
V.S.	W.R (≤)		1.20	1.40			
Ope	rating Freque	ency Range	9		DC - 6		GHz
	edance			50			Ω
	Resistance k power at 25	°C (1us 1	%0)		50 2000		Ω ± 5% W
	age power at 25		/00)		50		W (Free Air Cooled)
							W (Conduction Cooled)
Con Weig	nectors ght		TNC 284,9700		ARACTERISTICS Male		MIL C39012
			erating temperatur rage temperature	range	-55/+12 -55/+12		
			(%) Hang (%) Hang (-15	rsus temperature		
				SPECIFIC	ATION		
			<u>0</u>	THER CHARA	CTERISTICS		
	M	OUNTED V			CTERISTICS	NVECTIO	Ν
	M	OUNTED				NVECTIO	Ν