
Technical Data Sheet

BNC ATTENUATOR 14 DB 3 GHZ 1W





This document contains proprietary information and such information shall not be disclosed to any third party for any purpose whatsoever or used for manufacturing purposes without prior written agreement from Radiall. The data defined in this document are given as an indication, in the effort to improve our products; we reserve the right to make any changes judged necessary.

Technical Data Sheet

BNC ATTENUATOR 14 DB 3 GHZ 1W



	ISSUE 31	ISSUE 31-03-20C SERIE ATTENUA		OR	PAR	T NUMBER	R412414124
	-		FL		ARACTERISTICS		
	(0)11)					-	
	Frequency (GHz) V.S.W.R (≤)		DC - 2 1.20	2 - 3 1.30			
	viation(±dB)		0.50	0.50			
	. ,						
Ope	erating Freque	ncy Range	e	DC - 3			GHz
	Impedance				50		Ω
	Nominal Attenuation Peak power at 25°C (14		dB
			%0)	100			W
Ave	rage power at	25°C	3		1		W (Free Air Cooled)
							W (Conduction Cooled)
Wei	ght		12,84	g			
			100 90 80 770 60 80 40 30 20 10 0	Power derating	Versus temperature	85 °C	
				SPECIF	CATION		

This document contains proprietary information and such information shall not be disclosed to any third party for any purpose whatsoever or used for manufacturing purposes without prior written agreement from Radiall. The data defined in this document are given as an indication, in the effort to improve our products; we reserve the right to make any changes judged necessary.