

# FAN.00.250.CLA

## SUMMARY

#### # Wires

Coax



Image is for illustrative purpose only

| Series           | 00                |
|------------------|-------------------|
| Termination type | Male solder       |
| IP rating        | 50                |
| AWG wire size    | 0.00 - 0.00       |
| Cable Ø          | 0.00 - 0.00 mm    |
| Status           | Active            |
| Matching parts   | PCA.00.250.CTLC29 |

1

### Request a quote

Download

Catalog

### **TECHNICAL DETAILS**

#### **Mechanics**

| Shell Style/Model | FA*: Fixed plug, non-latching, nut fixing   |
|-------------------|---|
| Keying            | Circular, male  |
| Housing Material  | Brass (chrome plated [SAE AMS 2460]) shell and collet nut, nickel plated [SAE AMS QQ N 290] brass latch sleeve and mid pieces |
| Weight            | 2.49 g  |
| Performance       |   |
| Configuration     | 00.250 : 1 Coax (50 Ohm)  |
| Insulator         | L: PEEK (UL 94 / V-0/1.5)   |
| Rated Current     | 4 Amps  |
|                   |   |
| Coolifications    |   |

#### Specifications

Contact Type: Coaxial 50 Ohm (Solder) Contact Dia.: 0.7 mm (0.028in) Bucket Dia.: 0.6 mm (0.024in) Test voltage: 2.1 kV (rms) R (max): 6.1 mOhm Vtest: 2100 V (AC), 3000 V (DC)


#### Impedance: 50 Ohm


LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

#### Others

Endurance (Shell): 5000 mating cycles F ret (min): 100 N Salt Spray Corrosion: >1000 hr

### DRAWINGS







#### Dimensions

|     | А    | В    | E    | L    | м    | N    | S1   | \$3  | e      |
|-----|------|------|------|------|------|------|------|------|--------|
| mm. | 8    | 10.3 | 2.9  | 18.1 | 9    | 15.0 | 6.3  | 9    | M7x0.5 |
| in. | 0,31 | 0,41 | 0,11 | 0,71 | 0,35 | 0,59 | 0,25 | 0,35 |        |

**RECOMMENDED BY LEMO** 

Tools

#### Cables

| 159580 | PVC | Black |  |
|--------|-----|-------|--|
| 17420  | PVC | Black |  |

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

| 17450               | COPOLYMER | Black |  |
|---------------------|-----------|-------|--|
| 178190              | PTFE      | Brown |  |
| 18000               | PTFE      | Brown |  |
| 18700               | PTFE      | White |  |
| 18800               | PTFE      | White |  |
| 196270              | PTFE      | White |  |
| 31600               | PTFE      | Brown |  |
| 62000               | PVC       | Black |  |
| CCX.50.030.083.180B |           | White |  |
| CCX.50.RG0.58AU14B  | FEP       | White |  |
| CCX.50.RG1.74-U25N  | PVC       | Black |  |
| CCX.50.RG1.74AU28N  | PVC       | Black |  |
| CCX.50.RG1.74AU28N  | PVC       | Black |  |
| CCX.50.RG1.74U25N   | PVC       | Black |  |
| CCX.50.RG1.78BU18M  | FEP       | Brown |  |
| CCX.50.RG1.78BU18M  | PTFE      | Brown |  |
| CCX.50.RG1.88AU24B  | TFE       | White |  |
| CCX.50.RG1.88AU26B  | PFA       | White |  |
| CCX.50.RG1.88AU26B  | PTFE      | White |  |
| CCX.50.RG1.96AU19B  | PTFE      | White |  |
| CCX.50.RG1.96AU20B  | PFA       | White |  |
| CCX.50.RG3.16BU26M  | FEP       | Brown |  |
| CCX.50.RG3.16U28M   | PTFE      | Brown |  |
| CCX.75.040.195327G  | PVC       | Grey  |  |
| CCX.75.RG0.59BU62N  | PVC       | Black |  |
| CCX.75.RG1.79BU26M  | FEP       | Brown |  |
| CCX.75.RG1.87AU26B  | PFA       | White |  |
| CCX.75.RG1.87AU27B  | PTFE      | White |  |
| CCX.93.RG0.62AU62N  | PVC       | Black |  |
| CCX.95.RG1.80BU36M  | PTFE      | Brown |  |
| CCX.95.RG1.95AU37B  | PFA       | White |  |

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.