

SPECIFICATION


THIS DRAWING CONTAINS INFORMATION PROPRIETARY TO RF INDUSTRIES, LTD. ANY UNAUTHORIZED USE OF THIS DRAWING IS EXPRESSLY PROHIBITED. ANY VIOLATION IS PUNISHABLE UNDER U.S. COPYRIGHT LAWS.


REV	DESCRIPTION	DWN DATE		APPROVED	
Α	ENGINEERING RELEASE	czs	9/5/97	R. RICE	
		П			


ALL DIMENSIONS REFERENCE ONLY














SUGGESTED STRIPPING INSTRUCTIONS SUGGESTED CRIMP: .068

SPECIFICATIONS:

IMPEDANCE: 50 OHMS

WORKING VOLTAGE: 500 VRMS @ SEA LEVEL FREQUENCY RANGE: 0-4 GHz INSERTION LOSS: \leq -.2 dB @ 3 GHz VSWR MAX: 1.4:1 @ 3 GHz

FOR TIMES LMR-200, LMR-200 ULTRAFLEX, ALPHA 9848 & MSI-22

12	IN LINE NUT	1		SILVER	DIMENSIONS ARE AND [MILLIMETERS		Γ,	$\overline{}$			610 MIRAM		
11	WASHER	1	BRASS	SILVER	AND [MILLIMETER.	اد	<i> L</i>	71400		S. S.	AN DIEGO,		
10	GASKET	1	S.I. RUBBER	RED	UNLESS OTHERWISE NOTED TOLERANCES ARE:		DIVISION OF RF INDUSTRIES, LTD. (619)549-6345 FAX						
9	CLAMP	1	BRASS	SILVER									
8	WASHER	1	BRASS	SILVER	DECIMALS [DIAMETER				<u> </u>			
7	SPRING	1	QQB613 (BRASS)	NONE	DECIMALS	SIMILILIX		RER	1	100 - 02	$T \supset C$		
6	SPLIT LOCK WASHER	1	BRASS	SILVER						100-02	. O I		
5	GASKET	1	S.I. RUBBER	RED	DRAWN	1			MALE	CLAMP PLUC			
4	SHELL	1	BRASS	SILVER	C. ZUNIGA	9/5/97	MALE CLAMP PLUG						
3	DIELECTRIC	1	PTFE	NONE	CHECKED		SIZE	CABLE GROUP_	_	DWG NO.		REV	
2	PIN [PIN-3C2-11]	1	BRASS	GOLD	ORJ DRAWN		ΙΑ		>	874	16	1 A I	
1	BODY	1	BRASS	SILVER	C. ZUNIGA 9/5/97		- ` `				. 	1 ' '	
ITEM	DESCRIPTION	QTY	MATERIAL	FINISH	APPROVALS	DATE	SCA	ALE: 2:1	CAD FII	LE 13ARC B	SHEET	1 OF 1	