

THIS DRAWING CONTAINS INFORMATION PROPRIETARY TO RF INDUSTRIES, ANY UNAUTHORIZED USE OF THIS DRAWING IS EXPRESSLY PROHIBITED WITHOUT WRITTEN PERMISSION FROM RF INDUSTRIES. ANY VIOLATION IS PUNISHABLE UNDER U.S. COPYRIGHT LAWS.

ALL DIMENSIONS ARE REFERENCE ONLY

PAR	RFF-1401-D			
REV	DESCRIPTION	DWN	DATE	APPROVED
_	ENGINEERING RELEASE	CZS	4/25/06	JDMc





RECOMMENDED STRIPPING DIMENSIONS USE RFA-4004-20 CRIMP TOOL

SPECIFICATIONS:

IMPEDANCE: 75 Ohms

1 BODY

FREQUENCY RANGE: SEE CABLE

MANUFACTURER SPECS

FOR RG-59, 59A, 59B, 62, 62A, 62C/U; ALPHA 9059, 9062, 9830, 9840, 9845; BELDEN 8221, 8241, 9169, 9204,

9228; CANARE LV-61S; CommScope 5555, 5560, 5563

NICKEL, 100μ " _____

1 BRASS

2 COMPRESSION PLAST 3 RING 4 SHELL 5	BRASS NICKEL, 100		UNLESS OTHERWISE SPECIFIED:	7610 MIRAMAR RD SAN DIEGO, CA 92126 (858) 549-6340 (858) 549-6345 FAX
7 8 9		DRAWN C. ZUNIGA 4/25/06	DIMENSIONS ARE IN INCHES AND [MILLIMETERS] UNLESS OTHERWISE NOTED	F PLUG COMPRESSION CLAMP, WATERPROOF
11 12 13 14		CHECKED ORJ DRAWN C. ZUNIGA 10/21/04	TOLERANCES ARE: DECIMALS DIAMETER	SIZE CABLE GROUP DWG NO. REV CAD FILE
# DESCRIPTION	QTY MATERIAL FINISH	APPROVALS DATE		SCALE: NTS CAD FILE OUTLINE SHEET 1 OF 1

UNLESS OTHERWISE SPECIFIED: