

# **MLFB-Ordering data**

6SL3230-1YE14-0AF0



Client order no. : Order no. :

Offer no. : Remarks:

Item no.: Consignment no. : Project :

Rated data		
Input		
Number of phases	3 AC	
Line voltage	380 480 V	′ +10 % -20 %
Line frequency	47 63 Hz	
Rated voltage	400V IEC	480V NEC
Rated current (LO)	3.60 A	3.00 A
Rated current (HO)	2.72 A	2.70 A
Output		
Number of phases	3 AC	
Rated voltage	400V IEC	480V NEC
Rated power (LO)	1.50 kW	2.00 hp
Rated power (HO)	1.10 kW	1.50 hp
Rated current (LO)	4 10 A	3 40 4

Rated current (HO)	2.72 A	2.70 A
Output		
Number of phases	3 AC	
Rated voltage	400V IEC	480V NEC
Rated power (LO)	1.50 kW	2.00 hp
Rated power (HO)	1.10 kW	1.50 hp
Rated current (LO)	4.10 A	3.40 A
Rated current (HO)	3.10 A	3.00 A
Rated current (IN)	4.30 A	
Max. output current	4.80 A	
Pulse frequency	4 kHz	
Output frequency for vector control	0 200 Hz	
Output frequency for V/f control	0 550 Hz	

iiput		
Number of phases	3 AC	
Line voltage	380 480 V +10 % -20 %	
Line frequency	47 63 Hz	
Rated voltage	400V IEC	480V NEC
Rated current (LO)	3.60 A	3.00 A
Rated current (HO)	2.72 A	2.70 A
Dutput		
Number of phases	3 AC	
Rated voltage	400V IEC	480V NEC
Rated power (LO)	1.50 kW	2.00 hp
Rated power (HO)	1.10 kW	1.50 hp
Rated current (LO)	4.10 A	3.40 A
Rated current (HO)	3.10 A	3.00 A
Rated current (IN)	4.30 A	
Max. output current	4.80 A	
Pulse frequency	4 kHz	
Output frequency for vector control	0 200 Hz	
Output frequency for V/f control	0 550 Hz	

Overload capability	

### Low Overload (LO)

110% base load current IL for 60 s in a 300 s cycle time

#### High Overload (HO)

150% x base load current IH for 60 s within a 600 s cycle time

General tech. specifications		
Power factor λ	0.70 0.85	
Offset factor cos φ	0.96	
Efficiency η	0.98	
Sound pressure level (1m)	55 dB	
Power loss	0.060 kW	
Filter class (integrated)	RFI suppression filter for Category C2	
EMC category (with accessories)	Category C2	

Ambient conditions		
Standard board coating type	Class 3C3, according to IEC 60721-3-3: 2002	
Cooling	Air cooling using an integrated fan	
Cooling air requirement	0.005 m³/s (0.177 ft³/s)	
Installation altitude	1000 m (3280.84 ft)	
Ambient temperature		
Operation	-20 45 °C (-4 113 °F)	
Transport	-40 70 °C (-40 158 °F)	
Storage	-25 55 °C (-13 131 °F)	

### **Relative humidity**

	95 % At 40 °C (104 °F), condensation
Max. operation	and icing not permissible



# **MLFB-Ordering data**

6SL3230-1YE14-0AF0



			Figure simil
Mechanica	l data	Closed-loop cor	ntrol techniques
Degree of protection	IP20 / UL open type	VIII. 1	.II.
Size	FSA	V/f linear / square-law / parameteri	<b>zable</b> Yes
Net weight	3 kg (7.50 lb)	V/f with flux current control (FCC)	Yes
Width	73 mm (2.87 in)	V/f ECO linear / square-law	Yes
Height	232 mm (9.13 in)	Sensorless vector control	Yes
Depth	218 mm (8.58 in)	Vector control, with sensor	No
Inputs / ou	tputs	Encoderless torque control	Yes
Standard digital inputs		Torque control, with encoder	No
Number	6		
Switching level: 0→1	11 V	Communication	
Switching level: 1→0	5 V	Communication	PROFINET, EtherNet/IP
Max. inrush current	15 mA	Connections	
Fail-safe digital inputs	13 1111	Signal cable	
Number	1	Conductor cross-section	0.15 1.50 mm <sup>2</sup> (AWG 24 AWG 16)
Digital outputs		Line side	
Number as relay changeover contact	2	Version	screw-type terminal
Output (resistive load)	DC 30 V, 5.0 A	Conductor cross-section	1.50 2.50 mm <sup>2</sup> (AWG 16 AWG 14)
Number as transistor	0	Motor end	
Analog / digital inputs		Version	Screw-type terminals
Number	2 (Differential input)	Conductor cross-section	1.50 2.50 mm² (AWG 16 AWG 14)
Resolution	10 bit	DC link (for braking resistor)	,
Switching threshold as digital in	put	<u> </u>	0.1
0→1	4 V	PE connection	On housing with M4 screw
1→0	1.6 V	Max. motor cable length	4-0 (400 40 (1)
Analog outputs		Shielded	150 m (492.13 ft)
3			
NI	4 (1)		

Page 2 of 3

PTC/ KTY interface

Number

1 (Non-isolated output)



### MLFB-Ordering data


6SL3230-1YE14-0AF0



Figure similar

## Converter losses to EN 50598-2\*

Efficiency class	IE2
Comparison with the reference converter (90% / 100%)	-35.00 %



The percentage values show the losses in relation to the rated apparent power of the converter.

The diagram shows the losses for the points (as per standard EN 50598) of the relative torque generating current (I) over the relative motor stator frequency(f). The values are valid for the basic version of the converter without options/components.

## **Standards**

Compliance with standards UL, cUL, CE, C-Tick (RCM), EAC, KCC, SEMI F47, REACH

**CE** marking

EMC Directive 2004/108/EC, Low-Voltage Directive 2006/95/EC

<sup>\*</sup>converted values