

# **MLFB-Ordering data**

#### 6SL3230-2YE50-0AF0



Client order no. : Order no. : Offer no. : Remarks : Item no. : Consignment no. : Project :

Rated data			
nput			
Number of phases	3 AC		
Line voltage	380 480 V +10 % -20	380 480 V +10 % -20 %	
Line frequency	47 63 Hz		
Rated voltage	400V IEC 480V NE	c	
Rated current (LO)	308.00 A 301.00 A	١	
Rated current (HO)	275.00 A 263.00 A	١	
Output			
Number of phases	3 AC		
Rated voltage	400V IEC 480V NE	C	
Rated power (LO)	160.00 kW 250.00 h	р	
Rated power (HO)	132.00 kW 150.00 h	'n	

Rated current (HO)	275.00 A	263.00 A
Output		
Number of phases	3 AC	
Rated voltage	400V IEC	480V NEC
Rated power (LO)	160.00 kW	250.00 hp
Rated power (HO)	132.00 kW	150.00 hp
Rated current (LO)	302.00 A	302.00 A
Rated current (HO)	250.00 A	240.00 A
Rated current (IN)	309.00 A	
Max. output current	408.00 A	
Pulse frequency	2 kHz	
Output frequency for vector control	0 200 Hz	
Output frequency for V/f control	0 550 Hz	

General tech. specifications			
Power factor λ	0.90 0.95		
Offset factor cos φ	0.99		
Efficiency η	0.98		
Sound pressure level (1m)	74 dB		
Power loss	3.670 kW		
Filter class (integrated)	RFI suppression filter for Category C2		
EMC category (with accessories)	Category C2		

Ambient conditions			
Standard board coating type	Class 3C3, according to IEC 60721-3-3: 2002		
Cooling	Air cooling using an integrated fan		
Cooling air requirement	0.210 m³/s (7.416 ft³/s)		
Installation altitude	1000 m (3280.84 ft)		
Ambient temperature			
Operation	-20 45 °C (-4 113 °F)		
Transport	-40 70 °C (-40 158 °F)		
Storage	-25 55 °C (-13 131 °F)		

## **Overload capability**

Low Overload (LO)

110% base load current IL for 60 s in a 300 s cycle time

High Overload (HO)

150% x base load current IH for 60 s within a 600 s cycle time

Page 1 of 3

**Relative humidity** 

Max. operation

95~% At 40 °C (104 °F), condensation and icing not permissible



# **MLFB-Ordering data**

### 6SL3230-2YE50-0AF0



Mechanical	data	Closed-loop cor	ntrol techniques
Degree of protection	IP20 / UL open type		
Size	FSG	V/f linear / square-law / parameterizable Yes	
Net weight	105 kg (231.49 lb)	V/f with flux current control (FCC)	Yes
Width	305 mm (12.01 in)	V/f ECO linear / square-law	Yes
Height	999 mm (39.33 in)	Sensorless vector control	Yes
Depth	369 mm (14.53 in)	Vector control, with sensor	No
Inputs / out		Encoderless torque control	Yes
Standard digital inputs	11.5.55	Torque control, with encoder	No
Number	6		
Switching level: 0→1	11 V	Communication	
Switching level: 1→0	5 V	Communication	PROFINET, EtherNet/IP
Max. inrush current	15 mA	Connections	
Fail-safe digital inputs		Signal cable	
Number	1	Conductor cross-section	0.15 1.50 mm <sup>2</sup> (AWG 24 AWG 16)
Digital outputs		Line side	
Number as relay changeover contact	2	Version	M10 screw
Output (resistive load)	DC 30 V, 5.0 A	Conductor cross-section	35.00 185.00 mm <sup>2</sup> (AWG 1 MCM 2 x 350)
Number as transistor	0	Motor end	
Analog / digital inputs		Version	M10 screw
Number	2 (Differential input)	Conductor cross-section	35.00 185.00 mm <sup>2</sup> (AWG 1 MCM 2 x 350)
Resolution	10 bit	DC link (for braking resistor)	(WG1 WEW 2 X 330)
Switching threshold as digital in	put		1410
0→1	4 V	PE connection	M10 screw
1→0	1.6 V	Max. motor cable length	(100 10 5)
Analog outputs		Shielded	150 m (492.13 ft)

# PTC/ KTY interface

Number

1 motor temperature sensor input, sensors that can be connected: PTC, KTY and Thermo-Click, accuracy  $\pm 5~^{\circ}\text{C}$ 

1 (Non-isolated output)




### MLFB-Ordering data

#### 6SL3230-2YE50-0AF0



Converter lo	osses to	EN	50598-	2*
--------------	----------	----	--------	----

Efficiency class	IE2
Comparison with the reference converter (90% / 100%)	-43.00 %



 $The \ percentage \ values \ show \ the \ losses \ in \ relation \ to \ the \ rated \ apparent \ power \ of \ the \ converter.$ 

The diagram shows the losses for the points (as per standard EN 50598) of the relative torque generating current (I) over the relative motor stator frequency(f). The values are valid for the basic version of the converter without options/components.

## Standards

Compliance with standards UL, cUL, CE, C-Tick (RCM), EAC, KCC, SEMI F47, REACH

CE marking EMC Directive 2004/108/EC, Low-Voltage Directive 2006/95/EC

# Operator panel: Basic Operator Panel (BOP-2)

S	Screen	Amb	ient conditions
Display design	LCD, monochrome	monochrome Ambient temperature during	
		Operation	0 50 °C (32 122 °F)
Mech	anical data	Storage	-40 70 °C (-40 158 °F)
Degree of protection	IP55 / UL type 12	Transport	-40 70 °C (-40 158 °F)
Net weight	0.14 kg (0.31 lb)	Relative humidity at 25°C (	during
Width	70.0 mm (2.76 in)	Max. operation	95 %
Height	106.85 mm (4.21 in)		Approvals
Depth	19.60 mm (0.77 in)		
		Certificate of suitability	CE, cULus, EAC, KCC, RCM

<sup>\*</sup>converted values