SIEMENS

Data sheet

3RA2110-0GD15-1AP0



Load feeder fuseless, Direct-on-line starting 400 V AC, Size S00 0.45...0.63 A 230 V AC screw terminal for 60 mm busbar systems (also fulfills type of coordination 1) Type of coordination 2, Iq = 150 kA 1 NO (contactor)

product brand name	SIRIUS
product designation	Direct (on-line) starter
design of the product	for 60 mm busbars
product type designation	3RA21
manufacturer's article number	
 of the supplied contactor 	<u>3RT2015-1AP01</u>
 of the supplied circuit-breakers 	<u>3RV2011-0GA10</u>
 of the supplied busbar adapter 	<u>8US1251-5DS10</u>
 of the supplied link module 	<u>3RA1921-1DA00</u>
General technical data	
size of the circuit-breaker	S00
size of load feeder	S00
insulation voltage with degree of pollution 3 at AC rated value	690 V
surge voltage resistance rated value	6 kV
degree of protection NEMA rating	other
shock resistance according to IEC 60068-2-27	6g / 11 ms
mechanical service life (switching cycles) of contactor typical	30 000 000
type of assignment	2
type of protection according to ATEX directive 2014/34/EU	Ex II (2) GD
certificate of suitability according to ATEX directive 2014/34/EU	DMT 02 ATEX F 001
Substance Prohibitance (Date)	10/01/2009
Ambient conditions	
ambient temperature	
 during operation 	-20 +60 °C
 during storage 	-50 +80 °C
during transport	-50 +80 °C
temperature compensation	-20 +60 °C
relative humidity during operation	10 95 %
Main circuit	
number of poles for main current circuit	3
design of the switching contact	electromechanical
adjustable current response value current of the current-dependent overload release	0.45 0.63 A
operating voltage	
 rated value 	690 V
 at AC-3 rated value maximum 	690 V

operating frequency rated value	50 60 Hz			
operational current at AC-3 at 400 V rated value	0.6 A			
operating power at AC-3				
at 400 V rated value	180 W			
Control circuit/ Control				
type of voltage of the control supply voltage	AC			
control supply voltage at AC				
• at 50 Hz rated value	230 V			
 at 50 Hz rated value 	230 230 V			
 at 60 Hz rated value 	230 V			
 at 60 Hz rated value 	230 230 V			
apparent holding power of magnet coil at AC	4.2 VA			
Auxiliary circuit				
product extension auxiliary switch	Yes			
Protective and monitoring functions				
trip class	CLASS 10			
design of the overload release	thermal (bimetallic)			
UL/CSA ratings				
full-load current (FLA) for 3-phase AC motor				
• at 480 V rated value	0.63 A			
Short-circuit protection				
product function short circuit protection	Yes			
design of the short-circuit trip	magnetic			
conditional short-circuit current (Iq)				
 at 400 V according to IEC 60947-4-1 rated value 	150 000 A			
Installation/ mounting/ dimensions				
mounting position	vertical			
fastening method	for snapping onto 60 mm busbar systems			
height	200 mm			
width	45 mm			
depth	155 mm			
required spacing				
for grounded parts				
	20 mm			
— forwards				
— backwards	0 mm			
— upwards	50 mm			
— at the side	20 mm			
— downwards	10 mm			
 for live parts 				
— forwards	20 mm			
— backwards	0 mm			
— upwards	50 mm			
— downwards	10 mm			
— at the side	20 mm			
Connections/ Terminals				
type of electrical connection				
• for main current circuit	screw-type terminals			
 for auxiliary and control circuit 	screw-type terminals			
Safety related data				
B10 value with high demand rate according to SN 31920	1 000 000			
proportion of dangerous failures				
with high demand rate according to SN 31920	73 %			
touch protection on the front according to IEC 60529	finger-safe, for vertical contact from the front			
Communication/ Protocol				
protocol is supported				
PROFINET IO protocol	No			
PROFIsafe protocol	No			
protocol is supported AS-Interface protocol	No			
Certificates/ approvals				


General Product A	pproval			For use in hazard- ous locations	Declaration of Conformity
SP Esa	<u>Confirmation</u>	(UL) III	EHC	K ATEX	UK CA
Declaration of Conformity	Test Certificates		Marine / Shipping		
CE EG-Konf.	Special Test Certific- ate	<u>Type Test Certific-</u> ates/Test Report	ABS	BUREAU VERITAS	Lloyd's Register uts
Marine / Shipping				other	Railway
PRS	RINA	RMRS RMRS	DNV-GL DNV-GL DNV-LCORAP	<u>Confirmation</u>	Vibration and Shock
https://www.siemens Industry Mall (Onlin https://mall.industry.s Cax online generate http://support.automa Service&Support (M	ne ordering system) siemens.com/mall/en/en/	Catalog/product?mlfb= CAXorder/default.aspx haracteristics, FAQs,	?lang=en&mlfb=3RA211)		


http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3RA2110-0GD15-1AP0&lang=en Characteristic: Tripping characteristics, I²t, Let-through current


 https://support.industry.siemens.com/cs/ww/en/ps/3RA2110-0GD15-1AP0/char

 Further characteristics (e.g. electrical endurance, switching frequency)

 http://www.automation.siemens.com/bilddb/index.aspx?view=Search&mlfb=3RA2110-0GD15-1AP0&objecttype=14&gridview=view1







last modified:

2/16/2022 🖸