3RA2110-1AA15-1BB4

Data sheet



Load feeder fuseless, Direct-on-line starting 400 V AC, Size S00 1.10...1.60 A 24 V DC screw terminal for installation on standard mounting rail (also fulfills type of coordination 1) Type of coordination 2, Iq = 150 kA 1 NO (contactor)

| product brand name | SIRIUS |
|--|-------------------------------------|
| product designation | Direct (on-line) starter |
| design of the product | for standard rail or screw mounting |
| product type designation | 3RA21 |
| manufacturer's article number | |
| of the supplied contactor | 3RT2015-1BB41 |
| of the supplied circuit-breakers | 3RV2011-1AA10 |
| of the supplied link module | 3RA1921-1DA00 |
| General technical data | |
| size of the circuit-breaker | S00 |
| size of load feeder | S00 |
| insulation voltage with degree of pollution 3 at AC rated value | 690 V |
| surge voltage resistance rated value | 6 kV |
| degree of protection NEMA rating | other |
| shock resistance according to IEC 60068-2-27 | 6g / 11 ms |
| mechanical service life (switching cycles) of contactor typical | 30 000 000 |
| type of assignment | 2 |
| type of protection according to ATEX directive 2014/34/EU | Ex II (2) GD |
| certificate of suitability according to ATEX directive 2014/34/EU | DMT 02 ATEX F 001 |
| Substance Prohibitance (Date) | 10/01/2009 |
| Ambient conditions | |
| ambient temperature | |
| during operation | -20 +60 °C |
| during storage | -50 +80 °C |
| during transport | -50 +80 °C |
| temperature compensation | -20 +60 °C |
| relative humidity during operation | 10 95 % |
| Main circuit | |
| number of poles for main current circuit | 3 |
| design of the switching contact | electromechanical |
| adjustable current response value current of the current-dependent overload release | 1.1 1.6 A |
| operating voltage | |
| • rated value | 690 V |
| • at AC-3 rated value maximum | 690 V |
| operating frequency rated value | 50 60 Hz |

| operational current at AC-3 at 400 V rated value | 1.5 A |
|---|--|
| operating power at AC-3 | |
| at 400 V rated value | 550 W |
| Control circuit/ Control | |
| type of voltage of the control supply voltage | DC |
| control supply voltage at DC | |
| rated value | 24 V |
| rated value | 24 24 V |
| holding power of magnet coil at DC | 4 W |
| Auxiliary circuit | |
| product extension auxiliary switch | Yes |
| Protective and monitoring functions | |
| trip class | CLASS 10 |
| design of the overload release | thermal (bimetallic) |
| UL/CSA ratings | |
| - | |
| full-load current (FLA) for 3-phase AC motor • at 480 V rated value | 1.6 A |
| yielded mechanical performance [hp] | 1.071 |
| • for 3-phase AC motor | |
| — at 460/480 V rated value | 0.75 hp |
| — at 575/600 V rated value | 0.75 hp |
| Short-circuit protection | |
| | Yes |
| product function short circuit protection design of the short-circuit trip | magnetic |
| | magnetic |
| conditional short-circuit current (Iq) • at 400 V according to IEC 60947-4-1 rated value | 150 000 A |
| | 130 000 A |
| Installation/ mounting/ dimensions | |
| mounting position | vertical |
| fastening method | screw and snap-on mounting onto 35 mm standard mounting rail |
| height width | 167 mm 45 mm |
| | 97 mm |
| depth required encoing | 97 11111 |
| required spacing | |
| for grounded partsforwards | 20 mm |
| — lorwards — backwards | 0 mm |
| — upwards | 50 mm |
| — at the side | 20 mm |
| — driftle side — downwards | 10 mm |
| for live parts | 10 11111 |
| — forwards | 20 mm |
| — lorwards — backwards | 0 mm |
| — upwards | 50 mm |
| — downwards | 10 mm |
| — at the side | 20 mm |
| Connections/ Terminals | |
| type of electrical connection | |
| for main current circuit | screw-type terminals |
| for main current circuit for auxiliary and control circuit | screw-type terminals screw-type terminals |
| type of connectable conductor cross-sections | Solow-type terrilliais |
| • for main contacts | |
| — stranded | 0.5 4 mm², 2x (0.75 2.5 mm²) |
| at AWG cables for main contacts | 2x (20 16), only for contactor 2x (18 14), 2x 12 |
| connectable conductor cross-section for main contacts | 0.5 2.5 mm ² |
| finely stranded with core end processing | 5.5 <u>2.0</u> Hill |
| Safety related data | |
| | |
| | 1 000 000 |
| B10 value with high demand rate according to SN 31920 | 1 000 000 |
| | 1 000 000 73 % |

touch protection on the front according to IEC 60529 finger-safe, for vertical contact from the front Communication/ Protocol protocol is supported • PROFINET IO protocol No PROFIsafe protocol No protocol is supported AS-Interface protocol No

Certificates/ approvals

General Product Approval

For use in hazardous locations

Declaration of Conformity



Confirmation









Declaration of Conformity

Test Certificates

Marine / Shipping



Special Test Certificate

Type Test Certificates/Test Report







Marine / Shipping

other Railway









Confirmation

Vibration and Shock

Dangerous Good

Transport Information

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

https://www.siemens.com/ic10

Industry Mall (Online ordering system)

https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3RA2110-1AA15-1BB4

Cax online generator

http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RA2110-1AA15-1BB4

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

https://support.industry.siemens.com/cs/ww/en/ps/3RA2110-1AA15-1BB4

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3RA2110-1AA15-1BB4&lang=en

Characteristic: Tripping characteristics, I2t, Let-through current

https://support.industry.siemens.com/cs/ww/en/ps/3RA2110-1AA15-1BB4/char

Further characteristics (e.g. electrical endurance, switching frequency)

http://www.automation.siemens.com/bilddb/index.aspx?view=Search&mlfb=3RA2110-1AA15-1BB4&objecttype=14&gridview=view1

last modified:

2/16/2022