### K10D004QCH

cam stepping switch - 1 pole -  $30^{\circ}$  - 10~A - for Ø 16 or 22 mm



Main		
Range of Product	Harmony K	
Product or Component Type	Complete cam switch	
Component name	K10	
[lth] conventional free air thermal current	10 A	
Product mounting	Front mounting	
Fixing Mode	Ø 16 or 22 mm hole	
Cam switch head type	With front plate 30 x 30 mm	
Type of operator	Black handle	
Rotary handle padlocking	Without	
Presentation of legend	With metallic, 0 - 1 - 2 - 3 - 4 black	
Cam switch function	Stepping switch	
Return	Without	
Off position	With Off position	
Poles description	1P	
Switching positions	Right: 270° - 300° - 330° - 0° - 30°	
IP degree of protection	Contact block IP20 Operating head IP65 IEC 60529	

#### Complementary

Complementary		
Number of steps	4	
Switching angle	30 °	
[Ui] rated insulation voltage	440 V 3)IEC 60947-1	
Rated operational power in W	370 W AC-23A, 110/120 V 1 phase 750 W AC-23A, 220/240 V 1 phase	
Rated power in hp	0.33 Hp 110/120 V AC, 1 phase 0.75 hp 220/240 V AC, 1 phase	
[le] rated operational current AC	10 A 400 V AC-1 10 A 400 V AC-21A 3 A 240 V AC-15 6 A 120 V AC-15	
[le] rated operational current DC	10 A 24 V resistive 0.3 A 220 V resistive 0.7 A 110 V resistive	
Electrical durability	100000000 cycles	
Short-circuit protection	10 A cartridge fuse gG	
[Uimp] rated impulse withstand voltage	4 kV IEC 60947-1	
Contact operation	Slow-break	
Electrical connection	Captive screw clamp terminals 2 x 1.5 mm <sup>2</sup>	
Mechanical durability	1000000 cycles	
CAD overall width	1.18 in (30 mm)	
CAD overall height	1.18 in (30 mm)	
CAD overall depth	3.46 in (88 mm)	
Net Weight	0.10 lb(US) (0.045 kg)	

#### Environment

Standards	CENELEC EN 50013 EN/IEC 60947-3 EN/IEC 60947-5-1
Product certifications	CULus
Protective treatment	TC
Ambient air temperature for operation	-4131 °F (-2055 °C)
Ambient Air Temperature for Storage	-40158 °F (-4070 °C)
Electrical shock protection class	Class II IEC 60536

### Ordering and shipping details

Category	21446 - 9003 K CAM SWITCHES
Discount Schedule	CS1
GTIN	3389110076578
Nbr. of units in pkg.	1
Package weight(Lbs)	2.19 oz (62 g)
Returnability	No
Country of origin	AT

### **Packing Units**

r doming office	
Unit Type of Package 1	PCE
Package 1 Height	1.61 in (4.1 cm)
Package 1 width	1.61 in (4.1 cm)
Package 1 Length	4.13 in (10.5 cm)
Unit Type of Package 2	S02
Number of Units in Package 2	65
Package 2 Weight	10.30 lb(US) (4.67 kg)
Package 2 Height	5.91 in (15 cm)
Package 2 width	11.81 in (30 cm)
Package 2 Length	15.75 in (40 cm)

### Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACh Regulation	REACh Declaration
REACh free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	₫Yes
China RoHS Regulation	☑ China RoHS Declaration
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

### Contractual warranty


Warranty	18 months

# Product data sheet Dimensions Drawings

## K10D004QCH

### Cam Switch

### Front Mounting by Ø16 mm/0.63 in. or Ø 22 mm/0.87 in. hole




- a 63 mm/2.48 in.
- e support panel thickness: 0.5 mm to 5 mm/0.02 in. to 0.2 in.


# Product data sheet Mounting and Clearance

## K10D004QCH

### Cam Switch

### Ø 16 mm/0.63 in. and Ø 22 mm/0.87 in. Panel Cut-outs






## Product data sheet Technical Description

### K10D004QCH

#### Link Positions (Factory Mounted)



#### Marking



### Angular Position of Switch



### Switching Program



### Convention Used for Switching Program Representation

Contact closed

Contact closed in 2 positions and maintained between the 2 positions

Sealed assembly for auto-maintain control

Overlapping contacts

Spring return position: for a switching angle of 90°, spring return is over 30° after the last position (for a maximum of 3 simultaneous contacts).

Example:

