SIEMENS

Data sheet

3RA2220-0GB23-0BB4



Combination Starter Reversing FLA Ramge 0.45-0.63A 3 Pole 24VDC Coil S2 Open Type 1NO <(>&<)> 1NC Aux

product brand name	SIRIUS				
product designation	non-fused motor starter 3RA2				
design of the product	reversing starter				
manufacturer's article number					
 of the supplied contactor 	3RT2023-1BB40				
 of the supplied circuit-breakers 	3RV2011-0GA10				
 of the supplied RH assembly kit 	3RA2923-1BB1				
 of the supplied busbar adapter 	3RA2922-1AA00				
 of the supplied link module 	3RA2921-1BA00				
 of the supplied standard mounting rail adapter 	3RA2922-1AA00				
General technical data					
size of the circuit-breaker	S00				
size of load feeder	S0				
product extension auxiliary switch	Yes				
insulation voltage with degree of pollution 3 at AC rated value	690 V				
degree of pollution	3				
surge voltage resistance rated value	6 kV				
shock resistance according to IEC 60068-2-27	6g / 11 ms				
mechanical service life (switching cycles) of contactor typical	10 000 000				
type of assignment	2				
Ambient conditions					
ambient temperature					
 during operation 	-20 +60 °C				
during storage	-50 +80 °C				
during transport	-55 +80 °C				
Main circuit					
number of poles for main current circuit	3				
design of the switching contact	electromechanical				
adjustable current response value current of the current-dependent overload release	0.45 0.63 A				
operating voltage					
rated value	690 V				
at AC-3 rated value maximum	690 V				
operating frequency rated value	50 60 Hz				
operational current at AC-3 at 400 V rated value	0.6 A				
operating power at AC-3					
● at 400 V rated value	180 W				
at 500 V rated value	180 W				

• at 690 V rated value		250 V	V				
Control circuit/ Control							
control supply voltage at DC							
• rated value		24 V					
holding power of magnet coil at DC		5.9 V	I				
		3.9 V					
Auxiliary circuit							
number of NC contacts for auxiliary contact		. 2					
number of NO contacts for auxiliary contacts			2				
Protective and monitoring functions							
trip class		CLASS 10					
design of the overload release		thermal (bimetallic)					
response value current of instantaneous short- unit	circuit trip	8.19 A					
Short-circuit protection							
product function short circuit protection		Yes					
design of the short-circuit trip		magr	magnetic				
conditional short-circuit current (Iq)							
 at 400 V according to IEC 60947-4-1 rate 	ed value	153 (000 A				
Installation/ mounting/ dimensions		,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,	155 000 A				
mounting position		vertic	al				
fastening method			snap-on fastening on 35 mm standard rail				
height width			265 mm				
		90 mm					
depth		130 mm					
required spacing							
• for grounded parts		40					
— forwards		10 mm					
— backwards		0 mm					
— upwards		30 mm					
— at the side		9 mm					
— downwards		10 m	10 mm				
 for live parts 							
— forwards		10 mm					
— backwards		0 mm					
— upwards		30 mm					
— downwards		10 mm					
— at the side		9 mm					
Connections/ Terminals							
type of electrical connection for main current circuit		screw-type terminals					
type of connectable conductor cross-sectio	ns		•				
for main contacts stranded		1 10 mm², 2x (2.5 6 mm²)					
 at AWG cables for main contacts 		2x (16 12), 2x (14 8)					
connectable conductor cross-section for main contacts finely stranded with core end processing		1 6 mm²					
Safety related data							
B10 value with high demand rate according to SN 31920			1 000 000				
proportion of dangerous failures with high demand rate according to SN 31920		73 %					
protection class IP on the front according to IEC 60529		IP20					
touch protection on the front according to IEC 60529		finger-safe, for vertical contact from the front					
Certificates/ approvals			migo. Sale, for voludar contact from the from				
General Product Approval	For use in ha		Declaration of Conformity	other	Dangerous Good		
Confirmation	⟨£x⟩	•	C€	Confirmation	Transport Informa- tion		

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

https://www.siemens.com/ic10

Industry Mall (Online ordering system)

https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3RA2220-0GB23-0BB4

Cax online generator

 $\underline{http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en\&mlfb=3RA2220-0GB23-0BB4}$

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

https://support.industry.siemens.com/cs/ww/en/ps/3RA2220-0GB23-0BB4

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3RA2220-0GB23-0BB4&lang=en

Characteristic: Tripping characteristics, I2t, Let-through current

https://support.industry.siemens.com/cs/ww/en/ps/3RA2220-0GB23-0BB4/char

Further characteristics (e.g. electrical endurance, switching frequency)

http://www.automation.siemens.com/bilddb/index.aspx?view=Search&mlfb=3RA2220-0GB23-0BB4&objecttype=14&gridview=view1