

#### **ASPI-0530HI Series**

Request Samples



Check Inventory (>)



5.7 x 5.3 x 3.0 mm **RoHS/RoHS II Compliant** MSL Level = 1

#### **Features**

- High saturation current.
- Low loss due to low DC resistance.
- Frequency application up to 3MHz.
- Low profile with max thickness 3.0mm.
- 100% lead free and RoHS compliant.
- Suitable for reflow soldering.
- High reliable SMD package

## **Electrical Specifications**

### **Applications**

- DC/DC converters in Notebook, Netbook, desktop, and server
- Low profile, high current power supplies.

Part Number	Inductance	Tolerance	DCR Typ	DCR Max	Saturation Current	Temperature Rise Current
Units	μH	%	mΩ	mΩ	A	A
Symbol	L	M			Isat*	Irms*
ASPI-0530HI-R22	0.22	M	4.0	5.0	23.0	15.0
ASPI-0530HI-R33	0.33	M	5.0	6.0	20.0	12.0
ASPI-0530HI-R47	0.47	M	6.3	7.4	18.0	13.0
ASPI-0530HI-R68	0.68	M	9.1	10.0	14.0	10.0
ASPI-0530HI-1R0	1.0	M	13.0	14.0	11.0	7.0
ASPI-0530HI-1R5	1.5	M	20.0	25.0	10.0	6.0
ASPI-0530HI-2R2	2.2	M	29.0	35.0	9.0	5.5
ASPI-0530HI-3R3	3.3	M	34.0	38.0	8.0	5.0
ASPI-0530HI-4R7	4.7	M	54.0	60.0	4.5	4.5
ASPI-0530HI-5R6	5.6	M	55.0	65.0	4.0	4.5
ASPI-0530HI-6R8	6.8	M	65.0	76.5	4.0	3.8
ASPI-0530HI-100	10.0	M	104	120	3.5	3.2

### **Test Conditions**

- 1. Inductance is measured in HP-4284A Precision LCR Meter.
- 2. RDC is measured in HP-4338B milli ohm meter. (Or equivalent).
- 3. Isat: Based on inductance change ( $\Delta L/Lo$ :  $\leq$  -20%)
- 4. Irms: Based on temperature rise ( $\Delta T: 40^{\circ}C TYP$ .)


**Operating Temperature & Humidity:** -55°C to +125°C (Including self-generated heat)

Storage Temperature & Humidity: +25°C to +35°C, 45% to 75% RH

**Maximum Voltage: 30VDC** 



**REVISION C: 10/24/2022** CERTIFIED



#### **ASPI-0530HI Series**

Request Samples





Check Inventory





5.7 x 5.3 x 3.0 mm RoHS/RoHS II Compliant MSL Level = 1


### **Performance Graphs**



















#### **ASPI-0530HI Series**

Request Samples





Check Inventory





5.7 x 5.3 x 3.0 mm RoHS/RoHS II Compliant MSL Level = 1


### **Performance Graphs**



















### **ASPI-0530HI Series**

Request Samples (>)




Check Inventory (>)




5.7 x 5.3 x 3.0 mm **RoHS/RoHS II Compliant** MSL Level = 1

### **Mechanical Specifications**



A	В	C	D	E
5.7 ±0.30	5.3 ±0.40	3.0 MAX	$2.2 \pm 0.5$	$1.2 \pm 0.50$


### **Recommended Land Pattern**



A	В	C
7.0 Typ.	3.0 Typ.	2.5 Typ.

**Dimensions: mm** 

### **Part Number Identification**





5101 Hidden Creek Ln, Spicewood TX 78669 Phone: 512-371-6159 Fax: 512-351-8858 For terms and conditions of sales, please visit: www.abracon.com

**REVISION C: 10/24/2022** 

ABRACON IS ISO9001-2015 CERTIFIED



### **ASPI-0530HI Series**

Request Samples (>)




Check Inventory (>)



5.7 x 5.3 x 3.0 mm RoHS/RoHS II Compliant MSL Level = 1

### **Reflow Profile**



Zone	Description	Temperature	Times
1	Preheat	$T_{SMIN} \sim T_{SMAX} \\ 150^{\circ}\text{C} \sim 200^{\circ}\text{C}$	$60 \sim 120 \text{ sec.}$
2	Reflow	T <sub>L</sub> 200°C	20 sec.
3	Peak heat	Т <sub>Р</sub> 250°С	3 sec. MAX





### **ASPI-0530HI Series**

Request Samples (>)




Check Inventory (>)




5.7 x 5.3 x 3.0 mm **RoHS/RoHS II Compliant** MSL Level = 1


### **Packaging**

T2: 2,000pcs / reel



A0	5.7 ±0.3
B0	5.9 ±0.3
K0	3.4 ±0.3
P	8.0 ±0.1
t	0.4 Typ
W	12 ±0.3
E	1.75 ±0.1
F	5.5 ±0.1
D	1.5 ±0.1
Н	12.5





**Dimension: mm** 

ATTENTION: Abracon LLC's products are COTS - Commercial-Off-The-Shelf products; suitable for Commercial, Industrial and, where designated, Automotive Applications. Abracon's products and/or property. For applications requiring high reliability and/or presenting an extreme operating environment, written consent and authorization from Abracon LLC is required. Please contact Abracon LLC for more information.



**REVISION C: 10/24/2022** 

ABRACON IS ISO9001-2015 CERTIFIED