SIEMENS

Data sheet

3RW5235-2AC04



SIRIUS soft starter 200-480 V 143 A, 24 V AC/DC spring-type terminals Analog output

product brand name	SIRIUS	
product category	Hybrid switching devices	
product designation	Soft starter	
product type designation	3RW52	
manufacturer's article number		
 of standard HMI module usable 	<u>3RW5980-0HS00</u>	
 of high feature HMI module usable 	<u>3RW5980-0HF00</u>	
 of communication module PROFINET standard usable 	<u>3RW5980-0CS00</u>	
 of communication module PROFIBUS usable 	<u>3RW5980-0CP00</u>	
 of communication module Modbus TCP usable 	<u>3RW5980-0CT00</u>	
 of communication module Modbus RTU usable 	<u>3RW5980-0CR00</u>	
 of communication module Ethernet/IP 	<u>3RW5980-0CE00</u>	
 of circuit breaker usable at 400 V 	3VA2220-7MN32-0AA0; Type of coordination 1, Iq = 65 kA, CLASS 10	
 of circuit breaker usable at 400 V at inside-delta circuit 	3VA2325-7MN32-0AA0; Type of coordination 1, Iq = 65 kA, CLASS 10	
 of the gG fuse usable up to 690 V 	<u>3NA3244-6; Type of coordination 1, Iq = 65 kA</u>	
 of the gG fuse usable at inside-delta circuit up to 500 V 	<u>3NA3244-6; Type of coordination 1, Iq = 65 kA</u>	
 of full range R fuse link for semiconductor protection usable up to 690 V 	<u>3NE1227-0; Type of coordination 2, Iq = 65 kA</u>	
 of back-up R fuse link for semiconductor protection usable up to 690 V 	<u>3NE3334-0B; Type of coordination 2, Iq = 65 kA</u>	
General technical data		
starting voltage [%]	30 100 %	
stopping voltage [%]	50 %; non-adjustable	
start-up ramp time of soft starter	0 20 s	
current limiting value [%] adjustable	130 700 %	
certificate of suitability		
CE marking	Yes	
 UL approval 	Yes	
CSA approval	Yes	
product component		
HMI-High Feature	No	
 is supported HMI-Standard 	Yes	
 is supported HMI-High Feature 	Yes	
product feature integrated bypass contact system	Yes	
number of controlled phases	3	
trip class	CLASS 10A (default) / 10E / 20E; acc. to IEC 60947-4-2	
buffering time in the event of power failure		
 for main current circuit 	100 ms	

for control circuit	100 ms
insulation voltage rated value	600 V
degree of pollution	3, acc. to IEC 60947-4-2
impulse voltage rated value	6 kV
blocking voltage of the thyristor maximum	1 400 V
service factor	1
surge voltage resistance rated value	6 kV
maximum permissible voltage for safe isolation	
between main and auxiliary circuit	600 V
shock resistance	15 g / 11 ms, from 12 g / 11 ms with potential contact lifting
vibration resistance	15 mm to 6 Hz; 2g to 500 Hz
	AC 53a
utilization category according to IEC 60947-4-2	Q
reference code according to IEC 81346-2	02/15/2018
Substance Prohibitance (Date)	02/15/2016
product function	
• ramp-up (soft starting)	Yes
• ramp-down (soft stop)	Yes
Soft Torque	Yes
adjustable current limitation	Yes
pump ramp down	Yes
intrinsic device protection	Yes
motor overload protection	Yes; Electronic motor overload protection
evaluation of thermistor motor protection	No
inside-delta circuit	Yes
auto-RESET	Yes
manual RESET	Yes
remote reset	Yes; By turning off the control supply voltage
 communication function 	Yes
 operating measured value display 	Yes; Only in conjunction with special accessories
 error logbook 	Yes; Only in conjunction with special accessories
 via software parameterizable 	No
 via software configurable 	Yes
PROFlenergy	Yes; in connection with the PROFINET Standard communication module
 firmware update 	Yes
 removable terminal for control circuit 	Yes
torque control	No
 analog output 	Yes; 4 20 mA (default) / 0 10 V (parameterizable with High Feature HMI)
Power Electronics	
operational current	
• at 40 °C rated value	143 A
• at 50 °C rated value	128 A
• at 60 °C rated value	118 A
operational current at inside-delta circuit	
• at 40 °C rated value	248 A
• at 50 °C rated value	222 A
● at 60 °C rated value	204 A
operating voltage	
rated value	200 480 V
at inside-delta circuit rated value	200 480 V
relative negative tolerance of the operating voltage	-15 %
relative positive tolerance of the operating voltage	10 %
relative negative tolerance of the operating voltage at inside-delta circuit	-15 %
relative positive tolerance of the operating voltage at inside-delta circuit	10 %
operating power for 3-phase motors	
• at 230 V at 40 °C rated value	37 kW
 at 230 V at inside-delta circuit at 40 °C rated value 	75 kW
• at 400 V at 40 °C rated value	75 kW

 at 400 V at inside-delta circuit at 40 °C rated value 	132 kW
Operating frequency 1 rated value	50 Hz
Operating frequency 2 rated value	60 Hz
relative negative tolerance of the operating frequency	-10 %
relative positive tolerance of the operating frequency	10 %
adjustable motor current	
 at rotary coding switch on switch position 1 	68 A
 at rotary coding switch on switch position 2 	73 A
 at rotary coding switch on switch position 3 	78 A
 at rotary coding switch on switch position 4 	83 A
 at rotary coding switch on switch position 5 	88 A
 at rotary coding switch on switch position 6 	93 A
 at rotary coding switch on switch position 7 	98 A
 at rotary coding switch on switch position 8 	103 A
 at rotary coding switch on switch position 9 	108 A
 at rotary coding switch on switch position 10 	113 A
 at rotary coding switch on switch position 11 	118 A
 at rotary coding switch on switch position 12 	123 A
 at rotary coding switch on switch position 13 	128 A
 at rotary coding switch on switch position 14 	133 A
 at rotary coding switch on switch position 15 	138 A
 at rotary coding switch on switch position 16 	143 A
• minimum	68 A
adjustable motor current	
 for inside-delta circuit at rotary coding switch on switch position 1 	118 A
 for inside-delta circuit at rotary coding switch on switch position 2 	126 A
 for inside-delta circuit at rotary coding switch on switch position 3 	135 A
 for inside-delta circuit at rotary coding switch on switch position 4 	144 A
 for inside-delta circuit at rotary coding switch on switch position 5 	152 A
 for inside-delta circuit at rotary coding switch on switch position 6 	161 A
 for inside-delta circuit at rotary coding switch on switch position 7 	170 A
 for inside-delta circuit at rotary coding switch on switch position 8 	178 A
for inside-delta circuit at rotary coding switch on switch position 9	187 A
for inside-delta circuit at rotary coding switch on switch position 10	196 A
for inside-delta circuit at rotary coding switch on switch position 11	204 A
 for inside-delta circuit at rotary coding switch on switch position 12 for inside delta circuit at rotary coding switch on 	213 A 222 A
 for inside-delta circuit at rotary coding switch on switch position 13 for inside-delta circuit at rotary coding switch on 	230 A
 for inside-delta circuit at rotary coding switch on for inside-delta circuit at rotary coding switch on 	239 A
 switch position 15 for inside-delta circuit at rotary coding switch on 	248 A
switch position 16 • at inside-delta circuit minimum	118 A
minimum load [%]	15 %; Relative to smallest settable le
power loss [W] for rated value of the current at AC	
• at 40 °C after startup	55 W
• at 50 °C after startup	50 W
• at 60 °C after startup	47 W
power loss [W] at AC at current limitation 350 %	
• at 40 °C during startup	2 127 W

• at 50 °C during startup	1 807 W		
• at 60 °C during startup	1 605 W		
Control circuit/ Control			
type of voltage of the control supply voltage	AC/DC		
control supply voltage at AC			
• at 50 Hz rated value	24 V		
• at 60 Hz rated value	24 V		
relative negative tolerance of the control supply	-20 %		
voltage at AC at 50 Hz			
relative positive tolerance of the control supply voltage at AC at 50 Hz	20 %		
relative negative tolerance of the control supply voltage at AC at 60 Hz	-20 %		
relative positive tolerance of the control supply voltage at AC at 60 Hz	20 %		
control supply voltage frequency	50 60 Hz		
relative negative tolerance of the control supply voltage frequency	-10 %		
relative positive tolerance of the control supply voltage frequency	10 %		
control supply voltage			
• at DC rated value	24 V		
relative negative tolerance of the control supply voltage at DC	-20 %		
relative positive tolerance of the control supply voltage at DC	20 %		
control supply current in standby mode rated value	160 mA		
holding current in bypass operation rated value	380 mA		
locked-rotor current at close of bypass contact maximum	7.6 A		
inrush current peak at application of control supply voltage maximum	3.3 A		
duration of inrush current peak at application of control supply voltage	12.1 ms		
design of the overvoltage protection	Varistor		
design of short-circuit protection for control circuit	4 A gG fuse (Icu=1 kA), 6 A quick-acting fuse (Icu=1 kA), C1 miniature circuit breaker (Icu= 600 A), C6 miniature circuit breaker (Icu= 300 A); Is not part of scope of supply		
Inputs/ Outputs			
number of digital inputs	1		
number of digital outputs	3		
 not parameterizable 	2		
digital output version	2 normally-open contacts (NO) / 1 changeover contact (CO)		
number of analog outputs	1		
switching capacity current of the relay outputs			
 at AC-15 at 250 V rated value 	3 A		
• at DC-13 at 24 V rated value	1 A		
Installation/ mounting/ dimensions			
mounting position	with vertical mounting surface +/-90° rotatable, with vertical mounting surface +/- 22.5° tiltable to the front and back		
fastening method	screw fixing		
height	306 mm		
width	185 mm		
depth	203 mm		
required spacing with side-by-side mounting	10 mm		
 forwards backwards 	10 mm 0 mm		
 Dackwards upwards 	100 mm		
downwards	75 mm		
at the side	5 mm		
weight without packaging	6.6 kg		
Connections/ Terminals			
type of electrical connection			

- for main any and should	husher connection
for main current circuit	busbar connection
for control circuit	spring-loaded terminals
width of connection bar maximum	25 mm
type of connectable conductor cross-sections	$2x (16 - 05 mm^2)$
for DIN cable lug for main contacts stranded	$2x (16 95 mm^2)$
for DIN cable lug for main contacts finely stranded type of connectable conductor cross-sections	2x (25 120 mm²)
for control circuit solid	2x (0.25 1.5 mm²)
 for control circuit solid for control circuit finely stranded with core end 	2x (0.25 1.5 mm ²)
processing	
 at AWG cables for control circuit solid 	2x (24 16)
 at AWG cables for control circuit finely stranded with core end processing 	2x (24 16)
wire length	
 between soft starter and motor maximum 	800 m
 at the digital inputs at AC maximum 	100 m
 at the digital inputs at DC maximum 	1 000 m
tightening torque	
 for main contacts with screw-type terminals 	10 14 N·m
 for auxiliary and control contacts with screw-type 	0.8 1.2 N·m
terminals	
tightening torque [lbf·in]	
 for main contacts with screw-type terminals 	89 124 lbf·in
 for auxiliary and control contacts with screw-type 	7 10.3 lbf·in
terminals	
Ambient conditions	
installation altitude at height above sea level maximum	5 000 m; Derating as of 1000 m, see catalog
ambient temperature	
during operation	-25 +60 °C; Please observe derating at temperatures of 40 °C or above
 during storage and transport 	-40 +80 °C
environmental category	
 during operation according to IEC 60721 	3K6 (no ice formation, only occasional condensation), 3C3 (no salt mist), 3S2 (sand must not get into the devices), 3M6
 during storage according to IEC 60721 	1K6 (only occasional condensation), 1C2 (no salt mist), 1S2 (sand must not get inside the devices), 1M4
during transport according to IEC 60721	2K2, 2C1, 2S1, 2M2 (max. fall height 0.3 m)
EMC emitted interference	acc. to IEC 60947-4-2: Class A
Communication/ Protocol	
communication module is supported	
 PROFINET standard 	Yes
EtherNet/IP	Yes
Modbus RTU	Yes
Modbus TCP	Yes
PROFIBUS	Yes
UL/CSA ratings	
manufacturer's article number	
 of circuit breaker 	
 — usable for Standard Faults at 460/480 V according to UL 	Siemens type: 3VA52, max. 250 A; Iq = 10 kA
 — usable for High Faults at 460/480 V according to UL 	Siemens type: 3VA52, max. 250 A; lq max = 65 kA
 — usable for Standard Faults at 460/480 V at inside-delta circuit according to UL 	Siemens type: 3VA52, max. 250 A; Iq = 10 kA
 — usable for High Faults at 460/480 V at inside- delta circuit according to UL 	Siemens type: 3VA52, max. 250 A; lq max = 65 kA
 — usable for Standard Faults at 575/600 V according to UL 	Siemens type: 3VA52, max. 250 A; Iq = 10 kA
— usable for Standard Faults at 575/600 V at inside-delta circuit according to UL	Siemens type: 3VA52, max. 250 A; Iq = 10 kA
 of the fuse usable for Standard Faults up to 575/600 V according to UL 	Type: Class RK5 / K5, max. 350 A; lq = 10 kA

	ligh Faults up to 575/ I	600 V	Type: Class J / L, max. 35	0 A; Iq = 100 kA	
circuit up to 57	∟ tandard Faults at insi 5/600 V according to		Type: Class RK5 / K5, max	x. 350 A; lq = 10 kA	
	ligh Faults at inside-d		Type: Class J / L, max. 350	0 A; lq = 100 kA	
operating power [hp]	0				
• at 200/208 V at 5	•		40 hp		
• at 220/230 V at 5	50 °C rated value		40 hp		
• at 460/480 V at 5	50 °C rated value		100 hp		
 at 200/208 V at in value 	nside-delta circuit at 5	50 °C rated	75 hp		
	nside-delta circuit at §	50 °C rated	75 hp		
• at 460/480 V at inside-delta circuit at 50 °C rated value		150 hp			
contact rating of auxi	liary contacts accor	ding to UL	R300-B300		
Safety related data					
protection class IP on 60529	n the front according	g to IEC	IP00; IP20 with cover		
touch protection on tl	he front according t	o IEC 60529	finger-safe, for vertical con	tact from the front with	cover
electromagnetic com			in accordance with IEC 60		
Certificates/ approvals					
General Product App	oroval				EMC
(Ch	Confirmation		ŝ	r M F	A
QP		(uc)	(^y L)	FHI	
CSA		ccc	UL	LIIL	RCM
Declaration of Confo	rmity	Test Certifica	ates Marine / Shipping		
UK		Type Test Cer		See 2	
			nort Para	B	Llovds
Zò	CE	ates/Test Re	port 💓		Register
ČÀ	EG-Konf.		port	BUREAU	Lloyd's Register urs
ĊÀ	EG-Konf.		A SHOW	B UREAU VERITAS	
ĊÀ	EG-Konf.		A SHOW	BUREAU	Llovds Register us
Marine / Shipping	EG-Konf.		A SHOW	B UREAU VERITAS	Llovds Kegister uis
CA	CE EG-Konf.	ates/Test Re	ABS	BUREAU	Llovds Kegister urs
CA	EG-Konf.	ates/Test Re	ABS	BUREAU	Llovds Kegister uts
CA	EG-Konf.	ates/Test Re	ABS	BUREAU VERITAS	Llovds Kegister urs
CA	EG-Konf.	ates/Test Re	ABS	BUREAU VERITAS	Llovds Kegister urs
CA	EG-Konf.	ates/Test Re	ABS	BUREAU	Llovds Kegister us
CA	EG-Konf.	ates/Test Re	ABS	BUREAU	Liovots Kegister urs
CA	EG-Konf.	ates/Test Re	ABS	BUREAU VERITAS	Liovors Kegister urs
CA Marine / Shipping	mloadcenter (Catalo	ates/Test Re	ABS	BUREAU VERITAS	Lievers
CA Marine / Shipping	rnloadcenter (Catalo	ates/Test Re	ABS	BUREAU VERITAS	Lis
CA Marine / Shipping	rnloadcenter (Catalo om/ic10 ordering system)	other <u>Confirmatic</u> ogs, Brochures,.	ABS	E U R E A U VERITAS	Lievers
CA Marine / Shipping	rnloadcenter (Catalo om/ic10 ordering system) mens.com/mall/en/er	other <u>Confirmatic</u> ogs, Brochures,.	ABS ABS		Lievers
CA Marine / Shipping	rnloadcenter (Catalo om/ic10 ordering system) mens.com/mall/en/er	other <u>Confirmatic</u> ogs, Brochures,. h/Catalog/product	201) :?mlfb=3RW5235-2AC04 It.aspx?lang=en&mlfb=3RW5		Lis
CA Marine / Shipping	rnloadcenter (Catalo om/ic10 ordering system) mens.com/mall/en/er on.siemens.com/WW nuals, Certificates, o .siemens.com/cs/ww/	other <u>Confirmatic</u> ogs, Brochures,. <u>A/Catalog/product</u> <u>/CAXorder/defau</u> Characteristics, /en/ps/3RW5235-) ?mlfb=3RW5235-2AC04 It.aspx?lang=en&mlfb=3RW5 FAQs,) -2AC04	5 <u>235-2AC04</u>	
CA Marine / Shipping	rnloadcenter (Catalo om/ic10 ordering system) mens.com/mall/en/er on.siemens.com/WW nuals, Certificates, o .siemens.com/cs/ww/ luct images, 2D dim	other <u>Confirmatic</u> ogs, Brochures,. <u>A/Catalog/product</u> <u>/CAXorder/defau</u> Characteristics, <u>/en/ps/3RW5235-</u> ension drawing:	ABS ABS	5235-2AC04 t diagrams, EPLAN m	
CA Marine / Shipping	rnloadcenter (Catalo ordering system) mens.com/mall/en/er on.siemens.com/WW nuals, Certificates, o .siemens.com/cs/ww/ luct images, 2D dim siemens.com/bilddb/o	other Confirmatic ogs, Brochures,. //Catalog/product /CAXorder/defau Characteristics, /en/ps/3RW5235- ension drawing: cax_de.aspx?mlf	ABS ABS ABS ABS ABS ABS ABS ABS	5235-2AC04 t diagrams, EPLAN m	
CA Marine / Shipping	rnloadcenter (Catalo ordering system) mens.com/mall/en/er on.siemens.com/WW nuals, Certificates, o .siemens.com/cs/ww/ luct images, 2D dim siemens.com/bilddb/o ng characteristics, I	other <u>Confirmatic</u> ogs, Brochures,. <u>Catalog/product</u> <u>CAXorder/defau</u> <u>Characteristics,</u> <u>(en/ps/3RW5235-</u> ension drawing: <u>cax_de.aspx?mlff</u> ² t, Let-through c	ABS ABS ABS ABS ABS ABS ABS ABS	5235-2AC04 t diagrams, EPLAN m	
CA Marine / Shipping Marine / Shipping	mloadcenter (Catalo om/ic10 ordering system) mens.com/mall/en/er on.siemens.com/WW nuals, Certificates, of siemens.com/cs/ww/ luct images, 2D dim siemens.com/bilddb/n g characteristics, I .siemens.com/cs/ww/ ation altitude	other Confirmatic Ogs, Brochures,. Catalog/product (CAXorder/defau Characteristics, (en/ps/3RW5235- ension drawing: cax_de.aspx?mlfl ² t, Let-through c (en/ps/3RW5235-	ABS ABS ABS ABS ABS ABS ABS ABS	5235-2AC04 t diagrams, EPLAN m n	acros,)
CA Marine / Shipping Marine / Shipping	rnloadcenter (Catalo om/ic10 ordering system) mens.com/mall/en/er on.siemens.com/WW nuals, Certificates, o .siemens.com/cs/ww/ luct images, 2D dim siemens.com/bilddb/n g characteristics, I .siemens.com/cs/ww/ ation altitude siemens.com/bilddb/n	other Confirmatic Ogs, Brochures,. Catalog/product (CAXorder/defau Characteristics, (en/ps/3RW5235- ension drawing: cax_de.aspx?mlfl ² t, Let-through c (en/ps/3RW5235-	ABS ABS ABS ABS ABS ABS ABS ABS	5235-2AC04 t diagrams, EPLAN m n	acros,)
CA Marine / Shipping Marine / Shipping	rnloadcenter (Catalo om/ic10 ordering system) mens.com/mall/en/er on.siemens.com/WW nuals, Certificates, of siemens.com/bilddb/i luct images, 2D dim siemens.com/bilddb/i ng characteristics, I .siemens.com/cs/ww/ ation altitude siemens.com/bilddb/i off Starters (STS)	other Confirmatic Ogs, Brochures,. D/Catalog/product /CAXorder/defau Characteristics, /en/ps/3RW5235- ension drawing: cax_de.aspx?mlfl ² t, Let-through c /en/ps/3RW5235- index.aspx?view=	ABS ABS) :?mlfb=3RW5235-2AC04 It.aspx?lang=en&mlfb=3RW5 FAQs,) :2AC04 s, 3D models, device circui b=3RW5235-2AC04⟨=e :urrent :2AC04/char =Search&mlfb=3RW5235-2A	5235-2AC04 t diagrams, EPLAN m n	acros,)
CA Marine / Shipping Marine / Shipping	rnloadcenter (Catalo om/ic10 ordering system) mens.com/mall/en/er on.siemens.com/WW nuals, Certificates, of siemens.com/bilddb/i luct images, 2D dim siemens.com/bilddb/i ng characteristics, I .siemens.com/cs/ww/ ation altitude siemens.com/bilddb/i off Starters (STS)	other Confirmatic Ogs, Brochures,. D/Catalog/product /CAXorder/defau Characteristics, /en/ps/3RW5235- ension drawing: cax_de.aspx?mlfl ² t, Let-through c /en/ps/3RW5235- index.aspx?view=	ABS ABS) :?mlfb=3RW5235-2AC04 It.aspx?lang=en&mlfb=3RW5 FAQs,) :2AC04 s, 3D models, device circui b=3RW5235-2AC04⟨=e :urrent :2AC04/char =Search&mlfb=3RW5235-2A	5235-2AC04 t diagrams, EPLAN m n	acros,)

last modified: