

RoHS & Halogen Free & REACH Compliance.


SPECIFICATION FOR APPROVAL

Customer:		
Customer P/N:		
Drawing No:	CE1-011	869
Quantity:	X Pcs. Date:	2020/01/17
Chilisin P/N:	BMRHDY10103	02R2MA1
	SPECIFICATION ACCEPTED BY:	
COMPONENT	, , , , , , , , , , , , , , , , , , ,	
ENGINEER		
ELECTRICAL		
ENGINEER		
MECHANICAL		
ENGINEER		
APPROVED		
REJECTED		
奇力新電子股份有限公司 Chilisin Electronics Corp No. 29, Alley 301, Tehhsin Rd. Hukou,Hsinchu 303, Taiwan TEL: +886-3- 599-2646 FAX: +886-3- 599-9176 E-mail: sales@chilisin.com http://www.chilisin.com	Chilisin Electronics (Yuliangwei Administration Dongguan City, 0251~3 3-0232
奇力新電子(越南廠)有限 Chilisin Electronics (Vietnam) I No 143 - 145, Road No 10, VS Lap Le Commune, Thuy Nguy Haiphong City, Vietnam Tel: 84-316 255 688 Fax: 84 689 E-mail: sales@chilisin.com	Limited HuNan Chillisin Elect No. 8, Shaziao Liang County, Huaihua Cit	cronics Technology Co., Ltd gshuijing Town, Yuanling y, Hunan Province 419601, 82
Drawn by 陳明宗 Bruce.Chen	Checked by 吳韋邑 Wayne.Wu	Approved by 葉信賢 Ben.Yeh



BMRHDY101030 Series Specification

- 1 Scope: This specification applies to Large current and Low Loss SMD Power INDUCTOR
- 2 Part Numbering:




3 Rating:

Operating Temperature: - 55°C ~ 125°C (Including self - temperature rise)

Storage Temperature: (on tape & reel): -20 °C to +40 °C; 75% RH max.

4 Marking:



Marking: XXX

Marking color: Black


5 Standard Testing Condition

	Unless otherwise specified	In case of doubt
Temperature	Ordinary Temperature(15 to 35℃)	20 to 30°C
Humidity	Ordinary Humidity(25 to 85% RH)	50 to 80 %RH



BMRHDY101030 Series Specification

6 Configuration and Dimensions:



Dimensions in mm

TYPE	101030
Α	10.1 ± 0.3
В	11.2 ± 0.3
С	2.8 ± 0.2
D	3.0 ± 0.5
F	2.5 ± 0.5

7 Electrical Characteristics:

Part No.	Inductance (uH)	Tolerance (±%)	Test Freq.	Irms(A) Typ	Isat(A) Typ	RDC(mΩ) Max(Typ)	Marking
BMRHDY1010302R2MA1	2.2	20	100kHz.0.5V	13	16	9(8)	2R2

Note:


- 1. Operating temperature range -55° C ~125° C (Including self temperature rise)
- 2.Isat for Inductance drop 30% from its value without current.
- 4.The part temperature (ambient + temp rise) should not exceed 125°C under worst case operating conditions. Circuit design 125°C under worst case operating conditions. Component placement, PWB trace size and thickness, airflow and other cooling provisions all affect the part temperature. Part temperature should be verified in the end application.
- 5. Absolute maximum voltage 30VDC



BMRHDY101030 Series Specification

8 BMRHDY101030 Series

8.1 Construction:



8.2 Material List:

ITEM	PART	DESCRIPTION		
1	CORE	Magnetic Metal Powder		
2	WIRE	Copper wire		
3	TERMINAL	TERMINAL COPPER		




BMRHDY101030 Series Specification

9 PACKAGING

9.1 Packaging -Cover tape


The force for tearing off cover tape is 10 to 130 grams in the arrow direction.



9.2 Packaging Quantity

TYPE	PCS/REEL
101030	500

9.3 Reel Dimensions



Dimensions in mm


TYPE	Α	В	С	D
101030	330	100	13	24.4



BMRHDY101030 Series Specification


9 PACKAGING

9.4 Tape Dimensions in mm



TYPE	A0	В0	K0	D	E	W	P	P0	P2
101030	10.6	11.7	3.25	1.55	1.75	24	16	4	2

10 Recommended Pattern



Dimensions in mm

TYPE	A(mm)	B(mm)	C(mm)
101030	4.0	9.5	3.5

11 Note:

- 1. Please make sure that your product has been evaluated and confirmed against your specifications when our product is mounted to your product.
- 2. Do not knock nor drop.
- 3. All the items and parameters in this product specification have been prescribed on the premise that our product is used for the purpose,under the condition and in the environment agreed upon between you and us. You are requested not to use our product deviating from such agreement.
- 4. Please keep the distance between transformer/coil and other components (refer to the standard IEC 950)
- 5. The moisture sensitivity level (MSL) of products is classified as level 1.



BMRHDY101030 Series Specification



