




THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC		DST		REVISIONS			
GP	00	TP	LTR	DESCRIPTION	DATE	OWN	APP'D
		K		REVISED PER ECO-08-007327	26JAN2009	ZMR	WLM

TERMINAL 36 REQUIRED
 YELLOW COLOR DOT LOCATED IN CENTER



1. THE CONTACT SURFACES OF THE TERMINALS ARE COATED WITH LUBRICANT.
2. ALL DIMENSIONS SHOWN ARE FOR REFERENCE ONLY UNLESS OTHERWISE SPECIFIED.
3. MATERIAL:
 HOUSING - THERMOPLASTIC (BLACK)
 TERMINALS - HIGH STRENGTH COPPER ALLOY PLATED WITH EITHER .000030 MIN GOLD OR GOLD FLASH OVER PALLADIUM NICKEL .000030 MIN TOTAL ON CONTACT MATING SURFACE. .000050 MIN NICKEL UNDERPLATE OVER ENTIRE TERMINAL.
4. WIRE SIZE: 26, 27, OR 28 AWG 7 STRANDS OF COPPER CONDUCTORS. MAX INSULATION ϕ .045 IS ACCEPTABLE FOR MOST APPLICATIONS.
5. CORING MAY OR MAY NOT APPEAR AND IS AT THE DISCRETION OF TYCO ELECTRONICS.



AS SHOWN	552470-1
DESCRIPTION	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DRN A. HOLT 3-8-01	Tyco Electronics Corporation Harrisburg, PA 17105-3808
DIMENSIONS: INCHES		CHK M.D. FRIEL 3-28-01	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APRD S. HEGE 3-30-01	NAME
0 PLC	±	PRODUCT SPEC	PLUG ASSY. 36 POSITIONS, E SLOT BAIL LOCK, CHAMP-LOK
1 PLC	±	APPLICATION SPEC	
2 PLC	±	WEIGHT	
3 PLC	±	CUSTOMER DRAWING	
4 PLC	±	SCALE	RESTRICTED TO
ANGLES	±	SIZE	DATE CODE
		A2	00779
			C=552470
			SHEET 1 of 1
			REV K