

## PLS-045B-3VAI



## PLS-045B-3VAI

Stainless Steel Level Sensor

### Electrical Characteristics @ 25 °C

Contact form		B
Contact rating max.	W / VA	10
Switching voltage max.	VDC	200
	VAC	140
Switching current max.	A	1
Carry current max.	A	1.2
Breakdown voltage min.	VDC	240
Total resistance max.	mΩ	180

### Environmental Characteristics


Operating temperature	°C	-40 to +125
Storage temperature	°C	-40 to +125

### Mechanical Characteristics

Density of float typ.*	g / cm <sup>3</sup>	0.7
Recommended minimum gravity of medium	g / cm <sup>3</sup>	Density of float + 20%

\* in delivery condition

### Dimensions in mm



### Features

- Stainless Steel housing
- Rugged and durable
- Suitable for food contact
- Extended temperature range
- Customized types available

### Approvals



### Ordering Information

Packing Unit	5	pcs
Weight per piece	46	g
Weight per package	232	g

PLS-045B-3VAI




## PLS-045B-3VAI

Stainless Steel Level Sensor

### Material Information

	Material	Colour
Housing	Stainless Steel 304, mechanically polished	
Cable	UL 1332, AWG 24, 4 mm stripped and tinned	black
Nuts	Stainless Steel 304, M10, 1 pc preassembled	
Float	Stainless Steel 304, mechanically polished	
Potting	PU / Epoxy	black
Sealing ring	Silicone	white

### Operation View




### Remarks

When mounted near ferromagnetic parts switching distance of PLS-045B-3VAI may vary.

Electromagnetical influences and magnetic fields may change the switching behaviour of the Level Sensor.

### Mounting



When mounted stem up, operating functions are reversed.