

# R2016-40.000-12-F-0810-X-TR-N1


#### **SPECIFICATIONS**

PARAMETER	VALUE	
NOMINAL FREQUENCY	40.000 MHz	
MODE OF OSCILLATION	Fundamental	
FREQUENCY TOLERANCE AT 25°C	±8 ppm max	
FREQUENCY STABILITY OVER TEMPERATURE	±10 ppm max -30/+85 ±15 ppm max -40/-30	
OPERATING TEMPERATURE RANGE	-40°C to +85°C ←	
STORAGE TEMPERATURE RANGE	-40°C to +90°C	
AGING	±2 ppm per year	
LOAD CAPACITANCE	12 pF	
EQUIVALENT SERIES RESISTANCE	30 Ω max	
SHUNT CAPACITANCE	1.5 pF max ←	
DRIVE LEVEL	50 μW typ., 100 μW max	
SHOCK RESISTANCE	±5 ppm max 75 cm drop test in 3 axes onto a hard surface	
INSULATION RESISTANCE	500 MΩ min	




Photo is not actual part

# **MECHANICAL SPECIFICATION**



### **CARRIER TAPE DIMENSIONS**



NOTE: REFER TO EIA-481 FOR DIMENSIONS

#### PACKAGING


178 mm REEL DIAMETER 8 mm TAPE WIDTH, 4 mm PITCH QUANTITY: 3000 PIECES PER REEL

IN ACCORDANCE WITH EIA-481



## R2016-40.000-12-F-0810-X-TR-N1

### REFLOW PROFILE



Reflow profile			
Temperature Min Preheat	T <sub>SMIN</sub>	150°C	
Temperature Max Preheat	T <sub>SMAX</sub>	200°C	
Time (T <sub>SMIN</sub> to T <sub>SMAX</sub> )	t <sub>S</sub>	60-180 sec.	
Temperature	T <sub>L</sub>	217°C	
Peak Temperature	T <sub>P</sub>	260°C	
Ramp-up rate	R <sub>UP</sub>	3°C/sec max.	
Ramp-down rate	R <sub>DOWN</sub>	6°C/sec max.	
Time within 5°C of Peak Temperature	t <sub>P</sub>	10 sec.	
Time t[25°C] to Peak Temperature	t[25°C] to Peak	480 sec.	
Time	t <sub>L</sub>	60-150 sec.	

#### ENVIRONMENTAL

PARAMETER	VALUE
MOISTURE SENSITIVITY LEVEL	1
RoHS	Compliant
REACH SVHC	Compliant
HALOGEN-FREE	Compliant
ESD CLASSIFICATION LEVEL	N/A
TERMINATION FINISH	Au





# R2016-40.000-12-F-0810-X-TR-N1

#### MARKING

R400 x8yw

x – 1 or 2 digits as Internal Production ID code

y – Year code

w – Week code

YEAR CODE		
Year	Code	
2015	5	
2016	6	
2017	7	
2018	8	
2019	9	
2020	0	
2021	1	
2022	2	
2023	3	
2024	4	
2025	5	

ALPHA WEEK CODE TABLE					
Week	Code	Week	Code	Week	Code
1	a	19	S	37	K
2	b	20	t	38	L
3	С	21	u	39	M
4	d	22	v	40	N
5	e	23	w	41	О
6	f	24	x	42	P
7	g	25	У	43	Q
8	h	26	Z	44	R
9	i	27	A	45	S
10	j	28	В	46	T
11	k	29	C	47	U
12	1	30	D	48	V
13	m	31	E	49	W
14	n	32	F	50	X
15	О	33	G	51	Y
16	р	34	Н	52	Z
17	q	35	I		
18	r	36	J		

### APPROVAL

DRAWN BY	YG Jiao, October 21, 2019
APPROVED BY	AG, October 21, 2019
	A, Initial Release
REVISION	B, AR, July 21, 2020
	Updated the Current Revision Levels

Raltron Electronics / RAMI Technology USA, LLC, including its affiliates, employees, agents and other persons acting on its behalf (collectively Raltron/RAMI Tech), disclaim any and all liability for any errors or inaccuracies contained in this data sheet. While Raltron/RAMI Tech has made every reasonable effort ensure the accuracy of all product information, specifications and data contained herein, Raltron/RAMI Tech does not guarantee that the information is accurate, reliable or current. The product information is provided only for reference purposes only and is subject to change, correction or revision, at any time without notice. Raltron/RAMI Tech does not assume any liability, airning out of an application or use of any product described herein and disclaims any warranties expressed or implied. The user of products in such applications shall assume all risks of such use and will agree to hold Raltron/RAMI Tech, have a paginated and the product described herein and disclaims any warranties expressed or implied. The user of products in such applications shall assume all risks of such use and will agree to hold Raltron/RAMI Tech, have a paginated and the product described herein and disclaims any warranties expressed or implied. The user of products in such applications shall assume all risks of such use and will agree to hold Raltron/RAMI Tech, have a paginated and the product described herein and disclaims any warranties expressed or implied. The user of products in such applications shall assume all risks of such use and will agree to hold Raltron/RAMI Tech, the product described herein and disclaims any warranties expressed or implied.

Copyright © 2016, Raltron Electronics / RAMI Technology USA, LLC. All rights reserved. No part of this document may be reproduced in any form without the prior written permission of Raltron Electronics / RAMI Technology USA, LLC.